Specifications





compact IO expansion block, Modicon TM5, 20 IO, 12 DI, 8 DO, transistor

TM5C12D8T

Main				
Range Of Product	Modicon TM5			
Product Or Component Type	Compact I/O expansion block			
Complementary				
Enclosure Material	Plastic			
Colour	White			
Input/Output Number	20			
For Enclosure Nominal Dimensions	12 I + 8 O			
Number Of Modules	Digital input: 3 module(s) x 4 Digital output: 2 module(s) x 4			
Discrete Input Number	12			
Discrete Input Voltage	24 V			
Discrete Input Voltage Type	DC			
Input Voltage Limits	20.428.8 V			
Discrete Input Logic	Sink			
Discrete Input Current	3.75 mA			
Input Impedance	6.4 kOhm			
Analogue Input Number	0			
Discrete Output Number	8			
Discrete Output Type	Transistor			
Wiring Mode	3-wire for discrete input 3-wire for discrete output			
Output Voltage	24 V DC			
Output Voltage Limits	20.428.8 V DC			
Discrete Output Logic	Source			
Discrete Output Current	0.5 A per output			
Peak Output Current	4 A			
Voltage State 0 Guaranteed	<= 5 V			
Voltage State 1 Guaranteed	>= 15 V			
Input Filtering	<= 100 ms hardware <= 25 ms configurable by software			
Response Time	<= 300 µs from state 0 to state 1 for output <= 300 µs from state 1 to state 0 for output			

Maximum Leakage Current	5 μA (when switched off) for output		
Isolation	500 Vrms AC insulation between channel and bus No insulation between channels		
Maximum Voltage Drop	<0.3 V at 500 mA for output		
Current Consumption	68 mA at 5 V DC bus 80 mA at 24 V DC input/output		
Max Current	1000 mA sensor supply 1500 mA actuator supply 4000 mA loads on I/O power segment		
Maximum Power Dissipation In W	2.36 W		
Local Signalling	5 LEDs (green) for power supply 5 LEDs (red) for power supply 12 LEDs (green) for input status 8 LEDs (yellow) for output status		
Sensor Power Supply	24 V, 500 mA for all channels with overload, short-circuit and reverse polarity protection		
Electrical Connection	Removable spring terminal block		
Marking	CE		
Surge Withstand	0.5 kV differential mode 24 V DC conforming to IEC 61000-4-5 1 kV common mode 24 V DC conforming to IEC 61000-4-5		
Electromagnetic Compatibility	Compatibility EN/IEC 61000-4-6		
Disturbance Radiated/Conducted	CISPR 11		

Environment

Standards	IEC 61131-2 UL 508 CSA C22.2 No 213 CSA C22.2 No 142			
Product Certifications	C-Tick GOST-R CSA cULus			
Ambient Air Temperature For Operation	-1050 °C (vertical installation) -1060 °C (horizontal installation)			
Ambient Air Temperature For Storage	-4070 °C			
Relative Humidity	595 % without condensation			
Ip Degree Of Protection	IP20 conforming to IEC 61131-2			
Pollution Degree	2 conforming to IEC 60664			
Operating Altitude	02000 m			
Storage Altitude	03000 m			
Vibration Resistance	1 gn at 8.4…150 Hz on DIN rail 3.5 mm at 5…8.4 Hz on DIN rail			
Shock Resistance	15 gn for 11 ms			
Resistance To Electrostatic Discharge	4 kV on contact conforming to IEC 61000-4-2 8 kV in air conforming to IEC 61000-4-2			
Resistance To Electromagnetic Fields	etic 1 V/m 22.7 GHz conforming to IEC 61000-4-3 10 V/m 802000 MHz conforming to IEC 61000-4-3			
Resistance To Fast Transients	sients 1 kV (I/O) conforming to IEC 61000-4-4 1 kV (shielded cable) conforming to IEC 61000-4-4 2 kV (power lines) conforming to IEC 61000-4-4			
Mounting Support	DIN rail			

Net	Weight
-----	--------

0.24 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.000 cm
Package 1 Width	9.100 cm
Package 1 Length	11.000 cm
Package 1 Weight	273.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	36
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	10.171 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance


Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration		
China Rohs Regulation	China RoHS declaration		
Environmental Disclosure	Product Environmental Profile		
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins		
Circularity Profile	End of Life Information		

Presentation

TM5 Compact I/O Module




N°	Designation
1	Input electronic module / 4 digital inputs
2	Output electronic module / 4 digital outputs

Dimensions Drawings

Compact I/O Module


Dimensions




Mounting and Clearance

TM5 System

Spacing Requirements



Mounting on a DIN Rail



Connections and Schema


TM5 System Wiring Recommendations

Wire Sizes to Use with the Removable Spring Terminal Blocks

mm in.	9 0.35		å		æ
	mm²	0,082,5	0,252,5	0,251,5	2 x 0,252 x 0,75
	AWG	2814	2414	2416	2 x 242 x 18

Digital Input 4In

Wiring Diagram



1 Internal electronics


2 24 Vdc I/O power segment integrated into the bus bases

3 3-wire sensor

4 2-wire sensor

Digital Output 4Out

Wiring Diagram



1 Internal electronics

2 24 Vdc I/O power segment integrated into the bus bases


3 Inductive load protection

4 2-wire load

5 3-wire load

Performance Curves

Switching Inductive Load Characteristics



(3)

(1) Load resistance in $\boldsymbol{\Omega}$

(2) Load inductance in H

(3) Max. operating cycles / second