


Product datasheet

Specifications



Transformer, Trihal, IEC, dry type, 2000kVA, 13,8kV, dyn11, 17,5kV, IP31, aluminum windings, air forced cooling

TRI200013682529802

 **Discontinued on:** Nov 20, 2022 AD

 **Discontinued**

Main

Product Range	Trihal
Product Or Component Type	Transformer
Transformer Type	Dry type transformer
Network Type	AC
Directives	2015/2014/548/EC- ecodesign
Type Of Installation	Indoor
Maximum Altitude	< 1000 m
Cooling Mode	AF (air forced)
Winding Material	Aluminium
Insulation Material	Cast resin (HV) Pre-impregnated (LV)
Degree Of Protection	IP31
Mounting Mode	Withdrawable Fixed

Complementary

Phase	3 phases
Rated Power	2000 kVA
Rated Frequency	60 Hz
Rated Primary Voltage	13.8 kV
Secondary Voltage (At No-Load)	No load: 419 V
Insulation Voltage To Industrial Frequency (50 Hz 1 Mn)	17.5 kV primary 1.1 kV secondary
Rated Insulation Level	Primary circuit: 38 kV AC Secondary circuit: 10 kV AC
Lighting Impulse Whistand Voltage (Bil) , 1.2/50 Ms	95 kV for primary circuit
Vector Group	Dyn11
Hv Tappings (Off Circuit)	+/- 2 x 2.5 %
Short Circuit Impedance	6 %
No-Load Losses	4500 W
Load Losses At 75°C/120 °C	16500 W at 120 °C
Temperature Rise Of Windings	90 K (winding)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Thermal Class	F
Sound Power Level	65 dB at 1 m
Protective Relay	PTC relay
Height	2200 mm
Width	1265 mm
Length	2195 mm
Total Weight	4455 kg

Environment

Ambient Air Temperature For Operation	-25...40 °C for C4
Ambient Air Temperature For Storage	-50...40 °C C4
Environmental Certification	0...95 % (E4)
Fire Certificate	F1
Standards	IEC 60076-11:2018
Corrosion Category	C3M

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Sustainability


Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.


Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Reach Free Of Svhc

 Rohs Exemption Information [Yes](#)

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive [Pro-active compliance \(Product out of EU RoHS legal scope\)](#)
[EU RoHS Declaration](#)

China Rohs Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information