Product data sheet

Specification





analog input module Modicon Quantum - 8 I multirange

140ACI03000C

- ! Discontinued on: Dec 31, 2021
- ! To be end-of-service on: Dec 31, 2029

! Discontinued - Service only

Main

Range Of Product	Modicon Quantum automation platform
Product Or Component Type	Analogue input module
Type Of Filter	Single pole low pass - 3 dB at 15 Hz +/- 20 %

Complementary

Analogue Input Number	8
Input Type	Differential
Addressing Requirement	9 input words
Analogue Input Resolution	12 bits
Linear Measuring Range	15 V 420 mA
Absolute Maximum Input	50 V DC 25 mA
Input Impedance	250 Ohm current +/- 0.01 % > 20 MOhm voltage
Absolute Accuracy Error	+/- 0.05 % of full scale +/- 0.1 % of full scale maximum
Linearity Error	+/- 0.04 %
Accuracy Drift According To Temperature	+/- 0.0025 % of full scale/°C <= 0.005 % of full scale/°C
Common Mode Rejection	> - 72 dB 60 Hz
Isolation Between Channels And Bus	1000 V DC 3000 V DC for 60 s
Isolation Between Channels	30 V DC
Update Time	5 ms
Fault Type	Broken wire 420 mA Undervoltage range 15 V
Marking	CE
Local Signalling	LED (green) for bus communication is present (Active) LED (red) for external fault LEDs (green) for channel is turned on LEDs (red) for channel fault
Bus Current Requirement	240 mA
Power Dissipation In W	2 W
Module Format	Standard

List Price displayed is VAT EXCLUSIVE.



Net Weight 0.3 kg

Environment

Protective Treatment	Conformal coating Humiseal 1A33
Standards	UL 508
	CSA C22.2 No 142
Product Certifications	FM Class 1 Division 2
	cUL
Resistance To Electrostatic	4 kV contact conforming to IEC 801-2
Discharge	8 kV on air conforming to IEC 801-2
Resistance To Electromagnetic Fields	10 V/m 801000 MHz conforming to IEC 801-3
Ambient Air Temperature For Operation	060 °C
Ambient Air Temperature For Storage	-4085 °C
Relative Humidity	95 % without condensation
Operating Altitude	<= 5000 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	16.5 cm
Package 1 Length	31.0 cm
Package 1 Weight	461.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	7
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.627 kg

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards


Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

140ACI03000C

Dimensions Drawings

Racks for Modules Mounting

Dimensions of Modules and Racks




- (1) 2 slots
- (2) 3 slots
- (3) 4 slots
- (4) 6 slots
- (5) 10 slots
- (6) 16 slots

140ACI03000C

Connections and Schema

Analog Input 8-Channel Unipolar Module

Wiring Diagram



N/C Not Connected

Apr 26, 2024

The maximum channel to channel working voltage cannot exceed 30 Vdc.