# Product data sheet

Specifications





## discrete output module Modicon Quantum - 32 O - 20..253 V AC

140DAO85300C

- () Discontinued on: Dec 31, 2021
- (!) To be end-of-service on: Dec 31, 2029

① Discontinued - Service only

### Main

Range Of Product	Modicon Quantum automation platform
Product Or Component Type	AC discrete output modules
Discrete Output Number	32

## Complementary

Group Of Channels	4 groups of 8 channels
Supply Frequency	4763 Hz
Maximum Voltage Drop	1.5 V
Discrete Output Voltage	20253 V AC
Addressing Requirement	2 output words
Absolute Maximum Output	300 Vrms for 10 s AC 400 Vrms 1 cycle AC
Maximum Load Current	16 A rms per module 4 A rms per group 0.88 mA 230 V off state leakage per output 1 A rms 20253 V per output
Surge Current	2.5 A during 1 ms
Dv/Dt	400 V/ms
Response Time	<= 0.5 ms at state 0 to state 1 <= 0.5 ms at state 1 to state 0
Protection Type	Internal output protection by 4 A fuse Internal by RC filter
Power Dissipation	1.60 + (1.0 V x total module load current)
Marking	CE
Local Signalling	1 LED (green) for bus communication is present (Active) 1 LED (red) for external fault detected (F) 32 LEDs (green) for input status
Bus Current Requirement	320 mA
Module Format	Standard
Net Weight	0.45 kg

### Environment

Protective Treatment	Conformal coating Humiseal 1A33
Product Certifications	cUL FM Class 1 Division 2

List Price displayed is VAT EXCLUSIVE.

Standards	UL 508 CSA C22.2 No 142
Electromagnetic Compatibility	Electrostatic discharge immunity test - test level: 4 kV (contact discharge) conforming to IEC 801-2 Electrostatic discharge immunity test - test level: 8 kV (air discharge) conforming to IEC 801-2 Susceptibility to electromagnetic fields - test level: 10 V/m (801000 MHz) conforming to IEC 801-3
Ambient Air Temperature For Operation	060 °C
Ambient Air Temperature For Storage	-4085 °C
Relative Humidity	95 % without condensation
Operating Altitude	<= 5000 m

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	16.0 cm
Package 1 Length	31.5 cm
Package 1 Weight	523.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	1
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	523.0 g

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

### Well-being performance

Reach Free Of Svhc

Mercury Free

Rohs Exemption Information Yes

### **Certifications & Standards**


Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

## Product data sheet

### **Dimensions Drawings**

### **Racks for Modules Mounting**

#### **Dimensions of Modules and Racks**




- (1) 2 slots
- (2) 3 slots
- (3) 4 slots
- (4) 6 slots
- (5) 10 slots
- (6) 16 slots

Connections and Schema

#### 24...230 Vac Discrete Output Module

#### Wiring Diagram



N/C Not Connected