# **Product datasheet**

Specification





# voltage transformer - 230..400 V - 1 x 115 V - 1600 VA

ABL6TS160G

#### Main

Range Of Product	Modicon Transformer Optimized			
Product Or Component Type	Safety and isolation transformer			
Rated Power In Va	1600 VA			
Input Voltage	230 V AC single phase, terminal(s): N-L1 400 V AC phase to phase, terminal(s): L1-L2			
Output Voltage	115 V AC			
Secondary Winding	Single			
Protective Cover	Without			
Ambient Air Temperature For Operation	-2050 °C			

#### **Complementary**

Complementary				
Input Voltage Limits	207253 V			
	360440 V			
Network Frequency Limits	4763 Hz			
Input Voltage Tolerance	+/- 15 V			
Efficiency	96 %			
Power Dissipation In W	66.7 W			
Output Sustained Overvoltage	2 % (no load, hot state)			
Maximum Voltage Drop At Rated Load	0.1 %			
No Load Losses	23.7 W			
Short-Circuit Voltage	0,0245			
Output Protection Type	Against overload, protection technology: with additional protection fuses or circuit- breakers in Selection of Protection Against overvoltage, protection technology: with additional protection fuses or circuit- breakers in Selection of Protection Against short-circuits, protection technology: with additional protection fuses or circuit-breakers in Selection of Protection			
Connections - Terminals	For input connection: screw type terminals, connection capacity: 5 x 4 mm² AWG 11 For input ground connection: screw type terminals, connection capacity: 1 x 4 mm² AWG 11 For output connection: screw type terminals, connection capacity: 2 x 4 mm² AWG 11			
	CE			
Fixing Mode	By 4 screws diameter: 7 mm on vertical panel, operating position: horizontal By 4 screws diameter: 7 mm on vertical panel, operating position: vertical By 4 screws diameter: 7 mm on horizontal panel with derating to 90 %			
Operating Altitude	3000 m			
Electrical Insulation Class	Class B			

Width	174.0 mm
Height	169.0 mm
Depth	163.0 mm
Net Weight	20.07 kg

## **Environment**

Product Certifications	UR EAC DNV-GL	
Standards	UL 506	
Ip Degree Of Protection	IP20	
<b>Environmental Characteristic</b>	EMC conforming to EN 62041 Safety conforming to EN 61558-1 Safety conforming to EN 61558-2-4	
Protective Treatment	TC	
Ambient Air Temperature For Storage	-4080 °C	
Overvoltage Category	Class I conforming to VDE 0106-1	
Dielectric Strength  2000 V between winding and ground 4000 V between primary and secondary		

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	30.400 cm
Package 1 Width	40.200 cm
Package 1 Length	40.200 cm
Package 1 Weight	21.566 kg
Unit Type Of Package 2	P06
Number Of Units In Package 2	4
Package 2 Height	75.000 cm
Package 2 Width	60.000 cm
Package 2 Length	80.000 cm
Package 2 Weight	92.876 kg

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

	Mercury Free	
	Rohs Exemption Information	Yes
<b>⊘</b>	Pvc Free	


#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations  Circularity Profile

## ABL6TS160G

#### **Dimensions Drawings**

#### **Dimensions**



#### Dimensions in mm

а	b	С	G	J	Ø
174	163	169	135	141	7

#### Dimensions in in.


а	b	С	G	J	Ø
6.85	6.42	6.65	5.31	5.55	0.27

# **Product datasheet**


## ABL6TS160G


#### Connections and Schema

#### Internal Scheme



#### Primary Voltage Wiring





#### **Secondary Voltage Wiring**

