

Product datasheet

Specifications



KNX ARGUS Presence 180/2.20 m flush-mounted, anthracite, System Design

MTN6302-6034

Main

Range	KNX
Aesthetic Name	System Design D-Life
Product Or Component Type	Presence detector
Bus Type	KNX
Colour Tint	Anthracite

Complementary

Device Presentation	Mechanism with central plate
Number Of Channels	5
Protection Type	Creep zone protection
Type Of Setting	Light sensitivity adjustable
Duty Cycle	15300 minutes
Time Delay Range	0...1 s (switch-on)
Detection Face	Lateral: 8 m
Detection Angle	180° horizontal
Material	Polycarbonate
Surface Treatment	Varnished
Device Mounting	Flush
Mounting Height	2.2 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.700 cm
Package 1 Width	7.700 cm
Package 1 Length	9.300 cm
Package 1 Weight	98.000 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	30
Package 2 Height	20.500 cm
Package 2 Width	30.400 cm

Package 2 Length	40.900 cm
-------------------------	-----------

Package 2 Weight	3.312 kg
-------------------------	----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant
[EU RoHS Declaration](#)

China Rohs Regulation [China RoHS declaration](#)
Pro-active China RoHS declaration (out of China RoHS legal scope)

Weee The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
