Specifications





Editable voice alarms, Harmony XVS, white, mounting 96mm DIN rail, NPN, 100...230V AC

XVSV9MWN

Main

Range Of Product	Harmony XVS
Product Or Component Type	Editable electronic alarm
Beacon Or Indicator Bank Unit Type	Sound unit
Device Short Name	XVSV

Complementary

Complementary	
Colour	White
Input Type	Bit: 6 channel input Binary: 63 channel input
Assembly Style	Ready assembled
Material	PC (polycarbonate): body PC (polycarbonate): back cover TPE (thermoplastic elastomer): front panel NBR (nitrile butadiene rubber)
Marking	CE
Overvoltage Category	Class II conforming to IEC 61140
Mounting Support	96 mm DIN rail
[Us] Rated Supply Voltage	100230 V AC
[Ue] Rated Operational Voltage	90264 V AC
[Ui] Rated Insulation Voltage	250 V
Inrush Current	30 A
Associated Fuse Rating	1 A
[Uimp] Rated Impulse Withstand Voltage	2.5 kV conforming to IEC 60947-1
Power Consumption In W	10 W
Current Consumption	100 mA at 100 V AC
Clamping Connection Capacity	<= 1 x 1.5 mm ²
Device Application	Packaging Subway Printing
Mounting Diameter	105 mm
Width	105 mm
Height	105 mm
Depth	50.1 mm
Net Weight	0.287 kg

Environment

Discrete Output Type	NPN
Signalling Type	Adjustable vocal sound
Standards	IEC 60947-5-1
Protective Treatment	TC
Ambient Air Temperature For Storage	-2060 °C
Ambient Air Temperature For Operation	050 °C
Pollution Degree	2
Relative Humidity	3585 % without condensation
Vibration Resistance	7 gn
Ip Degree Of Protection	Panel mounted: IP65 conforming to IEC 60529 Wall mounted: IP20
Noise Level	097 dB (stop or suppress) at 1 m

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.5 cm
Package 1 Width	5 cm
Package 1 Length	10.5 cm
Package 1 Weight	287 g

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free


Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	End of Life Information	

Dimensions Drawings

Dimensions




(t): Waterproof rubber (1.6 mm / 0.06 in.)

4

Mounting and Clearance


Panel Cut Dimensions



(1) Installation panel

A	В	С
92 +0.6/0 mm (3.62 +0.0236/0 in.)	92 +0.6/0 mm (3.62 +0.0236/0 in.)	14 mm (0.040.15 in.)


Wall Mount Dimensions



(1) Installation panel

Connections and Schema

Wiring Diagram



- (1) Green
- (2) Yellow
- (3) Brown
- (4) Blue
- (5) Purple
- (6) Gray
- (7) White
- (8) Black
- (9) Red
- (10) Fuse (Rated current:1 A)