Product datasheet

Specification





Reflex iC60N Ti24 63 A 4P curve C integrated control MCB

A9C62463

Main

Device Application	Distribution Control	
Range	Acti9	
Product Name	Reflex iC60	
Device Short Name	Reflex iC60N	
Product Or Component Type	Integrated control circuit breaker	
Poles Description	4P	
Number Of Protected Poles	4	
Network Type	AC	
Trip Unit Technology	Thermal-magnetic	
Curve Code	С	

Complementary

[In] Rated Current	63 A
Network Frequency	50/60 Hz
Breaking Capacity Code	N
Breaking Capacity	20 kA lcu at 220240 V AC 50/60 Hz conforming to EN/IEC 60947-2 10 kA lcu at 380415 V AC 50/60 Hz conforming to EN/IEC 60947-2
[Ui] Rated Insulation Voltage	500 V AC
Contact Position Indicator	Yes
Control Type	Remote control by pulse Toggle Remote control by continuous command ON/OFF button
Control Signal Type	Impulse Maintained Maintained very low voltage
Local Signalling	Red LED: fault Green LED: device ON Flashing LED: device tripped Flashing LED: device overheat Flashing LED: device ready
[Uc] Control Circuit Voltage	230 V AC 50/60 Hz 24 V AC 50/60 Hz 48 V AC 50/60 Hz 24 V DC 48 V DC
[Us] Rated Supply Voltage	230 V AC at 50/60 Hz
Mounting Mode	Fixed

Mounting Support	35 mm symmetrical DIN rail
9 Mm Pitches	13
Height	84 mm
Width	117 mm
Depth	77 mm
Colour	White
Mechanical Durability	50000 cycles
Electrical Durability	AC-1: 50000 cycles AC 50 Hz
Provision For Padlocking	Padlockable
Locking Options Description	Padlock in OFF position
Earth-Leakage Protection	Separate block
Product Compatibility	With PLC

Environment

Ip Degree Of Protection	IP20 conforming to IEC 60529
Pollution Degree	3
Tropicalisation	2
Relative Humidity	93 % at 40 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.0 cm
Package 1 Width	11.2 cm
Package 1 Length	16.5 cm
Package 1 Weight	898.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	14
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	13.098 kg

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information