Product datasheet

Specification





iPRD20r modular surge arrester - 1P + N - 350V - with remote transfert

A9L20501

Main

Range Of Product	Acti9
Product Name	Acti9 iPRD
Product Or Component Type	Surge arrester with pluggable cartridge
Device Short Name	iPRD20r
Device Application	Distribution
Standards	EN 61643-11:2012 IEC 61643-11:2011
Product Certifications	CE
Quality Labels	KEMA-KEUR NF
Poles Description	1P + N
Remote Signalling	With
Signal Contacts Composition	1 SD (1 C/O)
Surge Arrester Type	Electrical distribution network
Earthing System	TN-S TT

Complementary

Surge Arrester Class Type	Type 2
Surge Arrester Technology	MOV + GDT
[Ue] Rated Operational Voltage	230/400 V AC (+/- 10 %) at 50/60 Hz
[In] Nominal Discharge Current	Common mode: 5 kA (L/PE) Common mode: 5 kA (N/PE) Differential mode: 5 kA (L/N)
[Imax] Maximum Discharge Current	Common mode: 20 kA L/PE Common mode: 20 kA N/PE Differential mode: 20 kA L/N
[Uc] Maximum Continuous Operating Voltage	Common mode: 260 V N/PE Common mode: 350 V L/PE Differential mode: 350 V L/N
Maximum [Up] Voltage Protection Level	Differential mode <1.1 kV type 2 L/N Common mode <1.4 kV type 2 N/PE
[Ut] Temporary Overvoltage	337 V L/N 5 s withstand 1200 V N/PE 200 ms safe failure mode 442 V L/PE 5 s withstand 1453 V L/PE 200 ms safe failure mode

Disconnector Device Tur-	A
Disconnector Device Type	Associated circuit breaker IC60N 20 A curve C - Icu 10 kA
	Associated circuit breaker iC60H 20 A curve C - Icu 15 kA
	Associated circuit breaker iC60L 20 A curve C - Icu 25 kA
	Associated circuit breaker NG125H 20 A curve C - Icu 36 kA
	Associated circuit breaker NG125L 20 A curve C - Icu 50 kA
	Associated fuse gG 40 A - Icu 15 kA
	Associated fuse gG 80 A - Icu 50 kA
Signalling Circuit Voltage	0.25 A/250 V AC 50/60 Hz
Mounting Mode	Clip-on (DIN rail)
9 Mm Pitches	4
Height	85 mm
Width	36 mm
Depth	69 mm
Net Weight	0.215 kg
Colour	White (RAL 9003)
[Ipe] Ground Residual Current	0.003 mA
	0.6 mA
Connections - Terminals	Tunnel type terminal (downside) 2.535 mm²
	Tunnel type terminal (upside) 2.535 mm ²
Tightening Torque	2.5 N.m

Environment

Ik Degree Of Protection	IK03 conforming to IEC 62262
Relative Humidity	595 %
Operating Altitude	2000 m
Ambient Air Temperature For Operation	-2560 °C
Ambient Air Temperature For	-4085 °C

Packing Units

PCE
1
4.3 cm
7.2 cm
9.2 cm
243 g
BB1
6
8.3 cm
9.9 cm
27.6 cm
1.522 kg
\$03
54
30 cm
30 cm

Package 3 Length	40 cm
Package 3 Weight	14.223 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

✓ R

Reach Free Of Svhc



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information