

# Product datasheet

Specifications



variable speed drive, Easy Altivar  
610, 75kW, 100hp, 380 to 460V,  
IP20

ATV610D75N4

## Main

|                                    |  |
|------------------------------------|--|
| Range Of Product                   | Easy Altivar 610   |
| Product Or Component Type          | Variable speed drive   |
| Product Specific Application       | Fan, pump, compressor, conveyor  |
| Device Short Name                  | ATV610   |
| Variant                            | Standard version   |
| Product Destination                | Asynchronous motors<br>Synchronous motors  |
| Mounting Mode                      | Cabinet mount  |
| Emc Filter                         | Integrated conforming to IEC 61800-3 category C3 with 50 m   |
| Ip Degree Of Protection            | IP20   |
| Type Of Cooling                    | Forced convection  |
| Supply Frequency                   | 50...60 Hz +/-5 %  |
| Network Number Of Phases           | 3 phases   |
| [Us] Rated Supply Voltage          | 380...460 V - 15...10 %  |
| Motor Power Kw                     | 75 kW for normal duty<br>55 kW for heavy duty  |
| Motor Power Hp                     | 100 hp for normal duty<br>75 hp for heavy duty   |
| Line Current                       | 147.9 A at 380 V (normal duty)<br>130.2 A at 460 V (normal duty)<br>115.8 A at 380 V (heavy duty)<br>101.7 A at 460 V (heavy duty) |
| Prospective Line Isc               | 22 kA  |
| Apparent Power                     | 103.7 kVA at 460 V (normal duty)<br>81.0 kVA at 460 V (heavy duty)   |
| Continuous Output Current          | 145 A at 2.5 kHz for normal duty<br>106 A at 2.5 kHz for heavy duty  |
| Maximum Transient Current          | 160 A during 60 s (normal duty)<br>159 A during 60 s (heavy duty)  |
| Asynchronous Motor Control Profile | Constant torque standard<br>Optimized torque mode<br>Variable torque standard  |
| Output Frequency                   | 0.1...500 Hz   |
| Nominal Switching Frequency        | 2.5 kHz  |
| Switching Frequency                | 1...8 kHz adjustable   |
| Number Of Preset Speeds            | 16 preset speeds   |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                                     |  |
|-------------------------------------|--|
| Communication Port Protocol         | Modbus serial  |
| Option Card                         | Slot A: communication card, Profibus DP V1<br>Slot A: digital or analog I/O extension card<br>Slot A: relay output card  |
| <h2>Complementary</h2>              |  |
| Output Voltage                      | <= power supply voltage  |
| Motor Slip Compensation             | Automatic whatever the load<br>Can be suppressed<br>Adjustable<br>Not available in permanent magnet motor law  |
| Acceleration And Deceleration Ramps | S, U or customized<br>Linear adjustable separately from 0.01 to 9000 s   |
| Braking To Standstill               | By DC injection  |
| Protection Type                     | Thermal protection: motor<br>Motor phase break: motor<br>Thermal protection: drive<br>Overheating: drive<br>Overcurrent between output phases and earth: drive<br>Overload of output voltage: drive<br>Short-circuit protection: drive<br>Motor phase break: drive<br>Overvoltages on the DC bus: drive<br>Line supply overvoltage: drive<br>Line supply undervoltage: drive<br>Line supply phase loss: drive<br>Overspeed: drive<br>Break on the control circuit: drive |
| Frequency Resolution                | Display unit: 0.1 Hz<br>Analog input: 0.012/50 Hz  |
| Electrical Connection               | Control, screw terminal: 0.5...1.5 mm²<br>Line side, screw terminal: 95...120 mm²<br>Motor, screw terminal: 95...120 mm²   |
| Connector Type                      | 1 RJ45 (on the remote graphic terminal) for Modbus serial  |
| Physical Interface                  | 2-wire RS 485 for Modbus serial  |
| Transmission Frame                  | RTU for Modbus serial  |
| Transmission Rate                   | 4.8, 9.6, 19.2, 38.4 kbit/s for Modbus serial  |
| Type Of Polarization                | No impedance for Modbus serial   |
| Number Of Addresses                 | 1...247 for Modbus serial  |
| Method Of Access                    | Slave  |
| Supply                              | External supply for digital inputs: 24 V DC (19...30 V), <1.25 mA, protection type: overload and short-circuit protection<br>Internal supply for reference potentiometer (1 to 10 kOhm): 10.5 V DC +/- 5 %, <10 mA, protection type: overload and short-circuit protection   |
| Local Signalling                    | 2 LEDs for local diagnostic<br>1 LED (yellow) for embedded communication status<br>2 LEDs (dual colour) for communication module status<br>1 LED (red) for presence of voltage   |
| Width                               | 290 mm   |
| Height                              | 762 mm<br>922 mm with EMC plate  |
| Depth                               | 323 mm   |
| Net Weight                          | 53 kg  |
| Analogue Input Number               | 3  |

|                           |  |
|---------------------------|--|
| Analogue Input Type       | AI1, AI2, AI3 software-configurable voltage: 0...10 V DC, impedance: 30 kOhm, resolution 12 bits<br>AI1, AI2, AI3 software-configurable current: 0...20 mA, impedance: 250 Ohm, resolution 12 bits<br>AI2, AI3 software-configurable temperature probe or water level sensor   |
| Discrete Input Number     | 6  |
| Discrete Input Type       | DI1...DI6 programmable as logic input, 24 V DC ( $\leq 30$ V), impedance: 3.5 kOhm<br>DI5, DI6 programmable as pulse input: 0...30 kHz, 24 V DC ( $\leq 30$ V)   |
| Input Compatibility       | DI1...DI6: logic input level 1 PLC conforming to IEC 61131-2<br>DI5, DI6: pulse input level 1 PLC conforming to IEC 65A-68   |
| Discrete Input Logic      | Positive logic (source): DI1...DI6 configurable logic input, $< 5$ V (state 0), $> 11$ V (state 1)<br>Negative logic (sink): DI1...DI6 configurable logic input, $> 16$ V (state 0), $< 10$ V (state 1)<br>Positive logic (source): DI5, DI6 configurable pulse input, $< 0.6$ V (state 0), $> 2.5$ V (state 1)  |
| Analogue Output Number    | 2  |
| Analogue Output Type      | Software-configurable current AQ1, AQ2: 0...20 mA, resolution 10 bits<br>Software-configurable voltage AQ1, AQ2: 0...10 V DC impedance 470 Ohm, resolution 10 bits   |
| Sampling Duration         | 5 ms $\pm$ 0.1 ms (AI1, AI2, AI3) - analog input<br>2 ms $\pm$ 0.5 ms (DI1...DI6)configurable - discrete input<br>5 ms $\pm$ 1 ms (DI5, DI6)configurable - pulse input<br>10 ms $\pm$ 1 ms (AQ1, AQ2) - analog output  |
| Accuracy                  | $\pm$ 0.6 % AI1, AI2, AI3 for a temperature variation 60 °C analog input<br>$\pm$ 1 % AQ1, AQ2 for a temperature variation 60 °C analog output   |
| Linearity Error           | AI1, AI2, AI3: $\pm$ 0.15 % of maximum value for analog input<br>AQ1, AQ2: $\pm$ 0.2 % for analog output   |
| Relay Output Number       | 3  |
| Relay Output Type         | Configurable relay logic R1: fault relay NO/NC electrical durability 100000 cycles<br>Configurable relay logic R2: sequence relay NO electrical durability 100000 cycles<br>Configurable relay logic R3: sequence relay NO electrical durability 100000 cycles   |
| Refresh Time              | Relay output (R1, R2, R3): 5 ms ( $\pm$ 0.5 ms)  |
| Minimum Switching Current | Relay output R1, R2, R3: 5 mA at 24 V DC   |
| Maximum Switching Current | Relay output R1, R2, R3 on resistive load, $\cos \phi = 1$ : 3 A at 250 V AC<br>Relay output R1, R2, R3 on resistive load, $\cos \phi = 1$ : 3 A at 30 V DC<br>Relay output R1, R2, R3 on inductive load, $\cos \phi = 0.4$ and L/R = 7 ms: 2 A at 250 V AC<br>Relay output R1, R2, R3 on inductive load, $\cos \phi = 0.4$ and L/R = 7 ms: 2 A at 30 V DC |
| Isolation                 | Between power and control terminals  |
| Insulation Resistance     | $> 1$ MOhm 500 V DC for 1 minute to earth  |

## Environment

|                               |  |
|-------------------------------|--|
| Noise Level                   | 78 dB conforming to 86/188/EEC   |
| Power Dissipation In W        | 1460 W(forced convection) at 380 V, switching frequency 2.5 kHz<br>177 W(natural convection) at 380 V, switching frequency 2.5 kHz   |
| Volume Of Cooling Air         | 295 m <sup>3</sup> /h  |
| Operating Position            | Vertical $\pm$ 10 degree   |
| Electromagnetic Compatibility | Electrostatic discharge immunity test level 3 conforming to IEC 61000-4-2<br>Radiated radio-frequency electromagnetic field immunity test level 3 conforming to IEC 61000-4-3<br>Electrical fast transient/burst immunity test level 4 conforming to IEC 61000-4-4<br>1.2/50 $\mu$ s - 8/20 $\mu$ s surge immunity test level 3 conforming to IEC 61000-4-5<br>Conducted radio-frequency immunity test level 3 conforming to IEC 61000-4-6 |
| Pollution Degree              | 2 conforming to IEC 61800-5-1  |

|                                       |  |
|---------------------------------------|--|
| Vibration Resistance                  | 1.5 mm peak to peak (f= 2...13 Hz) conforming to IEC 60068-2-6<br>1 gn (f= 13...200 Hz) conforming to IEC 60068-2-6                    |
| Shock Resistance                      | 15 gn for 11 ms conforming to IEC 60068-2-27   |
| Relative Humidity                     | 5...95 % without condensation conforming to IEC 60068-2-3  |
| Ambient Air Temperature For Operation | -15...45 °C (without derating)<br>45...60 °C (with derating factor)  |
| Ambient Air Temperature For Storage   | -40...70 °C  |
| Operating Altitude                    | <= 1000 m without derating<br>1000...4800 m with current derating 1 % per 100 m  |
| Environmental Characteristic          | Chemical pollution resistance class 3C3 conforming to IEC 60721-3-3<br>Dust pollution resistance class 3S3 conforming to IEC 60721-3-3 |
| Standards                             | IEC 61800-3<br>Environment 2 category C3 IEC 61800-3<br>IEC 61800-5-1<br>IEC 60721-3   |
| Marking                               | CE   |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type Of Package 1       | PCE       |
| Number Of Units In Package 1 | 1         |
| Package 1 Height             | 46.500 cm |
| Package 1 Width              | 58.000 cm |
| Package 1 Length             | 93.500 cm |
| Package 1 Weight             | 70.500 kg |

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

Resource performance

✓ Upgradeable Through Digital Modules  
And Upgraded Components

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   Yes


Certifications & Standards

|                          |   |
|--------------------------|---|
| Reach Regulation         | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)  |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a>  |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Weee                     | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile      | <a href="#">End of Life Information</a>   |

Dimensions Drawings


Dimensions

IP20 Drives



Drawings from left to right: rear view, right side view with top cover, right side view without top cover.


IP20 Drives With EMC Plate



Drawings from left to right: rear view, right side view with top cover.

Mounting and Clearance

Clearances




| X1                  | X2                  | X3                 |
|---------------------|---------------------|--------------------|
| ≥ 100 mm (3.94 in.) | ≥ 100 mm (3.94 in.) | ≥ 10 mm (0.39 in.) |

- Mount the device in a vertical position ( $\pm 10^\circ$ ). This is required for cooling the device.
- Do not mount the device close to heat sources.
- Leave sufficient free space so that the air required for cooling purposes can circulate from the bottom to the top of the drive.

Mounting Types


---

Mounting Type A: Individual IP21




$a \geq 110 \text{ mm (4.33 in.)}$

Mounting Type B: Side by Side IP20 (Possible, 2 Drives Only)




Mounting Type C: Individual IP20



$a \geq 110 \text{ mm (4.33 in.)}$


Connections and Schema

Single or Three-phase Power Supply - Diagram With Line Contactor



- (1) Line chokes
- (2) See control block wiring diagram
- A1 : Drive
- KM1 : Line Contactor
- Q2, Q3 : Circuit breakers
- S1, S2 : Pushbuttons
- T1 : Transformer for control part


Control Block Wiring Diagram



- (1) Digital Input
- (2) Analog Output
- (3) Analog Input
- R1A, R1B, R1C : Fault relay output
- R2A, R2C : Sequence relay output
- R3A, R3C : Sequence relay output


Sensor Connection

It is possible to connect either 1 or 3 sensors on terminals AI2 or AI3.



Performance Curves

Derating Curves



**In** : Nominal Drive Current  
**SF** : Switching Frequency