



# servo motor BMI 3-phase untapped IP54 single turn - 32768 p/t - brake

BMI1003P06F

Discontinued on: May 6, 2023 AD

! Discontinued

# Main

Range Compatibility	Lexium 32i	
Product Or Component Type	Servo motor with power stage	
Device Short Name	BMI	

# Complementary

Maximum Mechanical Speed	6000 rpm
[Us] Rated Supply Voltage	208480 V - 1510 %
Supply Voltage Limits	208480 V
Network Number Of Phases	Three phase
Supply Frequency	50/60 Hz - 55 %
Network Frequency Limits	47.563 Hz
Emc Filter	Integrated
Continuous Output Current	4 A at 8 kHz
Output Current 3S Peak	12 A at 400 V for 3 s
Continuous Stall Current	4 A
Continuous Stall Torque	8.5 N.m at 208480 V three phase
Peak Stall Torque	19.2 N.m at 400 V three phase 19.2 N.m at 480 V three phase 19.2 N.m at 208 V three phase
Nominal Output Power	1000 W at 208 V three phase 2000 W at 400 V three phase 2100 W at 480 V three phase
Nominal Torque	7.2 N.m at 208 V three phase 6.8 N.m at 400 V three phase 5.6 N.m at 480 V three phase
Nominal Speed	1500 rpm at 208 V three phase 3000 rpm at 400 V three phase 3700 rpm at 480 V three phase
Maximum Current Irms	26.7 A at 208 V, three phase 26.7 A at 400 V, three phase 26.7 A at 480 V, three phase
Product Compatibility	Drive control unit LXM32i CANopen Drive control unit LXM32i EtherCAT
Shaft End	Untapped
Second Shaft	Without second shaft end
Shaft Diameter	19 mm

Shaft Length	40 mm
Feedback Type	Absolute single turn SinCos Hiperface
Speed Feedback Resolution	32768 points/turn
Holding Brake	With
Holding Torque	9 N.m holding brake
Mounting Support	International standard flange
Motor Flange Size	100 mm
Electrical Connection	Printed circuit board connector
Torque Constant	1.7 N.m/A at 20 °C
Back Emf Constant	112 V/krpm at 20 °C
Number Of Motor Poles	10
Rotor Inertia	10.3 kg.cm²
Stator Resistance	2.31 Ohm at 20 °C
Stator Inductance	11.43 mH at 20 °C
Stator Electrical Time Constant	4.95 ms at 20 °C
Maximum Radial Force Fr	1050 N at 1000 rpm 830 N at 2000 rpm 730 N at 3000 rpm 660 N at 4000 rpm 610 N at 5000 rpm
Maximum Axial Force Fa	0.2 x Fr
Brake Pull-In Power	8 W
Type Of Cooling	Natural convection
Length	338 mm
Number Of Motor Stacks	3
Centring Collar Diameter	95 mm
Centring Collar Depth	3.5 mm
Number Of Mounting Holes	4
Mounting Holes Diameter	9 mm
Circle Diameter Of The Mounting Holes	115 mm
Distance Shaft Shoulder-Flange	3.5 mm

# **Environment**

Ip Degree Of Protection Shaft: IP54
Housing: IP65

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	25.8 cm
Package 1 Width	20.0 cm
Package 1 Length	59.0 cm
Package 1 Weight	11.0 kg

Unit Type Of Package 2	P06
Number Of Units In Package 2	8
Package 2 Height	77.0 cm
Package 2 Width	80.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	96.5 kg

# **Contractual warranty**

Apr 19, 2024 AD

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

# Well-being performance

<b>Ø</b>	Mercury Free	
	Rohs Exemption Information	Yes
<b>②</b>	Pvc Free	


# **Certifications & Standards**

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	China RoHS declaration	
<b>Environmental Disclosure</b>	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
Circularity Profile	End of Life Information	

# **Dimensions Drawings**

### **External Dimensions**

# With Standard Braking Resistor



- (1) Module for supply voltage
- (2) I/O module
- (3) Standard braking resistor


#### Dimensions in mm

Difficitions in fillin		
W	Н	L
132,6	217	367

#### Dimensions in in

Difficitions in in.		
W	Н	L
5,22	8,54	14,45

#### Mounting type B



- (1) Module for supply voltage
- (2) I/O module

# BMI1003P06F

### (3) Standard braking resistor


Dimensions in mm	

W	Н	L
132,6	168	416

#### Dimensions in in.

W	Н	L
5,22	6,61	16,38

# With External Braking Resistor



- (1) Module for supply voltage
- (2) I/O module
- (4) External braking resistor

#### Dimensions in mm


W	Н	L
132,6	217	379

Dimensions in in.

	D					
W	Н	L				
5,22	8,54	14,92				

# Mounting type D

# BMI1003P06F




- (1) Module for supply voltage
- (2) I/O module
- (4) External braking resistor

#### Dimensions in mm

W	Н	L
132,6	180	416

#### Dimensions in in.

D					
W	Н	L			
5,22	7,09	16,38			



- (1) Module for supply voltage
- (2) I/O module
- (4) External braking resistor

### Dimensions in mm


W	Н	L
132,6	217	406

# BMI1003P06F

Dimensions in in.

W	Н	L
5,22	8,54	15,98

### Mounting type F



- (1) Module for supply voltage
- (2) I/O module
- (4) External braking resistor

#### Dimensions in mm

Difficitations in thirt					
W	Н	L			
132,6	206,5	416			

### Dimensions in in.


W	Н	L
5,22	8,13	16,38

# BMI1003P06F

### Performance Curves

# **Performance Curves**

# Torque/Speed Curves with 208 V Three Phases Supply Voltage




- (X) Speed (rpm)
- (Y) Torque (N.m)
- (1) Motor peak
- (2) Drive peak
- (3) Drive cont
- (4) Motor cont
- (5) Operating point

		Power	At Speed	With Torque
max. Peak Power		2675 W	1380 rpm	18.51 N.m
max Cont. Power (Drive)	•	1223 W	1620 rpm	7.21 N.m

# **Performance Curves**

### Torque/Speed Curves with 400 V Three Phases Supply Voltage




- (X) Speed (rpm)
- (Y) Torque (N.m)
- (1) Motor peak
- (2) Drive peak
- (3) Drive cont
- (4) Motor cont
- (5) Operating point

		Power	At Speed	With Torque
max. Peak Power		5328 W	2760 rpm	18.44 N.m
max Cont. Power (Drive)	•	2096 W	3240 rpm	6.18 N.m

# **Performance Curves**

### Torque/Speed Curves with 480 V Three Phases Supply Voltage



- (X) Speed (rpm)
- (Y) Torque (N.m)
- (1) Motor peak
- (2) Drive peak
- (3) Drive cont
- (4) Motor cont
- (5) Operating point

		Power	At Speed	With Torque
max. Peak Power		6454 W	3360 rpm	18.34 N.m
max Cont. Power (Drive)	•	1994 W	3960 rpm	4.81 N.m