

Lista sa podacima o proizvodima

Specifikacije



upravljačka stanica XAC-A sa rukohvatom - 2 tastera

XACA205

Cena* bez PDV-a: 12.437,00 RSD

Osnovne informacije

Grupa Proizvoda	Harmony XAC
Tip Proizvoda Ili Komponente	Upravljačka stanica
Kratko Ime Uređaja	XACA konzola

Dopunske informacije

Upotreba Upravljačke Stanice	Dvostruko izolovana
Materijal Kućišta	Polipropilen
Tip Upravljanja	Intuitivno
Tip Električnog Kola	Upravljačko kolo
Tip Ormana	Kompletno spreman za korišćenje
Upotreba Upravljačke Stanice	Upravljanje jednobrzinskim motorom dizalice
Sastav Upravljačke Stanice	2 tastera
Tip Upravljačkog Tastera	Prvi taster 1 NC + 1 NO dizanje, sporo Drugi taster 1 NC + 1 NO naniže, sporo
Kompatibilnost Proizvoda	ZB2BE102 + ZB2BE101 za svaki smer
Mehanička Blokada	Sa mehaničkom blokadom
Boja Upravljačke Stanice	Žuta
Povezivanje - Priklučci	Vijčani priključni blokovi, 1 x 2.5 mm ² sa ili bez kablovskog završetka Vijčani priključni blokovi, 2 x 1.5 mm ² sa ili bez kablovskog završetka
Standardi	UL 508 EN/IEC 60947-5-1 CSA C22.2 No 14 EN/IEC 60204-32
Sertifikacija Proizvoda	UL CSA
Tretman Zaštite	TH
Temperatura Okoline Za Rad Uređaja	-25...70 °C
Temperatura Okoline Za Skladištenje	-40...70 °C
Otpornost Na Vibracije	15 gn (f= 10...500 Hz) u skladu sa IEC 60068-2-6
Otpornost Na Udare	100 gn u skladu sa IEC 60068-2-27
Kategorija Prenapona	Klasa II u skladu sa IEC 61140
Ip Stepen Zaštite	IP65 u skladu sa IEC 60529
Ik Stepen Zaštite	IK08 conforming to EN 50102

Mehanička Trajnost 1000000 ciklusa
Sve cene koje su navedene u ovom cenovniku su informativne i neobavezujuće, bez PDV-a, isključivo u odnosu na ovlašćene distributere kompanije Schneider Electric. Svi prikazi, opisi i tehničke specifikacije i podaci u ovom cenovniku su podložni promenama od strane kompanije Schneider Electric bez prethodne najave.

Odricanje odgovornosti: Ova dokumentacija nije namenjena kao zamena i ne treba je koristiti za utvrđivanje podobnosti ili pouzdanosti ovih proizvoda za određene namene

Kablovski Uvod	Gumena kablovska spojnica sa stepenastim uvodom 7...15 mm
Označavanje Koda Kontakta	A600 AC-15, Ue = 240 V, Ie = 3 A u skladu sa IEC 60947-5-1 dodatak A A600 AC-15, Ue = 600 V, Ie = 1,2 A u skladu sa IEC 60947-5-1 dodatak A Q600 DC-13, Ue = 250 V, Ie = 0,27 A u skladu sa IEC 60947-5-1 dodatak A Q600 DC-13, Ue = 600 V, Ie = 0,1 A u skladu sa IEC 60947-5-1 dodatak A
[Ithe] Dozvoljena Termička Struja U Ormanu	10 A
[UI] Nazivni Napon Izolacije	600 V (stepen zaprljanosti 3) u skladu sa IEC 60947-1
[Uimp] Nazivni Podnosivi Impulsni Napon	6 kV u skladu sa IEC 60947-1
Operacija Kontakata	Sporo isključenje
Maksimalna Otpornost Kroz Priključke	25 MΩ
Sila U Radu	13...15 N
Zaštita Od Kratkog Spoja	10 A zaštitni osigurač sa rastavni uložak osigurač tip gG
Nazivna Snaga U W	40 W DC-13 za 1000000 ciklusa, broj operacija <60 ciklusa/min pri 120 V, faktor opterećenja = 0,5 (induktivno opterećenje) u skladu sa IEC 60947-5-1 dodatak C 48 W DC-13 za 1000000 ciklusa, broj operacija <60 ciklusa/min pri 48 V, faktor opterećenja = 0,5 (induktivno opterećenje) u skladu sa IEC 60947-5-1 dodatak C 65 W DC-13 za 1000000 ciklusa, broj operacija <60 ciklusa/min pri 24 V, faktor opterećenja = 0,5 (induktivno opterećenje) u skladu sa IEC 60947-5-1 dodatak C
Opis Priključaka Iso N°1	(11-12)NC (13-14)NO
Oznaka Priključaka	(11-12)NC (13-14)NO
Masa Proizvoda	0,3 kg

Pakovanje

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6,300 cm
Package 1 Width	9,600 cm
Package 1 Length	29,100 cm
Package 1 Weight	282,000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	15
Package 2 Height	30,000 cm
Package 2 Width	30,000 cm
Package 2 Length	40,000 cm
Package 2 Weight	4,718 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	120
Package 3 Height	75,000 cm
Package 3 Width	60,000 cm
Package 3 Length	80,000 cm
Package 3 Weight	48,404 kg

Ugovorna garancija

Garancija	18 meseci
-----------	-----------

Održivost

Oznaka **Green Premium™** je posvećenost kompanije Schneider Electric isporuci proizvoda sa ekološkim performansama najboljim u klasi. Green Premium obećava usaglašenost sa najnovijim propisima, transparentnost u pogledu uticaja na životnu sredinu, kao i sa cirkularnim i niskonaponskim CO₂ proizvodima.

Vodič za procenu održivosti proizvoda je bela knjiga koja razjašnjava globalne standarde za oznaku ekološke prihvatljivosti i način tumačenja ekoloških izjava.

[Saznajte više o oznaci Green Premium >](#)

[Vodič za procenu održivosti proizvoda >](#)



Prozirnost



RoHS/REACH


Performanse dobrobiti

✓ Reach Bez Svhc	
✓ Bez Toksičnih Teških Metala	
✓ Bez Žive	
✓ Informacije O Rohs Izuzecima	Da

Sertifikacija i standardi


Propis Reach	REACH deklaracija
Eu Rohs Direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS) EU RoHS deklaracija
Rohs Regulativa Za Kinu	RoHS deklaracija za Kinu
Izjava O Zaštiti Okoliša	Profil ekološke prihvatljivosti proizvoda
Weee	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.
Profil Cirkularnosti	Nema potrebe za namenskim operacijama recikliranja

Dimensions



(1) Internal Ø

Control of Single-Speed Reversing Motor




Performance Curves

Rated Operational Power

AC Supply 50/60 Hz Inductive Circuit

Operating rate: 3600 operating cycles/hour. Load factor: 0.5.

Millions of operating cycles, AC-15 utilization category



I_{the} Thermal current

(A) Current

DC Supply

Operating rate: 3600 operating cycles/hour. Load factor: 0.5.

Power broken in W for 1 million operating cycles, DC-13 utilization category

Voltage	V	24	48	120
Inductive circuit	W	65	48	40