


Lista sa podacima o proizvodima

Specifikacije



zeleni taster Ø 22 pečurkasta
glava Ø 401 NO-ATEX

XB4BC31EX

Osnovne informacije

Grupa Proizvoda	Harmony XB4
Tip Proizvoda Ili Komponente	Kompletni taster
Kratko Ime Uređaja	XB4
Materijal Podnožja	Hromirani metal
Materijal Montažnog Rama	Zamak
Tip Glave	Standardni
Prečnik Za Montiranje	22 mm
Prodaja Po Nedeljivim Količinama	1
Zona Prašine	Zona 21 - 22
Tip Glave Uređaja	sa povratkom
Profil Glave Uređaja	Zelena pečurkasti taster Ø 40 mm
Tip Kontakata I Sastav	1 NO

Dopunske informacije

Otpornost Na Uređaj Za Pranje Pod Pritiskom	7000000 Pa pri 55 °C, razdaljina : 0.1 m
Montaža Uređaja	Otvor za montažu - prečnik: 22,5 mm 22.3 +0.4/0 u skladu sa IEC 60947-1
Centar Za Fiksiranje	>= 30 x 40 mm (nosač panela)
Dubina Za Ugradnju	43 mm
Označavanje	Ex tb IIIC
Oblik Glave Signalne Jedinice	Okrugla
Operacija Kontakata	Sporo isključenje
Pozitivno Otvaranje	Bez
Put U Radu	2,6 mm (NO menja električno stanje) 4,3 mm (ukupni put)
Sila U Radu	3,8 N NO menja električno stanje
Mehanička Trajnost	5000000 ciklusa
Povezivanje - Priključci	Vijčani priključni blokovi, <= 2 x 1.5 mm² sa kablovskim završetkom u skladu sa IEC 60947-1 Vijčani priključni blokovi, 1 x 0.22...2 x 2.5 mm² bez kablovskog završetka u skladu sa IEC 60947-1
Moment Pritezanja	0,8...1,2 N.m u skladu sa IEC 60947-1

Sve cene koje su navedene u ovom cenovniku su informativne i neobavezujuće, bez PDV-a, isključivo u odnosu na ovlašćene distributere kompanije Schneider Electric. Svi prikazi, opisi i tehničke specifikacije i podaci u ovom cenovniku su podložni promenama od strane kompanije Schneider Electric bez prethodne najave.

Odricanje odgovornosti: Ova dokumentacija nije namenjena kao zamena i ne treba je koristiti za utvrđivanje podobnosti ili pouzdanosti ovih proizvoda za određene namene

Oblik Glave Zavrtnja	Ukrštena kompatibilno sa Philips no 1 odvijač Ukrštena kompatibilno sa pozidriv No 1 odvijač Sa prerezom kompatibilno sa matica Ø 4 mm odvijač Sa prerezom kompatibilno sa matica Ø 5.5 mm odvijač
Materijal Kontakata	Legura srebra (Ag/Ni)
Zaštita Od Kratkog Spoja	10 A rastavni uložak tip gG u skladu sa IEC 60947-5-1
[Ith] Dozvoljena Termička Struja U Vazduhu	10 A u skladu sa IEC 60947-5-1
[Ui] Nazivni Napon Izolacije	600 V (stepen zaprljanosti 3) u skladu sa IEC 60947-1
[Uimp] Nazivni Podnosivi Impulсни Napon	6 kV u skladu sa IEC 60947-1
[Ie] Nazivna Radna Struja	3 A pri 240 V, AC-15, A600 u skladu sa IEC 60947-5-1 6 A pri 120 V, AC-15, A600 u skladu sa IEC 60947-5-1 0,1 A pri 600 V, DC-13, Q600 u skladu sa IEC 60947-5-1 0,27 A pri 250 V, DC-13, Q600 u skladu sa IEC 60947-5-1 0,55 A pri 125 V, DC-13, Q600 u skladu sa IEC 60947-5-1 1,2 A pri 600 V, AC-15, A600 u skladu sa IEC 60947-5-1
Električna Trajnost	1000000 ciklusa AC-15, 2 A pri 230 V, broj operacija <3600 ciklusa/h, faktor opterećenja: 0,5 u skladu sa IEC 60947-5-1: dodatak C 1000000 ciklusa AC-15, 3 A pri 120 V, broj operacija <3600 ciklusa/h, faktor opterećenja: 0,5 u skladu sa IEC 60947-5-1: dodatak C 1000000 ciklusa AC-15, 4 A pri 24 V, broj operacija <3600 ciklusa/h, faktor opterećenja: 0,5 u skladu sa IEC 60947-5-1: dodatak C 1000000 ciklusa DC-13, 0,2 A pri 110 V, broj operacija <3600 ciklusa/h, faktor opterećenja: 0,5 u skladu sa IEC 60947-5-1: dodatak C 1000000 ciklusa DC-13, 0,5 A pri 24 V, broj operacija <3600 ciklusa/h, faktor opterećenja: 0,5 u skladu sa IEC 60947-5-1: dodatak C
Električna Pouzdanost Iec 60947-5-4	$\Lambda < 10\exp(-6)$ pri 5 V, 1 mA u čistoj sredini u skladu sa IEC 60947-5-4 $\Lambda < 10\exp(-8)$ pri 17 V, 5 mA u čistoj sredini u skladu sa IEC 60947-5-4

Okruženje

Tretman Zaštite	TH
Temperatura Okoline Za Skladištenje	-20...60 °C
Temperatura Okoline Za Rad Uređaja	-20...60 °C
Kategorija Prenapona	I u skladu sa IEC 60536
Ip Stepen Zaštite	IP66 u skladu sa IEC 60529
Nema Stepen Zaštite	NEMA 13 NEMA 4X
Ik Stepen Zaštite	IK03 conforming to IEC 50102
Standardi	EN 50014 EN 50281-1-1 IEC 61241-0 IEC 61241-1
Direktive	94/9/EC - ATEX direktiva
Sertifikacija Proizvoda	INERIS 04ATEX9004U GL DNV
Otpornost Na Vibracije	5 gn (f= 2...500 Hz) u skladu sa IEC 60068-2-6
Otpornost Na Udare	10 gn (trajanje = 11 milisekundi) za ubrzanje polovine sinusne periode u skladu sa IEC 60068-2-27

Pakovanje

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4,0 cm

Package 1 Width	15,0 cm
Package 1 Length	21,0 cm
Package 1 Weight	132,0 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	10
Package 2 Height	15,0 cm
Package 2 Width	15,0 cm
Package 2 Length	40,0 cm
Package 2 Weight	1,518 kg

Ugovorna garancija

Garancija	18 meseci
-----------	-----------

Održivost

Oznaka **Green Premium™** je posvećenost kompanije Schneider Electric isporuci proizvoda sa ekološkim performansama najboljim u klasi. Green Premium obećava usaglašenost sa najnovijim propisima, transparentnost u pogledu uticaja na životnu sredinu, kao i sa cirkularnim i niskonaponskim CO₂ proizvodima.

Vodič za procenu održivosti proizvoda je bela knjiga koja razjašnjava globalne standarde za oznaku ekološke prihvatljivosti i način tumačenja ekoloških izjava.

[Saznajte više o oznaci Green Premium >](#)

[Vodič za procenu održivosti proizvoda >](#)



Prozirnost



RoHS/REACH


Performanse dobrobiti

✓	Reach Bez Svhc	
✓	Bez Toksičnih Teških Metala	
✓	Bez Žive	
✓	Informacije O Rohs Izuzecima	Da

Sertifikacija i standardi

Propis Reach	REACH deklaracija
Eu Rohs Direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS) EU RoHS deklaracija
Rohs Regulativa Za Kinu	RoHS deklaracija za Kinu
Izjava O Zaštiti Okoliša	Profil ekološke prihvatljivosti proizvoda
Weee	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.
Profil Cirkularnosti	Informacije o kraju radnog veka

Emergency Stop



e : support thickness: 1 to 6 mm / 0.04 to 0.24 in.

Mounting and Clearance

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)

Connection by Screw Clamp Terminals or Plug-in Connectors or on Printed Circuit Board	Connection by Faston Connectors
(1) Diameter on finished panel or support (2) 40 mm min. / 1.57 in. min. (3) 30 mm min. / 1.18 in. min. (4) Ø 22.5 mm / 0.89 in. recommended (Ø 22.3 mm $^{+0.4}_0$ / 0.88 in. $^{+0.016}_0$) (5) 45 mm min. / 1.78 in. min. (6) 32 mm min. / 1.26 in. min.	