

Lista sa podacima o proizvodima

Specifikacije



taster za nužno isključenje OFF Ø
22-crvena peč. Ø40mm-otpuštanje
ključ.-1NO+1NC

XB7ES145P

Cena* bez PDV-a: 3.307,00 RSD

Osnovne informacije

Grupa Proizvoda	Harmony XB7
Tip Proizvoda Ili Komponente	Monolitni taster za nužno isključenje bez okidanja
Kratko Ime Uređaja	XB7
Prečnik Za Montiranje	22 mm
Prodaja Po Nedeljivim Količinama	10
Oblik Glave Signalne Jedinice	Okrugla
Tip Glave Uređaja	mehanička zadržka
Reset	Otpuštanje ključem
Profil Glave Uređaja	Crvena pečurkasti taster Ø 40 mm, neoznačeno
Tip Brave	Key 455
Tip Kontakata I Sastav	1 NO + 1 NC
Povezivanje - Priključci	Vijčani priključni blokovi, <= 2 x 1.5 mm² sa kablovskim završetkom u skladu sa IEC 60947-1 Vijčani priključni blokovi, 1 x 0.34...2 x 2.5 mm² bez kablovskog završetka u skladu sa IEC 60947-1
Prezentacija Uređaja	Monolitni proizvod

Dopunske informacije

Cad Ukupna Širina	40 mm
Cad Ukupna Visina	40 mm
Cad Ukupna Dubina	95 mm
Opis Priključaka Iso N°1	(21-22)NC (13-14)NO
Masa Proizvoda	0,058 kg
Montaža Uređaja	Otvor za montažu - prečnik: 22,5 mm 22.3 +0.4/0 u skladu sa IEC 60947-1
Centar Za Fiksiranje	>= 30 x 40 mm (nosač panela) metal 1...6 mm >= 30 x 40 mm (nosač panela) plastika 2...6 mm
Način Fiksiranja	Maticom za fiksiranje ispod glave: 2...2,4 N.m
Operacija Kontakata	Sporo isključenje
Upotreba Kontakata	Standardni
Positivno Otvaranje	Sa u skladu sa IEC 60947-5-1 dodatak K
Mehanička Trajnost	10000 ciklusa
Moment Pritezanja	0,8...1,2 N.m u skladu sa IEC 60947-1

Sve cene koje su navedene u ovom cenovniku su informativne i neobavezujuće, bez PDV-a, isključivo u odnosu na ovlašćene distributere kompanije Schneider Electric. Svi prikazi, opisi i tehničke specifikacije i podaci u ovom cenovniku su podložni promenama od strane kompanije Schneider Electric bez prethodne najave.

Odricanje odgovornosti: Ova dokumentacija nije namenjena kao zamena i ne treba je koristiti za utvrđivanje podobnosti ili pouzdanosti ovih proizvoda za određene namene

Oblik Glave Zavrtnja	Ukrštena kompatibilno sa JIS No 1 odvijač Ukrštena kompatibilno sa Philips no 1 odvijač Ukrštena kompatibilno sa pozidriv No 1 odvijač Sa prerezom kompatibilno sa matica Ø 4 mm odvijač Sa prerezom kompatibilno sa matica Ø 5.5 mm odvijač
Zaštita Od Kratkog Spoja	4 A rastavni uložak tip gG u skladu sa IEC 60947-5-1
[Ui] Nazivni Napon Izolacije	250 V (stepen zaprljanosti 3) u skladu sa IEC 60947-1
[Uimp] Nazivni Podnosivi Impulsni Napon	6 kV u skladu sa IEC 60947-1
[Ie] Nazivna Radna Struja	0,1 A pri 250 V, DC-13, R300 u skladu sa IEC 60947-5-1 0,22 A pri 125 V, DC-13, R300 u skladu sa IEC 60947-5-1 0,3 A pri 240 V, AC-14, D300 u skladu sa IEC 60947-5-1 0,6 A pri 120 V, AC-14, D300 u skladu sa IEC 60947-5-1
Električna Trajnost	1000000 ciklusa, DC-13, 0,3 A pri 24 V, broj operacija <216000 ciklusa/min, faktor opterećenja: 0,5 u skladu sa IEC 60947-5-1 dodatak C 1000000 ciklusa, AC-15, 0,03 A pri 230 V, broj operacija <216000 ciklusa/min, faktor opterećenja: 0,5 u skladu sa IEC 60947-5-1 dodatak C 1000000 ciklusa, AC-15, 0,09 A pri 240 V, broj operacija <108000 ciklusa/min, faktor opterećenja: 0,5 u skladu sa IEC 60947-5-1 dodatak C
Električna Pouzdanost Iec 60947-5-4	$\Lambda < 10\exp(-6)$ pri 17 V i 5 mA u skladu sa IEC 60947-5-4

Okruženje

Tretman Zaštite	TH
Temperatura Okoline Za Skladištenje	-40...70 °C
Temperatura Okoline Za Rad Uređaja	-25...70 °C
Klasa Zaštite Protiv Električnog Udara	Klasa II u skladu sa IEC 60536
Ip Stepen Zaštite	IP20 u skladu sa IEC 60529 (zadnji deo) IP54 u skladu sa IEC 60529 (prednji deo)
Nema Stepen Zaštite	NEMA 12 u skladu sa UL 50
Standardi	CSA C22.2 No 14 IEC 60364-5-53 UL 508 IEC 60947-1 IEC 60947-5-1
Sertifikacija Proizvoda	CCC
Otpornost Na Vibracije	5 gn (f= 2...500 Hz) u skladu sa IEC 60068-2-6
Otpornost Na Udare	10 gn (trajanje = 11 milisekundi) za ubrzanje polovine sinusne periode u skladu sa IEC 60068-2-27

Pakovanje

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6 cm
Package 1 Width	16 cm
Package 1 Length	19 cm
Package 1 Weight	64 g

Ugovorna garancija

Garancija	18 meseci
-----------	-----------

Održivost

Oznaka **Green Premium™** je posvećenost kompanije Schneider Electric isporuci proizvoda sa ekološkim performansama najboljim u klasi. Green Premium obećava usaglašenost sa najnovijim propisima, transparentnost u pogledu uticaja na životnu sredinu, kao i sa cirkularnim i niskonaponskim CO₂ proizvodima.

Vodič za procenu održivosti proizvoda je bela knjiga koja razjašnjava globalne standarde za oznaku ekološke prihvatljivosti i način tumačenja ekoloških izjava.

[Saznajte više o oznaci Green Premium >](#)

[Vodič za procenu održivosti proizvoda >](#)





Prozirnost

RoHS/REACH

Performanse dobrobiti

- ✓

Bez Žive
- ✓

Informacije O Rohs Izuzecima

Da


Sertifikacija i standardi

Propis Reach	REACH deklaracija
Eu Rohs Direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Rohs Regulativa Za Kinu	RoHS deklaracija za Kinu
Izjava O Zaštiti Okoliša	Profil ekološke prihvatljivosti proizvoda
Weee	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.
Profil Cirkularnosti	Informacije o kraju radnog veka

Dimensions Drawings

Emergency Switching off Pushbutton with Key

Dimensions




e Support panel thickness: 1 to 6 mm/0.4 to 0.24 in. (metal), 2 to 6 mm/0.8 to 0.24 in. (plastic).

Mounting and Clearance


Mounting

Diameter of Finished Fixing Holes



- (1) Minimum value.
- (2) 40 mm/1.58 in. for Emergency switching off pushbutton only.
- (3) Standard value: Ø 22.3 (0; + 0.4) mm/Ø 0.88 (0; + 0.02) in.

“U” Type Tag Connection



- (1) 6.5 mm/0.26 in. recommended, 7 mm/0.28 in. max.
- (2) M3 screw clamp terminal.

Wiring

