

Lista sa podacima o proizvodima

Specifikacije



svetlosna kolona sa zujalicom + 2
svetleće jedinice Ø 45 mm - 230 V
AC

XVMM2RGSSB

Cena* bez PDV-a: 9.112,00 RSD

Osnovne informacije

Grupa Proizvoda	Harmony XVM
Tip Proizvoda Ili Komponente	Sastavljena i prefabrikovana svetleća kolona
Tip Baze Svetleće Kolone Ili Semafora	2 svetleće jedinice
Ime Komponente	XVM
Svetlosni Izvor	Zelena izrazito sjajan LED sa BA 15d bazi trajna signalizacijom Crvena izrazito sjajan LED sa BA 15d bazi trajna signalizacijom
Boja Svetlosnog Bloka	Crvena/zelena
[Us] Nazivni Napon Napajanja	230 V AC
Tip Baze Svetleće Kolone	Baza sa integrisanom zujalicom
Način Montiranja	Vertikalno

Dopunske informacije

Sastav Seta	Plastična pločica za montažu Poklopac Aluminijumski cevasti nosač Baza
Prečnik Za Montiranje	45 mm
Povezivanje - Priključci	Žičani završeci, 1 x 0.325 mm ² (AWG 22)
Označavanje	CE
Držač Za Montažu	Aluminijum cev
Zaštita Od Preopterećenja I Kratkog Spoja	0,2 A
[Ui] Nazivni Napon Izolacije	250 V u skladu sa IEC 60947-1
Nazivno Ograničenje Napona	0.85...1.1 Un u skladu sa IEC 60947-5-1
Potrošnja Struje	18 mA na bazi 15 mA na LED jedinica za trajno osvetljenje
[Uimp] Nazivni Podnosivi Impulsni Napon	4 kV u skladu sa IEC 60947-1
Frekvencija Osnovnog Harmonika	4 kHz
Masa Proizvoda	0,404 kg

Okruženje

Ip Stepen Zaštite	IP42 vertikalnoj poziciji u skladu sa IEC 60529
Sertifikacija Proizvoda	CCC
Standardi	IEC 60947-5-1 IEC 60947-1

Sve cene koje su navedene u ovom cenovniku su informativne i neobavezujuće, bez PDV-a, isključivo u odnosu na ovlašćene distributere kompanije Schneider Electric. Svi prikazi, opisi i tehničke specifikacije i podaci u ovom cenovniku su podložni promenama od strane kompanije Schneider Electric bez prethodne najave.

Odricanje odgovornosti: Ova dokumentacija nije namenjena kao zamena i ne treba je koristiti za utvrđivanje podobnosti ili pouzdanosti ovih proizvoda za određene namene

Temperatura Okoline Za Skladištenje	-25...70 °C
Temperatura Okoline Za Rad Uređaja	-10...50 °C
Kategorija Prenapona	Klasa I u skladu sa IEC 60947-1 Klasa I u skladu sa IEC 60947-5-1 Klasa I u skladu sa IEC 61140
Tretman Zaštite	TC
Nivo Buke	0...80 dB pri 1 m

Pakovanje

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5,8 cm
Package 1 Width	8,5 cm
Package 1 Length	54 cm
Package 1 Weight	529 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	20
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	11,768 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	80
Package 3 Height	75 cm
Package 3 Width	40 cm
Package 3 Length	80 cm
Package 3 Weight	67,32 kg

Ugovorna garancija

Garancija	18 meseci
-----------	-----------

Održivost

Oznaka **Green Premium™** je posvećenost kompanije Schneider Electric isporuci proizvoda sa ekološkim performansama najboljim u klasi. Green Premium obećava usaglašenost sa najnovijim propisima, transparentnost u pogledu uticaja na životnu sredinu, kao i sa cirkularnim i niskonaponskim CO₂ proizvodima.

Vodič za procenu održivosti proizvoda je bela knjiga koja razjašnjava globalne standarde za oznaku ekološke prihvatljivosti i način tumačenja ekoloških izjava.

[Saznajte više o oznaci Green Premium >](#)

[Vodič za procenu održivosti proizvoda >](#)



Prozirnost



RoHS/REACH

Performanse dobrobiti

 Bez Žive	
 Informacije O Rohs Izuzecima	Da

Sertifikacija i standardi


Propis Reach	REACH deklaracija
Eu Rohs Direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Rohs Regulatorna Za Kinu	RoHS deklaracija za Kinu
Izjava O Zaštiti Okoliša	Profil ekološke prihvatljivosti proizvoda
Weee	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.
Profil Cirkularnosti	Nema potrebe za namenskim operacijama recikliranja

Dimensions Drawings

Pre-Assembled and Pre-Cabled Tower Light with Fixing Base for Mounting on Vertical
Support (Support Tube + Metal Bracket)

Dimensions

Below drawing shows the maximum configuration of the product. Select the number of stages according to the product characteristics in order to get **b2** dimension.



(1) Base unit with or without buzzer.

Number of illuminated units	b2 in mm	b2 in in.
1 unit	383	15.08
2 units	448	17.64
3 units	513	20.20
4 units	578	22.76

Connections and Schema

Pre-Assembled and Pre-Cabled Tower Light

Wire Colors


- 4th illuminated unit: yellow wire
- 3rd illuminated unit: green wire
- 2nd illuminated unit: white wire
- 1st illuminated unit: blue wire
- Common: black wire
- Buzzer (if integrated in base unit): grey wire

Technical Description

Base Unit with Integral Buzzer

Adjustment of Audible Signal

View from above:



- (1) Volume adjustment potentiometer: 0 to 85 dB. Use either a cross headed or flat tipped screwdriver.
- (2) 2-position selector for type of audible signal: continuous tone or intermittent tone