Product datasheet

Specifications





Circuit breaker, ComPact NSX100F, 36kA/415VAC, TMD trip unit 50A, 4 poles 3d

LV429643

() Discontinued on: Jun 9, 2022 AD

① Discontinued

Main

| Range | ComPact |
|---|---|
| Product Name | ComPact NSX |
| Range Of Product | ComPact NSX100250 |
| Device Short Name | NSX100F |
| Product Or Component Type | Circuit breaker |
| Device Application | Distribution |
| Number Of Poles | 4P |
| Protected Poles Description | 3t |
| Neutral Position | Left |
| [In] Rated Current | 50 A at 40 °C |
| [Ue] Rated Operational Voltage | 690 V AC 50/60 Hz |
| Network Type | AC |
| Network Frequency | 50/60 Hz |
| Suitability For Isolation | Yes conforming to EN/IEC 60947-2 |
| Utilisation Category | Category A |
| [Icu] Rated Ultimate Short-Circuit Breaking Capacity | 10 kA at 600 V AC 50/60 Hz conforming to UL 508 25 kA at 480 V AC 50/60 Hz conforming to UL 508 85 kA at 240 V AC 50/60 Hz conforming to UL 508 22 kA lcu at 525 V AC 50/60 Hz conforming to IEC 60947-2 25 kA lcu at 500 V AC 50/60 Hz conforming to IEC 60947-2 35 kA lcu at 440 V AC 50/60 Hz conforming to IEC 60947-2 36 kA lcu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 8 kA lcu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 8 kA lcu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 |
| Performance Level | F 36 kA 415 V AC |
| Trip Unit Name | TM-D |
| Trip Unit Technology | Thermal-magnetic |
| Trip Unit Protection Functions | LI |
| Control Type | Toggle |
| Circuit Breaker Mounting Mode | Fixed |

Complementary

| [Ui] Rated Insulation Voltage | 800 V AC 50/60 Hz |
|---|-------------------|
| [Uimp] Rated Impulse Withstand Voltage | 8 kV |

| [Ics] Rated Service Short-Circuit Breaking Capacity | 11 kA at 525 V AC 50/60 Hz conforming to IEC 60947-2 35 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 36 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 4 kA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 85 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 12.5 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2 |
|--|---|
| Mechanical Durability | 50000 cycles |
| Electrical Durability | 10000 cycles at 690 V In 20000 cycles at 690 V In/2 30000 cycles at 440 V In 50000 cycles at 440 V In/2 |
| Mounting Support | Backplate |
| Upside Connection | Front |
| Downside Connection | Front |
| Connection Pitch | 35 mm |
| Protection Type | L : for overload protection (thermal) I : for short-circuit protection (magnetic) |
| Trip Unit Rating | 50 A at 40 °C |
| Long-Time Pick-Up Adjustment Type Ir (Thermal Protection) | Adjustable |
| [Ir] Long-Time Protection Pick-Up Adjustment Range | 0.71 x ln |
| Long-Time Protection Delay Adjustment Type Tr | Fixed |
| [Tr] Long-Time Protection Delay Adjustment Range | 120…400 s at 1.5 x ln 15 s at 6 x lr |
| Short-Time Protection Pick-Up Adjustment Type Isd | Fixed |
| [Isd] Short-Time Protection Pick- Up Adjustment Range | 500 A |
| Short-Time Protection Delay Adjustment Type Tsd | Fixed |
| Earth-Leakage Protection | Without |
| Neutral Protection Settings | No protection (3t) |
| Number Of Slots For Electrical Auxiliaries | 5 slot(s) |
| Width (W) | 140 mm |
| Height (H) | 161 mm |
| Depth (D) | 86 mm |
| Net Weight | 2.4 kg |

Environment

| Standards | EN/IEC 60947 |
|-----------------------------------|------------------------------|
| Product Certifications | ссс |
| | EAC |
| | Marine |
| Overvoltage Category | Class II |
| Electrical Shock Protection Class | Class II |
| Pollution Degree | 3 conforming to IEC 60664-1 |
| Ip Degree Of Protection | IP40 conforming to IEC 60529 |
| Ik Degree Of Protection | IK07 conforming to IEC 62262 |
| Ambient Air Temperature For | -2570 °C |

| Ambient Air Temperature For Storage | -5085 °C |
|--|--|
| Relative Humidity | 095 % |
| Operating Altitude | 02000 m without derating 2000 m5000 m with derating |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|-----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 13.700 cm |
| Package 1 Width | 14.800 cm |
| Package 1 Length | 19.200 cm |
| Package 1 Weight | 2.318 kg |
| Unit Type Of Package 2 | S04 |
| Number Of Units In Package 2 | 9 |
| Package 2 Height | 30.000 cm |
| Package 2 Width | 40.000 cm |
| Package 2 Length | 60.000 cm |
| Package 2 Weight | 21.583 kg |

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | End of Life Information |