



# TeSys F - contactor coil - LX0FF - 220...230 V AC/DC

LX0FF008

! Discontinued on: Dec 30, 2020 AD

! Discontinued

### Main

Range	TeSys	
Product Or Component Type	Contactor coil	
Device Short Name	LX0FF	
Control Circuit Type	AC at 50400 Hz DC standard	
[Uc] Control Circuit Voltage	220230 V AC 50400 Hz 220230 V DC	
Average Resistance	37.55 Ohm latching at 20 °C 5139 Ohm unlatching at 20 °C	
Product Compatibility	CR1F150	
Operating Time	3540 ms latching 50100 ms unlatching	
Mechanical Durability	1 Mcycles	
Maximum Operating Rate	120 cyc/h 40 °C	

## Complementary

Control Circuit Voltage Limits Latching: 0.85...1.1 Uc Unlatching: 0.85...1.1 Uc

#### **Environment**

Net Weight 0.44 kg

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7 cm
Package 1 Width	8 cm
Package 1 Length	16 cm
Package 1 Weight	483 g

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>Ø</b>	Toxic Heavy Metal Free	
<b>9</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information