Product datasheet

Specification





Circuit breaker, EasyPact MVS, 3 Poles, 800A, 50kA, MDO, ET2, drawout, manual

MVS08N3MW2L

Main

Range	EasyPact	
Product Name	MVS08N	
Device Short Name	MVS08N	
Product Or Component Type	/pe Circuit breaker	
Device Application	Distribution	
Poles Description	3P	
Protected Poles Description	3P 3d	
[In] Rated Current	800 A at 40 °C	
Network Type	AC	
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz conforming to IEC 60947-2	
Breaking Capacity Code	N	
Suitability For Isolation	Yes conforming to IEC 60947-2	
Utilisation Category	Category B	
Trip Unit Name	ET2I	
Trip Unit Technology	Electronic	
Trip Unit Rating	800 A	

Complementary

Network Frequency	50/60 Hz
Control Type	Manually operated
Mounting Mode	Drawout
Mounting Support	Rail Base plate
Connection Position	Vertical Horizontal
Location Of Connection	Rear
[Ui] Rated Insulation Voltage	1000 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	12 kV conforming to IEC 60947-2
Circuit Breaker Ct Rating	800 A
Breaking Capacity	50 kA Icu at 220440 V AC 50/60 Hz conforming to IEC 60947-2
[Ics] Rated Service Breaking Capacity	50 kA (Ics) at 220440 V AC 50/60 Hz conforming to IEC 60947-2

Mechanical Durability	20000 cycles (with maintenance) conforming to IEC 60947-2 10000 cycles (without maintenance) conforming to IEC 60947-2
Electrical Durability	Category B: 6000 cycles 440 V AC 50/60 Hz without maintenance conforming to IEC 60947-2 Category B: 4000 cycles 690 V AC 50/60 Hz without maintenance conforming to IEC
	60947-2
Connection Pitch	115 mm without spreader
Contact Position Indicator	Yes
[Icm] Rated Short-Circuit Making Capacity	105 kA (lcm) at 220440 V AC 50/60 Hz conforming to IEC 60947-2
[Icw] Rated Short-Time Withstand Current	50 kA (1 s) at 220440 V AC 50/60 Hz conforming to IEC 60947-2 42 kA (1 s) at 690 V AC 50/60 Hz conforming to IEC 60947-2 25 kA (3 s) at 440/690 V AC 50/60 Hz conforming to IEC 60947-2
Trip Unit Protection Functions	Ц
Protection Type	Overload protection (long time) Instantaneous short-circuit protection
Fault Indication	Short-circuit Overload Internal fault
Long Time Pick-Up Adjustment Type Ir	Adjustable 9 settings
Long Time Pick-Up Adjustment Range	0.41 x ln
Long Time Delay Adjustment Type	Adjustable 9 settings
[Tr] Long-Time Delay Adjustment Range	0.524 s at 6 x lr
Thermal Memory	20 minutes before and after tripping
Instantaneous Pick-Up Adjustment Type Ii	Adjustable 9 settings
Instantaneous Pick-Up Adjustment Range	1.510 x lr
Zone Selective Interlocking Zsi	With
Current Sensor Rating Range	400/2000 A
Maximum Breaking Time	25 ms
Maximum Closing Response Time	70 ms
Height	439 mm
Width	441 mm
Depth	395 mm
Net Weight	70 kg
Environment	

Standards	IEC 60947-2
Product Certifications	GOST IEC CCS CCC
Pollution Degree	4 conforming to IEC 60664-1
Ip Degree Of Protection	IP40
Ambient Air Temperature For Operation	-570 °C
Ambient Air Temperature For Storage	-4085 °C without control unit -2585 °C with control unit

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	35.0 cm
Package 1 Width	42.0 cm
Package 1 Length	50.0 cm
Package 1 Weight	38.0 kg

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Mercury Free	
9	Rohs Exemption Information	Yes
9	Pvc Free	


Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Product datasheet

MVS08N3MW2L

Dimensions Drawings







Product datasheet

MVS08N3MW2L

Assembly





MVS08N3MW2L

Performance Curves

