

# Product datasheet

Specifications



## Evlink - Electric Vehicle Simulation tool

NCA93100

### Main

Range	EVlink
Product Or Component Type	Simulation tool

### Complementary

Earthing System	TN TT
Output Type	Socket-inlet T2 right 400 V Socket-inlet T1 left 230 V
Height	270 mm
Width	305 mm
Depth	170 mm
Net Weight	6 kg
Colour	Black

### Environment

Standards	IEC 61851-1 IEC 61010-1
Ip Degree Of Protection	IP44 (opened) IP54 (closed)
Ik Degree Of Protection	IK08
Ambient Air Temperature For Operation	-30...50 °C
Ambient Air Temperature For Storage	-30...50 °C

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	20 cm
Package 1 Width	28.2 cm
Package 1 Length	39 cm
Package 1 Weight	5.489 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Sustainability





**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	<a href="#">Yes</a>
Eu Rohs Directive		Compliant
		<a href="#">EU RoHS Declaration</a>
China Rohs Regulation		<a href="#">China RoHS declaration</a>