

Product datasheet

Specifications



system with charger, Harmony eXLhoist, standard, shoulder belt, cable USB/RJ45 and config software

XARSK8D18W

Main

| | |
|------------------------------|--|
| Range Of Product | Harmony eXLhoist |
| Product Or Component Type | Control station |
| Device Short Name | XARS |
| Control Station Type | Wireless |
| Product Specific Application | Hoisting applications Material handling |
| Number Of Channels | 50 |
| Control Station Application | Stop function: SIL 2 maximum (can reach PL d/category 3) conforming to IEC 62061 Stop function: SIL 2 maximum (can reach PL d/category 3) conforming to ISO 13849-1 Emergency stop function: SIL 3 maximum (can reach PL e/category 4) conforming to IEC 62061 Emergency stop function: SIL 3 maximum (can reach PL e/category 4) conforming to ISO 13849-1 Motion function: SIL 1 maximum (can reach PL c/category 1) conforming to IEC 62061 Motion function: SIL 1 maximum (can reach PL c/category 1) conforming to ISO 13849-1 Limiter protection function: SIL 1 maximum (can reach PL c/category 1) conforming to IEC 62061 Limiter protection function: SIL 1 maximum (can reach PL c/category 1) conforming to ISO 13849-1 |

Complementary

| | |
|----------------------------|--|
| Kit Composition | Remote control Base station Shoulder belt Cable Configuration software |
| Operating Distance | 100 m in free air |
| Cable Entry | Cable gland |
| Communication Network Type | Wireless: bluetooth low energy |
| Transmission Frequency | 2.4 GHz |

Environment

| | |
|-------------------|---|
| Radio Agreement | SRRC RSS ARIB ANATEL FCC ICASA |
| Relative Humidity | 0...95 % at -20...45 °C storage |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|-------------------------------|---|
| Electromagnetic Compatibility | Resistance to electrostatic discharge - test level: 4 kV class B (on contact) conforming to IEC 61000-4-2 Resistance to electrostatic discharge - test level: 8 kV class B (in air) conforming to IEC 61000-4-2 Resistance to radiated electromagnetic fields - test level: 10 V/m class B conforming to IEC 61000-4-3 |
| Standards | IEC 60204-1 safety ISO 13849-1 safety IEC 62061 safety IEC 61508 safety ISO 13850 safety IEC 60204-32 hoisting applications ETSI EN 301 489-1 radio ETSI EN 301 489-3 radio ETSI EN 301 489-17 radio ETSI EN 300 440-2 radio ETSI EN 300 328 radio FCC part 15 radio RSS GEN issue 3 radio RSS 210 issue 8 radio ARIB STD-T81 radio |
| Product Certifications | CE UL CSA C-Tick JIS KC EAC |

Packing Units

| | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 20.5 cm |
| Package 1 Width | 29.0 cm |
| Package 1 Length | 30.8 cm |
| Package 1 Weight | 3.148 kg |
| Unit Type Of Package 2 | S04 |
| Number Of Units In Package 2 | 2 |
| Package 2 Height | 30.0 cm |
| Package 2 Width | 40.0 cm |
| Package 2 Length | 60.0 cm |
| Package 2 Weight | 6.884 kg |

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.



[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Well-being performance

| | | |
|---|---|-----|
|  | Mercury Free | |
|  | Rohs Exemption Information | Yes |
| | | |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) | |
| | | |
| China Rohs Regulation | China RoHS declaration | |
| | | |
| Environmental Disclosure | Product Environmental Profile | |
| | | |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins | |
| | | |
| Circularity Profile | End of Life Information | |