

Lista sa podacima o proizvodima

Specifikacije



crvena glava signalne lampice
Ø16 za integrisan LED

ZB6AV4

Cena* bez PDV-a: 780,00 RSD

Osnovne informacije

Grupa Proizvoda	Harmony XB6
Tip Proizvoda Ili Komponente	Glava za signalnu lampicu
Kompatibilnost Proizvoda	Integrisan LED
Kratko Ime Uređaja	ZB6
Materijal Podnožja	Plastika
Prečnik Za Montiranje	16 mm
Prodaja Po Nedeljivim Količinama	1
Oblik Glave Signalne Jedinice	Okrugla
Boja Kapica/Glave Ili Sočiva	Crvena

Dopunske informacije

Cad Ukupna Širina	18 mm
Cad Ukupna Visina	18 mm
Cad Ukupna Dubina	33 mm
Masa Proizvoda	0,015 kg

Okruženje

Tretman Zaštite	TC
Temperatura Okoline Za Skladištenje	-40...70 °C
Temperatura Okoline Za Rad Uređaja	-25...70 °C
Klasa Zaštite Protiv Električnog Udara	Klasa II u skladu sa IEC 61140
Ip Stepen Zaštite	IP65 u skladu sa IEC 60529
Nema Stepen Zaštite	NEMA 13 u skladu sa UL 50 NEMA 4 u skladu sa UL 50 NEMA 4X u skladu sa UL 50 NEMA 13 u skladu sa CSA C22.2 No 94 NEMA 4 u skladu sa CSA C22.2 No 94 NEMA 4X u skladu sa CSA C22.2 No 94

Standardi	UL 508 EN/IEC 60947-5-1 JIS C 4520 EN/IEC 60947-5-5 JIS C 852 CSA C22.2 No 14 EN/IEC 60947-1
-----------	--

Sve cene koje su navedene u ovom cenovniku su informativne i neobavezujuće, bez PDV-a, isključivo u odnosu na ovlašćene distributere kompanije Schneider Electric. Svi prikazi, opisi i tehničke specifikacije i podaci u ovom cenovniku su podložni promenama od strane kompanije Schneider Electric bez prethodne najave.

Odricanje odgovornosti: Ova dokumentacija nije namenjena kao zamena i ne treba je koristiti za utvrđivanje podobnosti ili pouzdanosti ovih proizvoda za određene namene

Sertifikacija Proizvoda	GOST CSA CCC UL
Otpornost Na Vibracije	+/- 3 mm (f= 2...500 Hz) u skladu sa IEC 60068-2-6 5 gn (f= 2...500 Hz) u skladu sa IEC 60068-2-6
Otpornost Na Udare	30 gn (trajanje = 18 milisekundi) za ubrzanje polovine sinusne periode u skladu sa IEC 60068-2-27 50 gn (trajanje = 11 milisekundi) za ubrzanje polovine sinusne periode u skladu sa IEC 60068-2-27

Pakovanje

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3,2 cm
Package 1 Width	5,1 cm
Package 1 Length	8,6 cm
Package 1 Weight	8,0 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	80
Package 2 Height	15 cm
Package 2 Width	15 cm
Package 2 Length	40 cm
Package 2 Weight	840 g
Package 3 Height	15 cm

Ugovorna garancija

Garancija	18 meseci
-----------	-----------

Održivost

Oznaka **Green Premium™** je posvećenost kompanije Schneider Electric isporuci proizvoda sa ekološkim performansama najboljim u klasi. Green Premium obećava usaglašenost sa najnovijim propisima, transparentnost u pogledu uticaja na životnu sredinu, kao i sa cirkularnim i niskonaponskim CO₂ proizvodima.

Vodič za procenu održivosti proizvoda je bela knjiga koja razjašnjava globalne standarde za oznaku ekološke prihvatljivosti i način tumačenja ekoloških izjava.

[Saznajte više o oznaci Green Premium >](#)

[Vodič za procenu održivosti proizvoda >](#)



Prozirnost



RoHS/REACH

Performanse dobrobiti

- 

Bez Žive
- 

Informacije O Rohs Izuzecima

Da


Sertifikacija i standardi

Propis Reach	REACH deklaracija
Eu Rohs Direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Rohs Regulativa Za Kinu	RoHS deklaracija za Kinu
Izjava O Zaštiti Okoliša	Profil ekološke prihvatljivosti proizvoda
Profil Cirkularnosti	Informacije o kraju radnog veka

Dimensions Drawings

Circular Head for Pilot Light


Dimensions



Mounting and Clearance


Panel Cut-out

For Square or Circular Head




Pushbuttons, Switches and Pilot Lights for Printed Circuit Board Connection

Front Panel Cut-out (Viewed from Installer's Side)



Printed Circuit Board Drillings (Viewed from Electrical Block Side)



- A 24 mm/0.94 in. minimum for rectangular heads, 18 mm/0.71 in. minimum for square or circular heads
- B 18 mm/0.71 in. minimum
- (1) 6 x $\varnothing 1.1$ mm / 6 x $\varnothing 0.04$ in. holes.
- (2) 1 x $\varnothing 2.6^{0}_{-0,2}$ mm / 1 x $\varnothing 0.10^{0}_{-0,008}$ in. hole for locating pin, only when using socket adaptor ZB6Y010.
- (3) 1 x $\varnothing 3.2^{0}_{-0,2}$ mm / 1 x $\varnothing 0.13^{0}_{-0,008}$ in. hole for fixing of printed circuit board onto the front panel using body bracket ZB6Y011. This hole must be drilled on the left-hand side, when heads are positioned at the normal angle. Fit a body bracket ZB6Y011 every 72 mm/2.83 in. maximum for cut-outs on 24 mm/0.94 in. centres (rectangular heads) and 54 mm/2.13 in. maximum for cut-outs on 18 mm/0.71 in. centres (square or circular heads).

General tolerances of the panel and printed circuit board: T1, T2: T1 + T2 = 0.3 mm/0.01 in. maximum.
Installation precautions:


Lista sa podacima o
proizvodima

ZB6AV4

Thickness of printed circuit board: 1.6 mm/0.06 in. minimum.


Mounting with Body Bracket

With socket adaptor ZB6Y010



- (1) Head
- (2) Nut
- (3) Body
- (4) Body bracket
- (5) Contact block
- (6) Socket adaptor
- (7) Panel
- (8) Printed circuit

Direct mounting without socket adaptor ZB6Y010



- (1) Head
- (2) Nut
- (3) Body
- (4) Body bracket
- (5) Contact block
- (6) Panel
- (7) Printed circuit

