# **Product datasheet**

Specifications





Residual current breaker with overcurrent protection (RCBO), Acti9 iC60N RCBO, 1P+Ns, 16A, 30mA, A type, 6000A

A9D61816

#### Main

Circuit Breaker Application	Distribution
Range	Acti9
Product Name	Acti9 iC60 RCBO
Product Or Component Type	Residual current breaker with overcurrent protection (RCBO)
Device Short Name	iC60N RCBO
Poles Description	1P + Ns
[In] Rated Current	16 A at 50 °C
Earthing System	TN
Curve Code	С
Earth-Leakage Sensitivity	30 mA
Breaking Capacity	6000 A Icn at 230/240 V AC 50/60 Hz

## Complementary

Neutral Position	Left	
Number Of Protected Poles	1	
Device Location In System	Outgoer	
Network Frequency	50 Hz	
Network Type	AC	
Trip Unit Technology	Thermal-magnetic	
[Ue] Rated Operational Voltage	230/240 V AC 50/60 Hz	
Residual Current Tripping Technology	Voltage dependent	
Earth-Leakage Protection Time Delay	Instantaneous	
Earth-Leakage Protection Class	Туре А	
[Icw] Rated Short-Time Withstand Current	Icw: 250 A during 8/20 μs impulse withstand	
[Ics] Rated Service Breaking Capacity	6000 A at 230/240 V AC 50/60 Hz	
Limitation Class	3	
[Ui] Rated Insulation Voltage	400 V AC 50/60 Hz	
[Uimp] Rated Impulse Withstand Voltage	4 KV	
Surge Current	250 A	
Suitability For Isolation	Yes	

Contact Position Indicator	Yes	
Control Type	Toggle	
Local Signalling	ON/OFF indication	
Mounting Mode	Clip-on	
Mounting Support	DIN rail	
Comb Busbar And Distribution Block Compatibility	NO	
9 Mm Pitches	2	
Height	110 mm	
Width	18 mm	
Depth	77.5 mm	
Net Weight	205 g	
Colour	White	
Mechanical Durability	20000 cycles	
Electrical Durability	5000 cycles	
Provision For Padlocking	Padlockable with padlock Ø 4 mm	
Locking Options Description	ON/OFF locking facilities	
Connections - Terminals	Screw clamp terminal (top) 125 mm <sup>2</sup> rigid without cable end Screw clamp terminal (top) 116 mm <sup>2</sup> flexible Screw clamp terminal (bottom) 116 mm <sup>2</sup> rigid without cable end Screw clamp terminal (bottom) 110 mm <sup>2</sup> flexible	
Wire Stripping Length	Power circuit: 13 mm for bottom connection Power circuit: 14 mm for top connection	
Tightening Torque	Power circuit: 3.5 N.m top Power circuit: 2 N.m bottom	
Earth-Leakage Protection	Integrated	

### Environment

Standards	IEC 61009-2-2 IEC 61009-1 AS/NZS 61009.1
Ip Degree Of Protection	IP20
Tropicalisation	2
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-1560 °C
Ambient Air Temperature For Storage	-4085 °C

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.6 cm
Package 1 Width	2.8 cm
Package 1 Length	11.2 cm
Package 1 Weight	220 g
Unit Type Of Package 2	BB1

Number Of Units In Package 2	34
Package 2 Height	154 cm
Package 2 Width	290 cm
Package 2 Length	398 cm
Package 2 Weight	7.798 kg

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations Circularity Profile