

Product datasheet

Specifications



Modular contactor, TeSys GC, AC-7a, 100A, 4NO, 220 to 240VAC 50Hz coil

GC10040M5

Main

Range	TeSys
Product Name	TeSys GC
Product Or Component Type	Modular contactor
Device Short Name	GC100
Contactor Application	Lighting Heating Motor control

Complementary

Utilisation Category	AC-7A
Poles Description	4P
Power Pole Contact Composition	4 NO
[Ue] Rated Operational Voltage	<= 250 V AC
[Ie] Rated Operational Current	100 A AC-7A
Operating Position	30°/vertical
Control Circuit Type	AC at 50 Hz
[Uc] Control Circuit Voltage	220...240 V AC 50 Hz
[Uimp] Rated Impulse Withstand Voltage	4 kV
[Ith] Conventional Free Air Thermal Current	100 A (at 50 °C) for power circuit
[Icw] Rated Short-Time Withstand Current	800 A 40 °C - 10 s for power circuit 250 A 40 °C - 30 s for power circuit
Associated Fuse Rating	100 A gL at <= 440 V for power circuit
Average Impedance	1 mOhm - Ith 100 A 50 Hz for power circuit
[Ui] Rated Insulation Voltage	500 V conforming to IEC 61095 500 V conforming to VDE 0110
Electrical Durability	AC-7A: 30000 cycles
Power Dissipation Per Pole	10 W
Control Type	Remote control
Mounting Mode	Clip-on
Mounting Support	DIN rail
Standards	IEC 60947-5 IEC 61095

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Connections - Terminals	Power circuit: screw clamp terminals 1 cable(s) 35 mm²flexible without cable end Power circuit: screw clamp terminals 1 cable(s) 35 mm²flexible with cable end Power circuit: screw clamp terminals 1 cable(s) 35 mm²solid without cable end Power circuit: screw clamp terminals 2 cable(s) 10 mm²solid without cable end Control circuit: screw clamp terminals 1 cable(s) 2.5 mm²flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 2.5 mm²flexible without cable end Control circuit: screw clamp terminals 1 cable(s) 2.5 mm²flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 1.5 mm²flexible with cable end Control circuit: screw clamp terminals 1 cable(s) 1.5 mm²solid without cable end Control circuit: screw clamp terminals 2 cable(s) 1.5 mm²solid without cable end
Tightening Torque	Control circuit: 0.8 N.m - on screw clamp terminals Power circuit: 3.5 N.m - on screw clamp terminals
Operating Time	10...25 ms opening 10...30 ms closing
Mechanical Durability	1000000 cycles
Maximum Operating Rate	300 cyc/h 50 °C
Control Circuit Voltage Limits	Drop-out: 0.2...0.75 Uc at 50 Hz (at <50 °C) Operational: 0.85...1.1 Uc at 50 Hz (at <50 °C)
Inrush Power In Va	106 VA 50 Hz (at 20 °C)
Hold-In Power Consumption In Va	13 VA 50 Hz (at 20 °C)
Heat Dissipation	4.2 W at 50/60 Hz

Environment

Ip Degree Of Protection	IP40 conforming to VDE 0106 (in enclosure) IP20 conforming to VDE 0106
Protective Treatment	TC
Ambient Air Temperature For Operation	-5...50 °C
Ambient Air Temperature For Storage	-40...70 °C
Operating Altitude	<= 3000 m
Mechanical Robustness	Shocks contactor open: 10 Gn for 11 ms Shocks contactor closed: 15 Gn for 11 ms Vibrations contactor open: 2 Gn, 5...300 Hz Vibrations contactor closed: 3 Gn, 5...300 Hz
Total Number Of 18 Mm Modules	6
Height	85 mm
Width	108 mm
Depth	62.5 mm
Net Weight	0.78 kg
Quantity Per Set	Set of 2
Colour	White

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8 cm
Package 1 Width	8 cm
Package 1 Length	9 cm
Package 1 Weight	654 g
Unit Type Of Package 2	BB1

Number Of Units In Package 2	2
Package 2 Height	8 cm
Package 2 Width	9.5 cm
Package 2 Length	23 cm
Package 2 Weight	1.31 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	16
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	11.177 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Reach Free Of Svhc	
 Toxic Heavy Metal Free	
 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins