Product datasheet





C60 - circuit breaker - C60N - 4P -50A - D curve

24623

! Discontinued on: 25 Jul 2019

EAN Code: 3303430246237

! Discontinued

Main

Range Of Product	C60
Range	Multi9
Product Name	C60
Product Or Component Type	Miniature circuit-breaker
Device Short Name	C60N
Device Application	Distribution
Poles Description	4P
Number Of Protected Poles	4
[In] Rated Current	50 A at 40 °C
Network Type	DC AC
Trip Unit Technology	Thermal-magnetic
Curve Code	D
Breaking Capacity	10 kA Icu at 400415 V AC 50/60 Hz conforming to EN/IEC 60947-2 6 kA Icu at 440 V AC 50/60 Hz conforming to EN/IEC 60947-2 6000 A Icn at 230/400 V AC 50/60 Hz conforming to EN 60898 20 kA Icu at 125 V DC 2P conforming to EN/IEC 60947-2 20 kA Icu at 230240 V AC 50/60 Hz conforming to EN/IEC 60947-2 30 kA Icu at 125 V DC 3P conforming to EN/IEC 60947-2 40 kA Icu at <= 250 V DC 4P conforming to EN/IEC 60947-2
Suitability For Isolation	Yes conforming to IEC 60947-2

Complementary

Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	440 V AC 50/60 Hz 230240 V AC 50/60 Hz 400415 V AC 50/60 Hz <= 250 V DC 230/400 V AC 50/60 Hz
Magnetic Tripping Limit	1014 x ln
[Ics] Rated Service Breaking Capacity	7.5 kA conforming to EN/IEC 60947-2 - 230240 V AC 50/60 Hz 2.25 kA conforming to EN/IEC 60947-2 - 440 V AC 50/60 Hz 3.75 kA conforming to EN/IEC 60947-2 - 400415 V AC 50/60 Hz 6000 A conforming to EN 60898 - 230/400 V AC 50/60 Hz
Limitation Class	3 conforming to EN/IEC 60947-2
Contact Position Indicator	Yes
Control Type	Toggle

Life Is On Schneider 23 Apr 2024

	
Local Signalling	ON/OFF indication
Mounting Mode	Clip-on
Mounting Support	35 mm symmetrical DIN rail
Comb Busbar And Distribution Block Compatibility	NO
9 Mm Pitches	8
Height	81 mm
Width	72 mm
Depth	73 mm
Net Weight	0.48 kg
Mechanical Durability	20000 cycles
Connections - Terminals	Tunnel type terminals25 mm² flexible Tunnel type terminals35 mm² rigid
Tightening Torque	Power circuit: 3.5 N.m upside 3.5 N.m downside
Earth-Leakage Protection	Separate block
Product Compatibility	C60 accessories C60 auxiliary

Environment

Standards	EN 60898 EN/IEC 60947-2
Overvoltage Category	IV
Tropicalisation	2 conforming to IEC 60068-1
Relative Humidity	95 % at 55 °C
Operating Altitude	2000 m
Ambient Air Temperature For Operation	-2560 °C
Ambient Air Temperature For Storage	-4070 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	7.2 cm
Package 1 Length	7.5 cm
Package 1 Weight	0.478 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins