

# Product datasheet

Specifications



## Acti9 modular bell transformer iTR - 230 V 50..60 Hz - output 8 V - 4 VA

Local distributor code:

399362116

A9A15214

 **Discontinued on:** 15 Feb 2021

**EAN Code:** 3606480097867

 **Discontinued**

### Main

Range Of Product	Acti9
Product Name	Acti9 iTR
Product Or Component Type	Transformer
Device Short Name	iTR
Transformer Type	Bell transformer

### Complementary

[Ue] Rated Operational Voltage	230 V AC 50/60 Hz
Output Voltage	12 V: off load 8 V: +/- 15 % on load
Output Short-Circuit Protection	Built-in
Rated Power In Va	4 VA
Mounting Mode	Fixed
Mounting Support	35 mm symmetrical DIN rail
9 Mm Pitches	4
Height	89 mm
Width	36 mm
Depth	60 mm
Colour	White
Auxiliary Connection Terminal	Tunnel type terminalsrigid 2.5 mm² Tunnel type terminalsflexible 2.5 mm² Tunnel type terminalsflexible with ferrule 2.5 mm²
Wire Stripping Length	6 mm
Tightening Torque	0.5 N.m

### Environment

Standards	EN 61558-2-6 IEC 61558-2-6 EN 60742
Product Certifications	NF
Ip Degree Of Protection	IP20 conforming to IEC 60529
Overvoltage Category	Class II with terminal shields in option
Ambient Air Temperature For Operation	-20...55 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Storage	-25...80 °C
-------------------------------------	-------------

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4 cm
Package 1 Width	7 cm
Package 1 Length	9.5 cm
Package 1 Weight	232 g

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Sustainable Packaging

## Resource performance

✓ Sustainable Packaging

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins