

Product datasheet

Specifications



32A 250V 1 Gang Double Pole Switch with Neon, White

E8231D32N_WE

⚠ Discontinued on: 1 Nov 2020

⚠ Discontinued

Main

Range	Pieno
Product Or Component Type	Switch
Switch Application	Switch
Load Type	Resistive Fluorescent
Cover Frame Colour Tint	White

Complementary

Device Mounting	Surface Flush
Wiring Device Mounting	Flush Surface
Rated Current	32 A at 250 V AC 50 Hz
Local Signalling	Neon
Number Of Gangs	1 gang
Material	Polycarbonate: surround Polycarbonate: grid plate
Connections - Terminals	Pillar terminals
Clamping Connection Capacity	1 x 10 mm ² for solid cable(s)
Embedding Depth	23 mm
Width	87 mm
Height	87 mm
Depth	33.8 mm

Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Standards	MS IEC 60669-1 SS 227-1 IEC 60669-1 GB 16915.1 BS EN 60669-1

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	3.52 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	172.9 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	1.393 kg
Unit Type Of Package 3	CAR
Number Of Units In Package 3	80
Package 3 Height	32.5 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	13832 g

Contractual warranty

Warranty	18 months
----------	-----------