Product datasheet

Specifications





Circuit breaker, TeSys GB2, 1P, 1A, Icu 50kA at 240V, Thermal magnetic, DIN rail mounted

GB2CB06

Main

Range	TeSys
Product Name	TeSys GB2
Device Short Name	GB2
Product Or Component Type	Circuit breaker
Device Application	Control
Poles Description	1P
Network Type	AC/DC
Utilisation Category	Category A conforming to IEC 60947-2 DC-12 conforming to IEC 60947-5-1 DC-13 conforming to IEC 60947-5-1
Network Frequency	50/60 Hz conforming to IEC 60947-2
Breaking Capacity	50 kA Icu at 110 V AC 50/60 Hz conforming to IEC 60947-2 50 kA Icu at 230/240 V AC 50/60 Hz conforming to IEC 60947-2 1.5 kA Icu at 24 V DC conforming to IEC 60947-2 1 kA Icu at 48 V DC conforming to IEC 60947-2
[Ics] Rated Service Short-Circuit Breaking Capacity	25 % at 230/240 V AC 50/60 Hz conforming to IEC 60947-2 50 % at 110 V AC 50/60 Hz conforming to IEC 60947-2
Trip Unit Technology	Thermal-magnetic
Magnetic Tripping Current	14 A

Complementary

Mounting Mode	By clips
Mounting Support	Plate Rail
Mounting Position	Horizontal Vertical
Control Type	Toggle
[In] Rated Current	1 A
[Ue] Rated Operational Voltage	250 V AC 50/60 Hz conforming to IEC 60947-2 277 V AC 60 Hz conforming to CSA C22.2 No 235 277 V AC 60 Hz conforming to UL 1077 48 V DC
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to IEC 60947-2
Power Dissipation Per Pole	2 W
Mechanical Durability	8000 cycles
Electrical Durability	8000 cycles

Connections - Terminals	Connector 1 cable(s) 0.756 mm ² solid without cable end Connector 2 cable(s) 0.754 mm ² solid without cable end Connector 1 cable(s) 0.754 mm ² flexible with cable end Connector 2 cable(s) 0.752.5 mm ² flexible with cable end	
Tightening Torque	g Torque 1.2 N.m on connector	
Mechanical Robustness	Shocks: 22 Gn for 20 ms conforming to IEC 60068-2-27 Vibrations: 5 Gn, 5110 Hz conforming to IEC 60068-2-6	
Quantity Per Set	Set of 6	
9 Mm Pitches	2	
Height	74 mm	
Width	15 mm	
Depth	67 mm	

Environment

Standards	EN/IEC 60947-1 EN/IEC 60947-2 CSA C22.2 No 235 UL 1077	
Product Certifications	UL CSA	
Protective Treatment	TC	
Ip Degree Of Protection	IP20 conforming to IEC 60529	
Ambient Air Temperature For Operation	-2060 °C	
Ambient Air Temperature For Storage	nperature For -4080 °C	
Fire Resistance	960 °C conforming to IEC 60695-2-1	
Operating Altitude	3000 m	

Packing Units

PCE
1
1.500 cm
6.900 cm
7.400 cm
50.900 g
BB1
6
9.200 cm
10.200 cm
10.200 cm
332.000 g
S02
72
15.000 cm
30.000 cm
40.000 cm

2

Package 3 Weight

4.330 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations