# **Product datasheet**

Specification





# Power quality meter, PowerLogic PM8000, Standard, integrated display, 512 MB, 256 s/c

METSEPM8210

#### Main

Range	PowerLogic
Product Name	PowerLogic PM8000
Device Short Name	PM8210
Product Or Component Type	Power meter

Complementary	
Power Quality Analysis	conforming to EN 50160: 2010 compliance report
	conforming to IEEE 519: 2014 compliance report
	conforming to IEC 61000-4-30: class S power quality measurement
	up to the 63rd harmonic
	harmonic distortion
	waveform capture
	voltage sag and swell detection
	programmablity (logic and math functions)
	conforming to IEC 62586 power quality monitoring
	disturbance direction detection
	rapid voltage change
Device Application	Power monitoring
	WAGES metering
Type Of Measurement	Current
	Voltage
	Frequency
	Active and reactive power total
	Apparent power total
	Power factor total
	Active and reactive power per phase, rms
	Apparent power per phase, rms
	Power factor per phase, rms
Supply Voltage	2060 V DC +/- 10 %
Network Frequency	60 Hz
	50 Hz
[In] Rated Current	10 A
	5 A
	1 A
Poles Description	3P
	1P + N
	3P + N
Power Consumption In W	17 W
Display Type	Colour TFT LCD
Display Resolution	320 x 240 pixels QVGA
Sampling Rate	256 samples/cycle
Measurement Current	5010000 mA
Analogue Input Type	Voltage (impedance 5 MOhm)
	Current (impedance 0.3 mOhm)

Measurement Voltage	57400 V AC 4269 Hz between phase and neutral 100690 V AC 4269 Hz between phases
Frequency Measurement Range	4269 Hz
Number Of Inputs	3 digital 30 V AC 3 digital 60 V DC
Measurement Accuracy	Current +/- 0.1 % Voltage +/- 0.1 % Active energy +/- 0.2 %
Accuracy Class	Class 0.2S active energy conforming to IEC 62053-22 Class 0.2 active energy conforming to ANSI C12.20 Class 0.2 active power conforming to IEC 61557-12 Class 0.5S reactive energy conforming to IEC 62053-24 Class 0.5 power factor conforming to IEC 61557-12 Class 0.2 voltage conforming to IEC 61557-12 Class 0.2 current conforming to IEC 61557-12
Number Of Outputs	1 pulse
Information Displayed	Voltage Current Frequency Power Energy consumption Harmonic distortion
Communication Port Protocol	Modbus RTU at 115 kbauds - 2-wire ION at 115 kbauds - 2-wire DNP3 IEC 61850 Modbus TCP/IP Ethernet Modbus TCP/IP daisy chain at 10/100 Mbit/s RSTP 801.1d 2004
Communication Port Support	ETHERNET Screw terminal block: RS485
Communication Network Type	IPv6 (internet protocol)
Data Recording	Data logs Harmonics logs Waveform logs Min/max of instantaneous values Trending/forecasting Sag and swell logs Sequence of event recording GPS synchronisation Alarm logs Event logs Time stamping 50 data recorders
Memory Capacity	512 MB
Web Services	Customizable home page File upload/download via FTP File upload/download via SFTP Web server Alarm notification by e-mail Viewing of captured waveform (FTP) Viewing of captured waveform (web) HTTPS server
Communication Service	NTP time synchronization SMTP e-mail notification DHCP RSTP support SNMP PTP time synchronization
Cybersecurity	Syslog protocol support Password protection Port hardening Enable/disable communication ports Robust security logs
Mounting Mode	Flush-mounted

Mounting Support	Framework
Installation Category	III
Safety Construction	III400690 V conforming to IEC 61010-1:ed. 3 III400690 V conforming to EN 61010-1:ed. 3 III347600 V conforming to UL 61010-1:ed. 3 III347600 V conforming to CSA C22.2 No 61010-1:ed. 3
Standards	IEC 62052-11 IEC 61557-12 IEC 62053-22 IEC 62053-24 IEEE 1588 IEC 62586-2 IEC 61326-1
Product Certifications	CE CULus N998
Width	96 mm
Depth	77.5 mm
Height	96 mm
Net Weight	581 g

#### **Environment**

Electromagnetic Compatibility	Electrostatic discharge conforming to IEC 61000-4-2 Radiated radio-frequency electromagnetic field immunity test conforming to IEC 61000-4-3 Electrical fast transient/burst immunity test conforming to IEC 61000-4-4 Surge immunity test conforming to IEC 61000-4-5 Conducted RF disturbances conforming to IEC 61000-4-6 Magnetic field at power frequency conforming to IEC 61000-4-8 Voltage dips and interruptions immunity test conforming to IEC 61000-4-11 Immunity to impulse waves conforming to IEC 61000-4-12 Conducted and radiated emissions conforming to EN 55022 Conducted and radiated emissions conforming to EN 55011 Conducted and radiated emissions conforming to FCC part 15 Conducted and radiated emissions conforming to ICES-003 Conducted RF disturbances (2150 Hz) conforming to CLC/TR 50579 Surge withstand conforming to IEEE C37.90.1
Ip Degree Of Protection	IP54 front: conforming to IEC 60529 IP30 body: conforming to IEC 60529
Relative Humidity	595 %
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-4085 °C
Operating Altitude	3000 m

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14 cm
Package 1 Width	14 cm
Package 1 Length	18.5 cm
Package 1 Weight	0.954 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	8
Package 2 Height	30 cm

Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	8.073 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	32
Package 3 Height	45 cm
Package 3 Width	80 cm
Package 3 Length	60 cm
Package 3 Weight	40.792 kg



Green Premium<sup>TM</sup> label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Rohs Exemption Information

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information