

Product datasheet

Specifications



standard digital input kit STB - 115 V AC - 2 I

STBDAI5260K

Main

Range Of Product	Modicon STB distributed I/O solution
Product Or Component Type	Standard digital input kit
Kit Composition	STBXTS1110, 5-terminal screw type connector STBXTS2110, 5-terminal spring clamp connector STBXBA2000 base STBDAI5260 module
Discrete Input Number	2
Discrete Input Voltage	115 V
Discrete Input Voltage Type	AC

Complementary

Input Voltage Limits	0...20 V at state 0 74...132 V at state 1
Permissible Voltage	132 V
Absolute Maximum Voltage	200 V 20 ms
Network Frequency	50/60 Hz
Network Frequency Limits	47...63 Hz
Current State 0 Guaranteed	<= 2 mA
Current State 1 Guaranteed	>= 4 mA
Discrete Input Logic	Positive or negative
Response Time	1.5 ms off-to-on 1.5 ms on-to-off
Protection Type	Input protection metal oxide varistor limited Power protection external fuse 0.5 A
Insulation Between Channels	1780 V for 1 minute
Insulation Between Channels And Logic Bus	1780 V for 1 minute
Cold Swapping	Yes
Hot Swapping	Yes for standard NIMs
Product Compatibility	I/O base STBXBA2000 Power distribution module STBPDT2100/2105
[Us] Rated Supply Voltage	115/230 V AC
Supply	Power distribution module
Current Consumption	45 mA at 5 V DC for logic bus
Marking	CE

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Overvoltage Category	II
Status Led	1 LED (green) module status (RDY) 1 LED per channel (green) channel status (IN1 to IN2) 1 LED (red) module error (ERR)
Depth	65.1 mm
Height	18.4 mm
Width	125 mm
Net Weight	0.065 kg

Environment

Standards	EN/IEC 61131-2 type 1
Product Certifications	FM Class 1 Division 2 UL CSA
Pollution Degree	2 conforming to IEC 60664-1
Operating Altitude	<= 2000 m
Ip Degree Of Protection	IP20 conforming to IEC 61131-2 class 1
Ambient Air Temperature For Operation	0...60 °C (without derating)
Ambient Air Temperature For Operation	32...140 °F without derating
Ambient Air Temperature For Storage	-40...85 °C without derating
Ambient Air Temperature For Storage	-40...185 °F without derating
Relative Humidity	95 % at 60 °C without condensation
Vibration Resistance	3 gn at 58...150 Hz on 35 x 7.5 mm symmetrical DIN rail 5 gn at 58...150 Hz on 35 x 15 mm symmetrical DIN rail +/-0.35 mm at 10...58 Hz
Shock Resistance	30 gn for 11 ms conforming to IEC 88 reference 2-27

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	8.0 cm
Package 1 Length	13.0 cm
Package 1 Weight	138.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	28
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	4.29 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	448
Package 3 Height	60.0 cm

Package 3 Width	80.0 cm
Package 3 Length	448.0 cm
Package 3 Weight	61.824 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)


[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Dimensions Drawings

Dimensions




Connections and Schema

Wiring Diagram

Example

2 two-wire sensors



Pin	Top Connector	Bottom Connector
1	115 VAC source power 1 (to the module)	115 VAC source power 2 (to the module)
2	sensor power 1	sensor power 2
3	input from sensor 1	input from sensor 2
4	field power neutral 1 (to the module)	field power neutral 2 (to the module)
5	protective earth	protective earth