Product datasheet

Specification





discrete input module, Modicon TM3, 16 inputs, screw, 24V DC

TM3DI16

Main

Range Of Product	Madiana TMO
nange of Froduct	Modicon TM3
Product Or Component Type	Discrete input module
Range Compatibility	Modicon M241
	Modicon M251
	Modicon M221
	Modicon M262
Discrete Input Number	16 for input conforming to IEC 61131-2 type 3
Discrete Input Logic	Sink or source (positive/negative)
Discrete Input Voltage	24 V
Discrete Input Current	7 mA for input

Complementary

Complementary	
Discrete I/O Number	16
Current Consumption	40 mA at 5 V DC via bus connector (at state on) 5 mA at 5 V DC via bus connector (at state off) 0 mA at 24 V DC via bus connector (at state on) 0 mA at 24 V DC via bus connector (at state off)
Discrete Input Voltage Type	DC
Voltage State 1 Guaranteed	1528.8 V for input
Current State 1 Guaranteed	>= 2.5 mA (input)
Voltage State 0 Guaranteed	05 V for input
Current State 0 Guaranteed	<= 1 mA (input)
Input Impedance	3.4 kOhm
Response Time	4 ms (turn-on) 4 ms (turn-off)
Local Signalling	1 LED per channel (green) for input status
Electrical Connection	10 x 1.5 mm² removable screw terminal block with pitch 3.81 mm adjustment for inputs
Maximum Cable Distance Between Devices	Unshielded cable: <50 m for regular input
Insulation	Between input and internal logic at 500 V AC Non-insulated between inputs
Marking	CE
Mounting Support	Top hat type TH35-15 rail conforming to IEC 60715 Top hat type TH35-7.5 rail conforming to IEC 60715 plate or panel with fixing kit
Height	90 mm

Depth	84.6 mm
Width	27.4 mm
Net Weight	0.1 kg

Environment

Standards	IEC 61131-2
Product Certifications	CE
	cULus
	UKCA
	RCM
	EAC
	cULus HazLoc
Resistance To Electrostatic	8 kV in air conforming to IEC 61000-4-2
Discharge	4 kV on contact conforming to IEC 61000-4-2
Resistance To Electromagnetic	10 V/m 80 MHz1 GHz conforming to IEC 61000-4-3
Fields	3 V/m 1.4 GHz2 GHz conforming to IEC 61000-4-3
	1 V/m 2 GHz3 GHz conforming to IEC 61000-4-3
Daniatawaa Ta Maswatia Fialda	<u> </u>
Resistance To Magnetic Fields	30 A/m 50/60 Hz conforming to IEC 61000-4-8
Resistance To Fast Transients	1 kV for I/O conforming to IEC 61000-4-4
Surge Withstand	1 kV I/O common mode conforming to IEC 61000-4-5 DC
Resistance To Conducted	10 V 0.1580 MHz conforming to IEC 61000-4-6
Disturbances	3 V spot frequency (2, 3, 4, 6.2, 8.2, 12.6, 16.5, 18.8, 22, 25 MHz) conforming to
	Marine specification (LR, ABS, DNV, GL)
Electromagnetic Emission	Radiated emissions - test level: 40 dBµV/m QP class A (10 m) at 30230 MHz
	conforming to IEC 55011
	Radiated emissions - test level: 47 dBµV/m QP class A (10 m) at 2301000 MHz
	conforming to IEC 55011
Ambient Air Temperature For	-1035 °C vertical installation
Operation	-1055 °C horizontal installation
Ambient Air Temperature For	-2570 °C
Storage	40.050/ 31.4
Relative Humidity	1095 %, without condensation (in operation)
	1095 %, without condensation (in storage)
Ip Degree Of Protection	IP20 with protective cover in place
Pollution Degree	2
Operating Altitude	02000 m
Storage Altitude	03000 m
Vibration Resistance	3.5 mm at 58.4 Hz on DIN rail
	3 gn at 8.4150 Hz on DIN rail
	3.5 mm at 58.4 Hz on panel
	3 gn at 8.4150 Hz on panel
Shock Resistance	15 gn for 11 ms

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.345 cm
Package 1 Width	10.498 cm
Package 1 Length	12.471 cm
Package 1 Weight	210.8 g
Unit Type Of Package 2	S04

Number Of Units In Package 2	42
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	10.5 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	504
Package 3 Height	105 cm
Package 3 Width	120 cm
Package 3 Length	80 cm
Package 3 Weight	132 kg



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
②	Rohs Exemption Information Yes
⊘	Pvc Free


Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

25 Apr 2024

Dimensions Drawings

Dimensions





(*) 8.5 mm/0.33 in. when the clamp is pulled out.

TM3DI16


Mounting and Clearance

Spacing Requirements







Mounting on a Rail



Incorrect Mounting




Mounting on a Panel Surface



(1) Install a mounting strip


Mounting Hole Layout



Connections and Schema

Digital Input Module (16-channel, 24 Vdc)

Wiring Diagrams



The 4 COM terminals are connected internally

- (A) Sink wiring (positive logic)
- (B) Source wiring (negative logic)