# **Product datasheet**

Specifications





### energy sensor, PowerTag Monoconnect 63A 1P+N top position

Local distributor code: 404618975

A9MEM1521

EAN Code: 3606480909139

### Main

IVIAIII	
Range Of Product	PowerLogic
Product Name	PowerTag A9 M63
Product Or Component Type	Energy sensor
Poles	1P + N
Maximum Current [Imax]	63 A
[lb] Basic Current	10 A
Starting Current	40 mA
Saturation Current	130 A
Product Specific Application	Overload alarm Cost allocation Circuit monitoring Load monitoring Energy management
Concentrator Compatibility	Acti9 Smartlink SI B Acti9 Smartlink SI D Acti9 PowerTag Link C Acti9 PowerTag Link Acti9 PowerTag Link Wiser IP module EcoStruxure Panel Server Universal EcoStruxure Panel Server Advanced PrismaSet Active
Range Compatibility	Acti 9 Acti9 iKQE RCBO Multi9 Multi9 C60 Multi9 Multi9 ID Multi9 Multi9 C32N Multi9 Multi9 C65 Acti 9 Acti9 iID Acti 9 Acti9 iID K Acti 9 Acti9 iK60 Acti 9 Acti9 iKQ Acti 9 Acti9 iKQ Acti 9 Acti9 iKO Acti 9 Acti9 iC65 Acti 9 Acti9 iC65 Acti 9 Acti9 iC65 Acti 9 Acti9 iC65 Acti 9 Acti9 iC60 single terminal
Type Of Measurement	Power factor Current Active energy Active power Voltage
Accuracy Class	Class 1 current conforming to IEC 61557-12 Class 0.5 voltage conforming to IEC 61557-12 Class 1 active power conforming to IEC 61557-12 Class 1 active energy conforming to IEC 61557-12 Class 1 power factor conforming to IEC 61557-12
Mounting Location	Тор

Mounting Support	On circuit breaker	
Product Destination	Switchboard	
Event Management	Voltage loss with measured current at voltage loss	
Transmission Support Medium	Radio frequency 2.42.4835 GHz conforming to IEEE 802.15.4	
Emission Power	10 mW	

# Complementary

Mounting Mode	By screws (terminals)	
Electrical Connection (Voltage Sensing & Power Supply)	Connector tooth	
Cable Cross Section	1 rigid cable 1.516 mm² 2 stranded cable 1.52.5 mm² 2 rigid cable 1.52.5 mm² 1 stranded cable 1.516 mm²	
Supply Voltage	200240 V AC, +/- 20 %	
Network Frequency	50 Hz 60 Hz	
Maximum Power Consumption	1 VA	
Standards	IEC 61557-12 IEC 61010-1 IEC 61010-2-030 IEC 61326-1 ETSI EN 300 328 ETSI EN 301 487-1	
Height	16.5 mm	
Width	36 mm	
Depth	43 mm	
Net Weight	17.5 g	
Colour	White (RAL 9003)	

#### **Environment**

Quality Labels	CE	
Directives	2014/53/EU - radio equipment directive	
Operating Altitude	02000 m	
Ambient Air Temperature For Operation	-2560 °C	
Ambient Air Temperature For Storage	-4085 °C	
Overvoltage Category	III conforming to IEC 61010-1	
Measurement Category	Category III conforming to IEC 61010-2-030	
Ip Degree Of Protection	IP20 conforming to IEC 60529	
Ik Degree Of Protection	IK05	
Pollution Degree	3	
Relative Humidity	095 % at 45 °C conforming to IEC 60721-3-3	
Vibration Resistance	3M4 conforming to IEC 60721-3-3	
Electromagnetic Compatibility	Industrial electromagnetic environment conforming to IEC 61326-1 Radiated EMC conforming to ETSI EN 301 489-17 Electromagnetic emission conforming to IEC 62311	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	6.000 cm
Package 1 Length	8.500 cm
Package 1 Weight	47.000 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	48
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	2.500 kg

### **Contractual warranty**

Warranty

### Sustainability Screen Premium\*

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

19 Apr 2024