Product datasheet

Specification





Communication Module. EcoStruxure I/O Smart Link, Modbus, RS485

Local distributor code: 399369915

A9XMSB11

EAN Code: 3606480430602

Main

Range Of Product	EcoStruxure	
Product Name	EcoStruxure I/O Smart Link	
Product Or Component Type	Smart communication module	
Device Short Name	I/O Smart Link	
Application Type	Load control Breaker status monitoring Basic energy metering E	
Number Max Of Connected Devices	Up to 11 wired devices	
Group Of Channels	1 group of 11 digital channels	
Maximum Supply Current	1.5 A	
[Us] Rated Supply Voltage	24 V DC +/- 20 %	
Connectivity To Devices	Digital input and output Pulse output meter	
Communication Service	Modbus server for RS485	
Web Server	BMS controller compatible	
Web Services	Web page	

Complementary

Application Specific I/O	Pulse totalising counter Pulse converter
Protection Type	Against reverse polarity for auxiliary supply
	Against reverse polarity for input
	Overvoltage at 33 V DC for digital output
Immunity To Microbreaks	10 ms
Reset	Factory reset on front face
	By booted push-button
	By address encoder
	By plug in, plug out the power supply
Input/Output Type	2 inputs + 1 output per digital channel
Input Type	Current sink for digital input, 24 V DC +/- 20 % at 2.5 mA
Maximum Permanent Current	5 mA for digital input
Electronic Filtering Time	2 ms for digital input from state 0 to state 1
Output Type	Logic current source: 24 V - DC - 100 mA
Maximum Voltage Drop	<1 V at state 1 digital output
Inrush Current	0.5 A for digital output
	7 A for power supply

Local Signalling	Communication: 1 LED (yellow) Status: 1 LED (green, orange and red)
Tuno Of Sotting	
Type Of Setting	Modbus address 0199 for address encoders Reset for address encoders
	Reset for plug in, plug out the auxiliary supply
Mounting Position	Horizontal and vertical on DIN rail
Colour	White (RAL 9003)
Location Of Connection	Front
Connections - Terminals	Spring-loaded terminal Ti24 qty: 11 for digital input/output, ordered separately
	Plug-in connector qty: 1 for supply circuit Plug-in connector qty: 1 for communication bus
Clamping Connection Capacity	2 x 0.22 x 1.5 mm² for twisted shielded pairs cable, flexible with cable end for
	communication bus $2 \times 0.22 \times 1.5 \text{ mm}^2$ for twisted shielded pairs cable, flexible without cable end for
	communication bus 2 x 0.22 x 1.5 mm² for twisted shielded pairs cable, rigid with cable end for
	communication bus
	2 x 0.22 x 1.5 mm² for twisted shielded pairs cable, rigid without cable end for communication bus
	1 x 0.21 x 1.5 mm², flexible with cable end for control
	1 x 0.21 x 1.5 mm², flexible without cable end for control 1 x 0.21 x 1.5 mm², rigid with cable end for control
	1 x 0.21 x 1.5 mm², rigid without cable end for control
	2 x 0.22 x 1.5 mm², flexible with cable end for supply circuit
	2 x 0.22 x 1.5 mm², flexible without cable end for supply circuit 2 x 0.22 x 1.5 mm², rigid with cable end for supply circuit
	2 x 0.22 x 1.5 mm², rigid with cable end for supply circuit
Wire Stripping Length	Control: 10 mm
	Supply circuit: 7 mm
	Communication bus: 7 mm
Communication Network Type	RS485 Modbus RTU client/server SUB-D 9 4800 bps, 9600 bps, 19200 bps, 38.4 Kbps
9 Mm Pitches	0 useful
Height	22.5 mm
Width	359 mm
Depth	42 mm
Net Weight	188 g
Provided Equipment	Set of 1 bus connector
	Set of 1 power supply connector Set of 2 locking clips
Range Compatibility	Acti 9 iTL auxiliary
go companion.y	Linergy Linergy FM
	Acti 9 iOF+SD 24
	Acti 9 iACT24 Acti 9 iATL24
	PowerLogic pulse output meter
	Acti 9 RCA iC60
	Acti 9 Acti9 iCT auxiliary Acti 9 Acti9 iC60
	Acti 9 Acti9 iID
	Acti 9 Acti9 iSW-NA
	Acti 9 Acti9 iDPN Vigi
	Acti 9 Acti9 C40 Multi9 Multi9 C60
	Acti 9 Acti9 DT40
	Acti 9 Acti9 DT60
	Acti 9 Acti9 I-NA
	Acti 9 Acti9 ITG40 Acti 9 Acti9 iDPN
	Acti 9 Acti9 Reflex iC60 Ti24 connector
Commissioning Interface	EcoStruxure Power Commission
	Web page

Market Segment	Buildings Small commercial
Compatibility Code	Acti 9 Smartlink
	

Environment

Ip Degree Of Protection	IP20	
Ik Degree Of Protection	IK06 conforming to IEC 62262	
Pollution Degree	3	
Electromagnetic Compatibility	Resistance to electrostatic discharge (air discharge), class B, 8 kV, conforming to IEC 61000-4-2 Resistance to electrostatic discharge (contact discharge), class B, 4 kV, conforming to IEC 61000-4-2 Resistance to radiated electromagnetic fields (80 MHz3 GHz), class A, 10 V/m, conforming to IEC 61000-4-3 Power supply: resistance to radiated electromagnetic fields (1.46 GHz), class A, 3 V/m, conforming to IEC 61000-4-3 Power supply: resistance to fast transient (5100 kHz), class B, 2 kV, conforming to IEC 61000-4-4 Input/output: resistance to fast transient, class B, 1 kV, conforming to IEC 61000-4-4 Communication bus: resistance to fast transient (0.1580 MHz), class B, 1 kV, conforming to IEC 61000-4-4 Conducted EMC (0.1580 MHz), class A, 3 V, conforming to IEC 61000-4-6 Conducted emission (0.1530 MHz), class B, conforming to IEC 61026-1 Conducted emission (0.1530 MHz), class B, conforming to IEC 61326-1 Radiated emission (306000 MHz), class B, conforming to IEC 61326-1 Radiated emission (306000 MHz), class B, conforming to IEC 61326-1 Radiated emission (306000 MHz), class B, conforming to IEC 61326-1 Power supply: surges (DM coupling 42 Ohm), class B, 1 kV, conforming to IEC 61000-4-5 Power supply: surges (CM coupling 42 Ohm), class B, 1 kV, conforming to IEC 61000-4-5 Communication bus: surges (CM coupling 2 Ohm), class B, 1 kV, conforming to IEC 61000-4-5	
Environmental Characteristic	Corrosive 3C2 conforming to IEC 60721-3-3 Salt mist 2 conforming to IEC 60068-2-52	
Vibration Resistance	1 gn, amplitude = 3.5 mm (f = 5300 Hz)10 cycles conforming to EN/IEC 60068-2-6	
Shock Resistance	15 gn for 11 ms conforming to IEC 60068-2-27	
Fire Resistance	Other parts: 650 °C (30 s) conforming to IEC 60695-2-10 On connection terminals: 960 °C (30 s) conforming to IEC 60695-2-10	
Tropicalisation	2	
Relative Humidity	093 % at 40 °C	
Operating Altitude	02000 m	
Ambient Air Temperature For Operation	-2560 °C	
Ambient Air Temperature For Storage	-4085 °C	
Standards	IEC 61010-2-201 IEC 61010-1	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.4 cm
Package 1 Width	6.4 cm
Package 1 Length	36.4 cm
Package 1 Weight	271.0 g
Unit Type Of Package 2	S03

Number Of Units In Package 2	32
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	9.063 kg

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information