

Product datasheet

Specifications



rectified and filtered power supply - 3-phase - 400 V AC - 24 V - 30 A

Local distributor code:
389706766

ABL8TEQ24300

⚠ To be discontinued on: 30 May 2024

⚠ To be end-of-service on: 30 May 2025

⚠ Discontinued

EAN Code: 3389119401395

Main

Range Of Product	Modicon Rectified
Product Or Component Type	Power supply
Power Supply Type	Rectified and filtered
Rated Power In W	720 W
Nominal Input Voltage	400 V AC three phase, terminal(s): L1, L2, L3
Output Voltage	24 V DC
Power Supply Output Current	30 A
Anti-Harmonic Filter	Low frequency harmonic currents
Product Certifications	UL 508 cULus KC EAC

Complementary

Network Frequency Limits	47...63 Hz
Input Voltage Limits	360...440 V
Power Factor	0.835 at 400 V
Efficiency	77 %
Power Dissipation In W	165 W
Output Coupling	Series Parallel
Output Protection Type	Against overvoltage, protection technology: 2 J peak limiter Against overload and short-circuits, protection technology: external fuse, 40 A
Hold-Up Time	7 ms
Status Led	1 LED (green) output voltage
Connections - Terminals	For input ground connection: screw type terminals, connection capacity: 1 x 2.5...1 x 4 mm² AWG 14...AWG 11 For input connection: screw type terminals, connection capacity: 9 x 2.5...9 x 4 mm² AWG 14...AWG 11 For output connection: screw type terminals, connection capacity: 4 x 10...4 x 16 mm² AWG 8...AWG 6
Depth	247.0 mm
Height	107.0 mm
Width	240 mm
Net Weight	13.24 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Compatibility Code	ABL8T
--------------------	-------

Environment

Ip Degree Of Protection	IP20 conforming to EN/IEC 60529
Ambient Air Temperature For Operation	-20...55 °C
Ambient Air Temperature For Storage	-40...80 °C
Relative Humidity	0...95 % without condensation or dripping water
Operating Altitude	3000 m
Safety Class	Class I conforming to VDE 0106-1
Dielectric Strength	2000 V between input and ground 4600 V between input and output 500 V between output and ground
Other Environmental Characteristic	EMC conforming to IEC 62041 Safety conforming to EN/IEC 61558-2-6 Safety conforming to UL 508 Safety conforming to UL 60950-1 EMC conforming to EN/IEC 61000-3-2

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	25.700 cm
Package 1 Width	34.800 cm
Package 1 Length	35.300 cm
Package 1 Weight	14.402 kg
Unit Type Of Package 2	P06
Number Of Units In Package 2	4
Package 2 Height	75.000 cm
Package 2 Width	60.000 cm
Package 2 Length	80.000 cm
Package 2 Weight	66.108 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance


✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Pvc Free	

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Dimensions Drawings

Dimensions



Dimensions in mm


a	b	c	G	J	Ø
240	252	108	220	87	8

Dimensions in in.

a	b	c	G	J	Ø
9.45	9.92	4.25	8.66	3.42	0.31


Connections and Schema

Internal Wiring Diagram



Performance Curves

Load Limits Curve



- (1) Nominal line supply + 10%
- (2) Nominal line supply
- (3) Nominal line supply - 10%