

Main

Range of product	Modicon Transformer Economic
Product or component type	Safety and isolation transformer
Rated power in VA	40 VA
Input voltage	230 V AC phase to phase, terminal(s): L1-L2 230 V AC single phase, terminal(s): N-L1
Output voltage	24 V AC
Secondary winding	Single
Protective cover	Without
Ambient air temperature for operation	-20...40 °C

Complementary

Input voltage limits	207...253 V
Network frequency limits	47...63 Hz
Input voltage tolerance	+/- 15 V
Efficiency	74 %
Power dissipation in W	14.1 W
Voltage variation at nominal load	0,135 at 230 V
Output sustained overvoltage	0,155 (no load, hot state)
Maximum voltage drop at rated load	15.8 %
No load losses	3.8 W
Short-circuit voltage	16 %
Output protection type	Against overload, protection technology: external Against overvoltage, protection technology: external Against short-circuits, protection technology: external
Connections - terminals	For input connection: screw type terminals, connection capacity: 4 x 2.5...4 x 4 mm ² AWG 14...AWG 11 For input ground connection: screw type terminals, connection capacity: 1 x 2.5...1 x 4 mm ² AWG 14...AWG 11

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

For output connection: screw type terminals, connection capacity: 2 x 2.5...2 x 4 mm² AWG 14...AWG 11

Marking	CE
Fixing mode	By 4 screws diameter: 5 mm on vertical panel, operating position: vertical By 4 screws diameter: 5 mm on horizontal panel with derating to 90 %, operating position: horizontal By clips (with mounting plate) on 35 mm symmetrical DIN rail By 4 screws diameter: 5 mm on vertical panel
Operating altitude	3000 m
Electrical insulation class	Class B
Width	79.0 mm
Height	70.0 mm
Depth	90.0 mm
Product weight	1.02 kg

Environment

Product certifications	EAC DNV-GL
IP degree of protection	IP20
Environmental characteristic	EMC conforming to EN 62041 Safety conforming to EN 61558-1 Safety conforming to EN 61558-2-6
Ambient air temperature for storage	-40...80 °C
Relative humidity	0...95 % during operation
Overvoltage category	Class I conforming to VDE 0106-1
Dielectric strength	3200 V between input and ground 3200 V between output and ground 5100 V between input and output

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1.21 kg
Package 1 Height	12.6 cm
Package 1 width	14.8 cm
Package 1 Length	18 cm
Unit Type of Package 2	P06
Number of Units in Package 2	57
Package 2 Weight	83.05 kg
Package 2 Height	73.5 cm
Package 2 width	60 cm
Package 2 Length	80 cm


Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Dimensions




Dimensions in mm

a	b	c	G	J	Ø
79	90	70	56	48	4.8


Dimensions in in.

a	b	c	G	J	Ø
3.11	3.54	2.76	2.20	1.89	0.19

Internal Scheme



Primary Voltage Wiring



Secondary Voltage Wiring

