

Product datasheet

Specifications



voltage transformer - 230..400 V - 2 x 115 V - 630 VA



Local distributor code: 389707066 ABT7PDU063G

Main

Range of product	Modicon Transformer Universal
Product or component type	Safety and isolation transformer
Rated power in VA	630 VA
Input voltage	230 V AC single phase, terminal(s): N-L1 400 V AC phase to phase, terminal(s): L1-L2
Output voltage	115/230 V AC
Secondary winding	Double
Protective cover	Without
Ambient air temperature for operation	-20...60 °C

Complementary

Input voltage limits	360...440 V 207...253 V
Network frequency limits	47...63 Hz
Input voltage tolerance	+/- 15 V
Efficiency	90 %
Power dissipation in W	70 W
Voltage variation at nominal load	0,0358 at 230 V 0,0417 at 400 V
Output sustained overvoltage	0,049 (no load, hot state)
Maximum voltage drop at rated load	4.89 %
No load losses	23.55 W
Short-circuit voltage	0,048
Output protection type	Against overload, protection technology: external Against overvoltage, protection technology: external Against short-circuits, protection technology: external
Connections - terminals	For input connection: screw type terminals, connection capacity: 5 x 4 mm ² AWG 11 For input ground connection: screw type terminals, connection capacity: 1 x 4 mm ² AWG 11 For output connection: screw type terminals, connection capacity: 6 x 4 mm ² AWG 11
Marking	CE
Fixing mode	By 4 screws diameter: 7 mm on vertical panel, operating position: horizontal By 4 screws diameter: 7 mm on vertical panel, operating position: vertical By 4 screws diameter: 7 mm on horizontal panel with derating to 90 %

Output coupling	Parallel Series by internal jumper Grounding of secondary
Operating altitude	3000 m
Electrical insulation class	Class F
Width	150.0 mm
Height	113.0 mm
Depth	145.0 mm
Net weight	7.86 kg

Environment

Product certifications	EAC UR DNV-GL
Standards	UL 506
IP degree of protection	IP20
Environmental characteristic	EMC conforming to EN 62041 Safety conforming to EN 61558-1 Safety conforming to EN 61558-2-4
Ambient air temperature for storage	-40...80 °C
Relative humidity	0...95 % during operation
Overvoltage category	Class I conforming to VDE 0106-1
Dielectric strength	3200 V between input and ground 3200 V between output and ground 5100 V between input and output

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	8.113 kg
Package 1 Height	19 cm
Package 1 width	19.5 cm
Package 1 Length	26.5 cm
Unit Type of Package 2	P06
Number of Units in Package 2	21
Package 2 Weight	183.37 kg
Package 2 Height	73.5 cm
Package 2 width	60 cm
Package 2 Length	80 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration


Environmental Disclosure [Product Environmental Profile](#)

PVC free Yes

Contractual warranty

Warranty 18 months

Dimensions




Dimensions in mm

a	b	c	G	J	Ø
150	145	113	122	90.6	7


Dimensions in in.

a	b	c	G	J	Ø
5.91	5.71	4.45	4.80	3.57	0.27

Internal Scheme



Primary Voltage Wiring



Secondary Voltage Wiring

