Product datasheet

Specifications





circuit breaker, EasyPact EZS100E with TMD trip unit, 32A, 3P/3d

EZS100E3032

Main

Range Of Product	EasyPact EZS
Product Or Component Type	Circuit breaker
Device Short Name	EZS100E
Circuit Breaker Application	Distribution
Poles Description	3P
Protected Poles Description	3D
Breaking Capacity Code	E
Control Type	Toggle
Network Type	AC
Network Frequency	50/60 Hz
Upside Connection	Front
Downside Connection	Front
[In] Rated Current	32 A at 40 °C

Complementary

[Ui] Rated Insulation Voltage	690 V conforming to EN/IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to EN/IEC 60947-2
[Ue] Rated Operational Voltage	440 V AC 50/60 Hz conforming to EN/IEC 60947-2 400 V AC 50/60 Hz conforming to GB 14048.2
Neutral Position	Left
Mounting Mode	Fixed
Mounting Support	Backplate
Connection Pitch	25 mm
Breaking Capacity	50 kA Icu at 220/240 V AC 50/60 Hz conforming to EN/IEC 60947-2 25 kA Icu at 380/400 V AC 50/60 Hz conforming to EN/IEC 60947-2 25 kA Icu at 415 V AC 50/60 Hz conforming to EN/IEC 60947-2 17 kA Icu at 440 V AC 50/60 Hz conforming to EN/IEC 60947-2 40 kA Icu at 200/230 V AC 50/60 Hz conforming to GB 14048.2 25 kA Icu at 380/400 V AC 50/60 Hz conforming to GB 14048.2
[lcs] Rated Service Breaking Capacity	25 kA at 220/230 V AC 50/60 Hz conforming to GB 14048.2 13 kA at 380/400 V AC 50/60 Hz conforming to GB 14048.2 25 kA at 220/240 V AC 50/60 Hz conforming to EN/IEC 60947-2 15 kA at 380/400 V AC 50/60 Hz conforming to EN/IEC 60947-2
Suitability For Isolation	Yes
Utilisation Category	Category A

Mechanical Durability	13000 cycles conforming to EN/IEC 60947-2 20000 cycles conforming to GB 14048.2
Electrical Durability	4000 cycles 415 V In/2 conforming to EN/IEC 60947-2 8000 cycles 400 V In conforming to GB 14048.2
Protection Type	Overload protection (thermal) Short-circuit protection (magnetic)
Trip Unit Name	TM-D
Trip Unit Technology	Thermal-magnetic
Trip Unit Rating	32 A at 40 °C
Long Time Pick-Up Adjustment Type Ir	Fixed
Long Time Pick-Up Adjustment Range	1 ln
Long Time Delay Adjustment Type	Fixed
Instantaneous Pick-Up Adjustment Type Ii	Fixed
Integral Instant Protection	300 kA

Environment

Standards	EN 60947-2 IEC 60947-2
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 62262
Pollution Degree	3 conforming to IEC 60947-1
Ambient Air Temperature For Operation	-3570 °C
Ambient Air Temperature For Storage	-5085 °C
Height	130 mm
Width	75 mm
Depth	60 mm
Net Weight	0.78 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.979 cm
Package 1 Width	11.845 cm
Package 1 Length	15.807 cm
Package 1 Weight	869 a



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information