Product datasheet

Specifications





Socket, Vivace, universal, 3pin, 13A, 250V, 2 gangs, white

KBT413S_WE

Main

Range	Vivace
Product Or Component Type	Socket-outlet
Device Short Name	КВТ
Device Application	Power supply
Device Presentation	Complete mechanism
Outlet Standard	Universal
Colour Tint	White
Type Of Packing	Plastic bag
Socket Number	2
Rated Current	13 A
Colour Tint	Wall: white

Complementary

Integrated Connection Type	2 socket-outlet 220250 V AC, maximum load current: 13 A
Outlet Standard	Universal
Outlet Poles Configuration	2 x 2P + E with shutters
Number Of Gangs	2 gangs
Material	Polycarbonate: grid plate Polycarbonate: surround Nylon: base
Projecting Depth	8 mm
Device Mounting	Flush
Mounting Support	Wall mounted
Fixing Mode	By screws
Fixing Center	120.6 mm
Embedding Depth	25 mm
Rated Current	13 A at 250 V AC, resistive
[Ue] Rated Operational Voltage	220240 V
Network Frequency	50/60 Hz
Network Type	AC
Contacts Material	Brass and phosphor bronze
Connections - Terminals	Screw terminals

4	
Terminal Identifier	L
	Ν
	E
Tightening Torque	0.4 N.m
Clamping Connection Capacity	2.5 mm ²
	4 mm²
Width	146 mm
Surface Treatment	Untreated
Height	86 mm
Surface Finish	Glossy
Depth	33 mm
•	
Number Of Terminals	6
	-
Clamping Connection Capacity	1 x 2.53 x 2.5 mm ² for rigid or stranded cable(s)
, ,	

Environment

Ambient Air Temperature For Operation	-540 °C
Ambient Air Temperature For Storage	-560 °C
Relative Humidity	095 %
Operating Altitude	02000 m
Environmental Characteristic	Indoor use
Ip Degree Of Protection	IP20

Packing Units

PCE
1
8.6 cm
3 cm
14.6 cm
203.8 g
BB1
6
9.5 cm
15 cm
19 cm
1.293 kg
CAR
60
21 cm
31.5 cm
50 cm
12479 g

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations