Product datasheet





Circuit breaker, ComPact NSX160F AC/DC, 18kA/240VAC, TMD trip unit 160A, 1 pole 1d

LV438670

! Discontinued on: Jun 9, 2022 AD

! Discontinued

Main

Mani	
Range	ComPact
Product Name	ComPact NSX
Range Of Product	ComPact NSX100250 DC ComPact NSX100250
Device Short Name	NSX160F
Product Or Component Type	Circuit breaker
Device Application	Distribution
Number Of Poles	1P
Protected Poles Description	1t
[In] Rated Current	160 A at 40 °C
[Ue] Rated Operational Voltage	250 V DC 277 V AC 50/60 Hz
Network Type	DC AC
Network Frequency	50/60 Hz
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Utilisation Category	Category A
[Icu] Rated Ultimate Short-Circuit Breaking Capacity	36 kA Icu at 250 V DC 1P conforming to IEC 60947-2 36 kA Icu at 125 V DC 1P conforming to IEC 60947-2 18 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2
Performance Level	F 18 kA 240 V AC
Trip Unit Name	TM-D
Trip Unit Technology	Thermal-magnetic
Control Type	Toggle
Circuit Breaker Mounting Mode	Fixed

Complementary

[Ui] Rated Insulation Voltage	750 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-2
[Ics] Rated Service Short-Circuit Breaking Capacity	36 kA at 250 V DC conforming to IEC 60947-2 36 kA at 125 V DC conforming to IEC 60947-2 18 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2
Mechanical Durability	20000 cycles

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Electrical Durability	10000 cycles at 277 V In
	20000 cycles at 277 V In/2
Mounting Support	Backplate
Upside Connection	Front
Downside Connection	Front
Connection Pitch	35 mm
Protection Type	for overload protection (thermal) for short-circuit protection (magnetic)
Trip Unit Rating	160 A at 40 °C
Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)	Fixed
[Ir] Long-Time Protection Pick-Up Adjustment Range	1 ln
[Im] Magnetic Protection Pick-Up Range	1250 A
Earth-Leakage Protection	Without
Width (W)	35 mm
Height (H)	161 mm
Depth (D)	86 mm

Environment

Standards	EN/IEC 60947
Product Certifications	CCC EAC Marine
Overvoltage Category	Class II
Electrical Shock Protection Class	Class II
Pollution Degree	3 conforming to IEC 60664-1
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 62262
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-50…85 °C
Relative Humidity	095 %
Operating Altitude	02000 m without derating 2000 m5000 m with derating

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	13.0 cm
Package 1 Length	17.5 cm
Package 1 Weight	741.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	12
Package 2 Height	30.0 cm

Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	9 379 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information