# **Product datasheet**

Specification





# Modular discovery packs, Zelio Logic, smart relay discovery® pack, 10 I/O, 100...240 V AC

SR3PACKFU

### Main

Range Of Product	Zelio Logic
Product Or Component Type	Modular discovery packs
Discrete Input Number	6
Number Of Outputs	4 relay

## Complementary

Kit Composition	SR3B101FU Cable PC SR2USB01 for connection to PC
Input/Output Number	10
Local Display	With
Number Or Control Scheme Lines	120 with ladder programming 0200 with FBD programming
Cycle Time	690 ms
Backup Time	10 years at 25 °C
Clock Drift	12 min/year at 055 °C 6 s/month at 25 °C
Checks	Program memory on each power up
[Us] Rated Supply Voltage	100240 V
Supply Voltage Limits	85264 V
Supply Frequency	50/60 Hz
Maximum Supply Current	30 mA at 240 V (without extension) 40 mA at 240 V (with extensions) 80 mA at 100 V (with extensions) 80 mA at 100 V (without extension)
Power Consumption In Va	12 VA with extensions 7 VA without extension
Isolation Voltage	1780 V
Protection Type	Against inversion of terminals (control instructions not executed)
Discrete Input Voltage	100240 V AC
Discrete Input Current	0.6 mA
Discrete Input Frequency	4753 Hz 5763 Hz
Voltage State 1 Guaranteed	>= 79 V for discrete input
Voltage State 0 Guaranteed	<= 40 V for discrete input
Current State 1 Guaranteed	>= 0.17 mA (discrete input)

Current State 0 Guaranteed	<= 0.5 mA (discrete input)
Input Impedance	350 kOhm for discrete input
Output Voltage Limits	530 V DC (relay output) 24250 V AC
Contacts Type And Composition	NO for relay output
Output Thermal Current	8 A for all 4 outputs for relay output
Electrical Durability	AC-12: 500000 cycles at 230 V, 1.5 A for relay output conforming to IEC 60947-5-1 AC-15: 500000 cycles at 230 V, 0.9 A for relay output conforming to IEC 60947-5-1 DC-12: 500000 cycles at 24 V, 1.5 A for relay output conforming to IEC 60947-5-1 DC-13: 500000 cycles at 24 V, 0.6 A for relay output conforming to IEC 60947-5-1
Switching Capacity In Ma	>= 10 mA at 12 V (relay output)
Operating Rate In Hz	0.1 Hz (at le) for relay output 10 Hz (no load) for relay output
Mechanical Durability	10000000 cycles for relay output
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to EN/IEC 60947-1 and EN/IEC 60664-1
Clock	With
Response Time	50 ms with ladder programming (from state 0 to state 1) for discrete input 50 ms with ladder programming (from state 1 to state 0) for discrete input 50255 ms with FBD programming (from state 0 to state 1) for discrete input 50255 ms with FBD programming (from state 1 to state 0) for discrete input 10 ms (from state 0 to state 1) for relay output 5 ms (from state 1 to state 0) for relay output
Connections - Terminals	Screw terminals, 1 x 0.21 x 2.5 mm² (AWG 25AWG 14) semi-solid Screw terminals, 1 x 0.21 x 2.5 mm² (AWG 25AWG 14) solid Screw terminals, 1 x 0.251 x 2.5 mm² (AWG 24AWG 14) flexible with cable end Screw terminals, 2 x 0.22 x 1.5 mm² (AWG 24AWG 16) solid Screw terminals, 2 x 0.252 x 0.75 mm² (AWG 24AWG 18) flexible with cable end
Tightening Torque	0.5 N.m
Overvoltage Category	III conforming to IEC 60664-1
Net Weight	0.7 kg

## **Environment**

Immunity To Microbreaks	10 ms	
Product Certifications	GOST	
	C-Tick	
	GL	
	CSA	
	UL	
Standards	IEC 61000-4-2 level 3	
	IEC 61000-4-4 level 3	
	IEC 61000-4-12	
	IEC 61000-4-5	
	IEC 61000-4-11	
	IEC 61000-4-3	
	IEC 61000-4-6 level 3	
	IEC 60068-2-6 Fc	
	IEC 60068-2-27 Ea	
Ip Degree Of Protection	IP20 (terminal block) conforming to IEC 60529	
	IP40 (front panel) conforming to IEC 60529	
Environmental Characteristic	EMC directive conforming to IEC 61000-6-2	
	EMC directive conforming to IEC 61000-6-3	
	EMC directive conforming to IEC 61000-6-4	
	EMC directive conforming to IEC 61131-2 zone B	
	Low voltage directive conforming to IEC 61131-2	
Disturbance Radiated/Conducted	Class B conforming to EN 55022-11 group 1	
Pollution Degree	2 conforming to IEC 61131-2	

Ambient Air Temperature For Operation	-2040 °C in non-ventilated enclosure conforming to IEC 60068-2-1 and IEC 60068-2-2 -2055 °C conforming to IEC 60068-2-1 and IEC 60068-2-2
Ambient Air Temperature For Storage	-4070 °C
Operating Altitude	2000 m
Maximum Altitude Transport	3048 m
Relative Humidity	95 % without condensation or dripping water

# **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.0 cm
Package 1 Width	16.0 cm
Package 1 Length	24.0 cm
Package 1 Weight	485.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	10
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	5.326 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>②</b>	Mercury Free	
	Rohs Exemption Information	Yes
	Pvc Free	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information