

Product datasheet

Specifications



variable speed drive ATV71Q - 400kW / 450HP - 500...690V - IP20

Local distributor code:

398229616

ATV71QC40Y

 **Discontinued on:** 22 Sept 2021

EAN Code: 3606480389177

 **Discontinued**

Main

Range Of Product	Altivar 71Q
Product Or Component Type	Variable speed drive
Device Short Name	ATV71Q
Product Destination	Asynchronous motors Synchronous motors
Product Specific Application	Complex, high-power machines
Assembly Style	With heat sink
Variant	Reinforced version
Emc Filter	Integrated
Network Number Of Phases	3 phases
[Us] Rated Supply Voltage	500...690 V - 15...10 %
Supply Voltage Limits	425...759 V
Supply Frequency	50...60 Hz - 5...5 %
Network Frequency Limits	47.5...63 Hz
Motor Power Kw	315 kW, 3 phases at 500 V 400 kW, 3 phases at 690 V
Motor Power Hp	450 hp, 3 phases at 575 V
Maximum Motor Cable Length	15 m shielded cable without motor choke 30 m unshielded cable without motor choke 250 m shielded cable with motor choke 400 m unshielded cable with motor choke
Line Current	439 A for 500 V 3 phases 315 kW 401 A for 600 V 3 phases / 500 hp 409 A for 690 V 3 phases 400 kW

Complementary

Prospective Line Isc	35 kA for 3 phases
Continuous Output Current	462 A at 2.5 kHz, 500 V - 3 phases 420 A at 2.5 kHz, 575 V - 3 phases 420 A at 2.5 kHz, 690 V - 3 phases
Maximum Transient Current	693 A for 60 s, 3 phases 762.3 A for 2 s, 3 phases
Speed Drive Output Frequency	0.1...500 Hz
Nominal Switching Frequency	2.5 kHz
Switching Frequency	2...4.9 kHz adjustable 2.5...4.9 kHz with derating factor

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Speed Range	1...100 for asynchronous motor in open-loop mode, without speed feedback 1...50 for synchronous motor in open-loop mode, without speed feedback 1...1000 for asynchronous motor in closed-loop mode with encoder feedback
Speed Accuracy	+/- 0.01 % of nominal speed in closed-loop mode with encoder feedback 0.2 Tn to Tn +/- 10 % of nominal slip without speed feedback 0.2 Tn to Tn
Torque Accuracy	+/- 5 % in closed-loop mode with encoder feedback +/- 15 % in open-loop mode, without speed feedback
Transient Overtorque	170 % of nominal motor torque +/- 10 % for 60 s 220 % of nominal motor torque +/- 10 % for 2 s
Braking Torque	30 % without braking resistor ≤ 150 % with braking or hoist resistor
Asynchronous Motor Control Profile	Flux vector control without sensor, standard Voltage/frequency ratio - Energy Saving, quadratic U/f Flux vector control without sensor, ENA (energy Adaptation) system Flux vector control with sensor, standard Flux vector control without sensor, 2 points Voltage/frequency ratio, 2 points Voltage/frequency ratio, 5 points
Synchronous Motor Control Profile	Vector control with sensor, standard Vector control without sensor, standard
Regulation Loop	Adjustable PI regulator
Motor Slip Compensation	Adjustable Not available in voltage/frequency ratio (2 or 5 points) Suppressable Automatic whatever the load
Local Signalling	1 LED (red) for drive voltage
Output Voltage	≤ power supply voltage
Isolation	Electrical between power and control
Type Of Cable	Without mounting kit: 1 wire(s) IEC cable at 45 °C, copper 90 °C / XLPE/EPR Without mounting kit: 1 wire(s) IEC cable at 45 °C, copper 70 °C / PVC With an IP21 or an IP31 kit: 3 wire(s) IEC cable at 40 °C, copper 70 °C / PVC With a NEMA Type1 kit: 3 wire(s) UL 508 cable at 40 °C, copper 75 °C / PVC
Electrical Connection	Terminal 2.5 mm² / AWG 14 (AI1-/AI1+, AI2, AO1, R1A, R1B, R1C, R2A, R2B, LI1...LI6, PWR) Terminal 8 x 185 mm² (PC/-, PA/+) Terminal 2 x 4 x 185 mm² (R/L1.1, S/L2.1, T/L3.1, R/L1.2, S/L2.2, T/L3.2) Terminal 6 x 185 mm² (U/T1, V/T2, W/T3)
Tightening Torque	41 N.m, 360 lb.in (PC/-, PA/+) 41 N.m, 360 lb.in (R/L1.1, S/L2.1, T/L3.1, R/L1.2, S/L2.2, T/L3.2) 41 N.m, 360 lb.in (U/T1, V/T2, W/T3) 0.6 N.m (AI1-/AI1+, AI2, AO1, R1A, R1B, R1C, R2A, R2B, LI1...LI6, PWR)
Supply	Internal supply for reference potentiometer (1 to 10 kOhm): 10.5 V DC, +/- 5 %, <10 mA with overload and short-circuit protection Internal supply: 24 V DC (21...27 V), <200 mA with overload and short-circuit protection
Analogue Input Number	2
Analogue Input Type	AI2 software-configurable voltage: 0...10 V DC 24 V max, impedance: 30000 Ohm, resolution 11 bits AI1-/AI1+ bipolar differential voltage: +/- 10 V DC 24 V max, resolution 11 bits + sign AI2 software-configurable current: 0...20 mA, impedance: 242 Ohm, resolution 11 bits
Sampling Duration	2 ms +/- 0.5 ms (LI6) if configured as logic input - discrete input 2 ms +/- 0.5 ms (LI1...LI5) - discrete input 2 ms +/- 0.5 ms (AI1-/AI1+) - analog output 2 ms +/- 0.5 ms (AI2) - analog output
Accuracy	+/- 0.6 % (AI1-/AI1+) for a temperature variation 60 °C +/- 0.6 % (AI2) for a temperature variation 60 °C +/- 1 % (AO1) for a temperature variation 60 °C
Linearity Error	+/- 0.15 % of maximum value (AI1-/AI1+, AI2) +/- 0.2 % (AO1)

Analogue Output Number	1
Analogue Output Type	AO1 software-configurable voltage: 0...10 V DC, impedance: 470 Ohm, resolution 10 bits AO1 software-configurable current: 0...20 mA, impedance: 500 Ohm, resolution 10 bits AO1 software-configurable logic output 10 V 20 mA
Discrete Output Number	2
Discrete Output Type	Configurable relay logic: (R1A, R1B, R1C) NO/NC - 100000 cycles Configurable relay logic: (R2A, R2B) NO - 100000 cycles
Response Time	R1A, R1B, R1C 7 ms, tolerance +/- 0.5 ms R2A, R2B 7 ms, tolerance +/- 0.5 ms AO1 2 ms, tolerance +/- 0.5 ms <= 100 ms in STO (Safe Torque Off)
Minimum Switching Current	3 mA at 24 V DC for configurable relay logic
Maximum Switching Current	5 A at 250 V AC on resistive load - cos phi = 1 - L/R = 0 ms (R1, R2) 5 A at 30 V DC on resistive load - cos phi = 1 - L/R = 0 ms (R1, R2) 2 A at 250 V AC on inductive load - cos phi = 0.4 - L/R = 7 ms (R1, R2) 2 A at 30 V DC on inductive load - cos phi = 0.4 - L/R = 7 ms (R1, R2)
Discrete Input Number	7
Discrete Input Type	LI1...LI5: programmable 24 V DC with level 1 PLC, impedance: 3500 Ohm LI6: switch-configurable 24 V DC with level 1 PLC, impedance: 3500 Ohm LI6: switch-configurable PTC probe 0...6, impedance: 1500 Ohm PWR: safety input 24 V DC, impedance: 1500 Ohm conforming to ISO 13849-1 level d
Discrete Input Logic	Positive logic (source) (LI6)if configured as logic input, < 5 V (state 0), > 11 V (state 1) Negative logic (sink) (LI6)if configured as logic input, > 16 V (state 0), < 10 V (state 1) Positive logic (source) (LI1...LI5), < 5 V (state 0), > 11 V (state 1) Negative logic (sink) (LI1...LI5), > 16 V (state 0), < 10 V (state 1) Positive logic (source) (PWR), < 2 V (state 0), > 17 V (state 1)
Acceleration And Deceleration Ramps	Automatic adaptation of ramp if braking capacity exceeded, by using resistor S, U or customized Linear adjustable separately from 0.01 to 9000 s
Braking To Standstill	By DC injection
Protection Type	Overheating protection: drive Thermal protection: drive Short-circuit between motor phases: drive Input phase breaks: drive Overcurrent between output phases and earth: drive Overvoltages on the DC bus: drive Break on the control circuit: drive Against exceeding limit speed: drive Line supply undervoltage: drive Line supply overvoltage: drive Against input phase loss: drive Thermal protection: motor Motor phase break: motor Power removal: motor
Dielectric Strength	3110 V DC between earth and power terminals 5345 V DC between control and power terminals
Insulation Resistance	> 1 mOhm 500 V DC for 1 minute to earth
Frequency Resolution	Display unit: 0.1 Hz Analog input: 0.024/50 Hz
Communication Port Protocol	Modbus CANopen
Connector Type	1 RJ45 (on front face) for Modbus 1 RJ45 (on terminal) for Modbus 1 RJ45 for CANopen
Physical Interface	2-wire RS 485 for Modbus
Transmission Frame	RTU for Modbus

Transmission Rate	9600 bps, 19200 bps for Modbus on front face 4800 bps, 9600 bps, 19200 bps, 38.4 Kbps for Modbus on terminal 20 kbps, 50 kbps, 125 kbps, 250 kbps, 500 kbps, 1 Mbps for CANopen
Data Format	8 bits, 1 stop, even parity for Modbus on front face 8 bits, odd even or no configurable parity for Modbus on terminal
Type Of Polarization	No impedance for Modbus
Number Of Addresses	1...247 for Modbus 1...127 for CANopen
Method Of Access	Slave CANopen
Type Of Cooling	Water cooled
Cooling Fluid Type	Industrial water Clean water Water-glycol mixture
Operating Temperature Water	5...55 °C
Thermal Losses	5700 W 100 % of line current for area of liquid cooling (power part) 1320 W 100 % of line current for area of air cooling (control part)
Flow Velocity	24
Pressure Drop	2 bar
Volume Of Cooling Water	0.7 l
Operating Position	Vertical +/- 10 degree
Net Weight	300 kg
Option Card	Communication card for Modbus TCP Communication card for Fipio Communication card for Modbus/Uni-Telway Communication card for Modbus Plus Communication card for EtherNet/IP Communication card for DeviceNet Communication card for Profibus DP Communication card for Profibus DP V1 Communication card for Interbus-S Communication card for CC-Link Interface card for encoder I/O extension card Controller inside programmable card Overhead crane card
Width	1110 mm
Height	1150 mm
Depth	377 mm

Environment

Ambient Air Temperature For Operation	-10...50 °C (without derating)
Ambient Air Temperature For Storage	-25...70 °C
Operating Altitude	<= 1000 m without derating 1000...2260 m with current derating 1 % per 100 m
Electromagnetic Compatibility	Electrostatic discharge immunity test level 3 conforming to IEC 61000-4-2 Radiated radio-frequency electromagnetic field immunity test level 3 conforming to IEC 61000-4-3 Electrical fast transient/burst immunity test level 4 conforming to IEC 61000-4-4 1.2/50 µs - 8/20 µs surge immunity test level 3 conforming to IEC 61000-4-5 Conducted radio-frequency immunity test level 3 conforming to IEC 61000-4-6 Voltage dips and interruptions immunity test conforming to IEC 61000-4-11
Pollution Degree	2 conforming to EN/IEC 61800-5-1 3 conforming to UL 840

Ip Degree Of Protection	IP00 conforming to EN/IEC 61800-5-1 IP00 conforming to EN/IEC 60529 IP41 on upper part conforming to EN/IEC 61800-5-1 IP41 on upper part conforming to EN/IEC 60529 IP30 on the front panel conforming to EN/IEC 61800-5-1 IP30 on the front panel conforming to EN/IEC 60529 IP30 on side parts conforming to EN/IEC 61800-5-1 IP30 on side parts conforming to EN/IEC 60529 IP54 on lower part conforming to EN/IEC 61800-5-1 IP54 on lower part conforming to EN/IEC 60529
Vibration Resistance	1.5 mm peak to peak (f= 3...10 Hz) conforming to EN/IEC 60068-2-6 0.6 gn (f= 10...200 Hz) conforming to EN/IEC 60068-2-6
Shock Resistance	4 gn for 11 ms conforming to EN/IEC 60068-2-27
Relative Humidity	5...95 % without condensation conforming to IEC 60068-2-3 5...95 % without dripping water conforming to IEC 60068-2-3
Noise Level	77 dB conforming to 86/188/EEC
Standards	UL Type 1 EN/IEC 61800-3 EN 61800-3 environments 2 category C3 IEC 61508 SIL2 ISO 13849-1 level d EN 61800-3 environments 1 category C3 EN 55011 class A group 2 EN/IEC 61800-5-1 IEC 60721-3-3 class 3C2
Product Certifications	NOM 117 GOST CSA C-Tick UL
Marking	CE

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	53.0 cm
Package 1 Width	63.5 cm
Package 1 Length	129.0 cm
Package 1 Weight	370.0 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)


Well-being performance

	Mercury Free	
	Rohs Exemption Information	Yes
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	


Dimensions Drawings

Dimensions

Without or with 1 option card




With 2 option cards




Mounting and Clearance

Clearance



Wall-Mounting

The drive is designed for installation on the wall, in an electrical room or into an enclosure. The device is built according to pollution degree 2. If the environment does not correspond to these conditions then the necessary transition of the pollution degree must be provided e.g. by means of an enclosure.




- (1) Drive
- (2) Cooling water inlet
- (3) Cooling water return
- (4) Cooling air for control part
- (5) Cooling air for power part (only capacitors)

Connections and Schema


Wiring Diagram

Standard 6-pulse Design



- A1 Drive
- BU Braking Unit
- F1 Fast-acting semi-conductor fuse
- IL1 Line choke
- KM1 Optional line contactor
- M Motor
- Q1 Switch
- RFI Optional radio frequency interference filter
- (1) Filter
- (2) Control
- (3) Relay control
- (4) Control potentiometer
- (5) PLC
- (6) External optional braking resistor
- (7) Optional motor choke

Optional 12-pulse Design




- A1 Drive
- BU Braking Unit
- F1, F2 Fast-acting semi-conductor fuse
- KM1 Optional line contactor
- M Motor
- Q1, Q2 Switches
- T1 Transformer with two out-of-phase secondary windings
- (1) Filter
- (2) Control
- (3) Relay control
- (4) Control potentiometer
- (5) PLC
- (6) External optional braking resistor
- (7) Optional motor choke
- (8) Insulation monitoring relay

Performance Curves

Continuous Current at Output Frequencies < 1 Hz

Due to the especially efficient liquid cooling of the drive the full overload capability is also available in the speed range of 0 Hz.



- (1) Continuous operation: 150% (165%) overload capability
- (2) Overload 150% for 60 s
- (3) Overload 165% for 2 s

Power Derating

4 kHz pulse frequency	+5°K air temperature
18%	5%