# **Product datasheet**





# servo motor BMI 3-phase untapped IP54 single turn -131072 p/t

BMI0702P01A

! Discontinued on: 9 Feb 2023

① Discontinued

EAN Code: 3606485375649

### Main

| Range Compatibility       | Lexium 32i                   |
|---------------------------|------------------------------|
| Product Or Component Type | Servo motor with power stage |
| Device Short Name         | BMI                          |

# Complementary

| Maximum Mechanical Speed  | 8000 rpm  |
|---------------------------|---|
| [Us] Rated Supply Voltage | 208480 V - 1510 %   |
| Supply Voltage Limits     | 208480 V  |
| Network Number Of Phases  | Three phase   |
| Supply Frequency          | 50/60 Hz - 55 %   |
| Network Frequency Limits  | 47.563 Hz   |
| Emc Filter                | Integrated  |
| Continuous Output Current | 2 A at 8 kHz  |
| Output Current 3S Peak    | 6 A at 400 V for 3 s  |
| Continuous Stall Current  | 2 A   |
| Continuous Stall Torque   | 2.48 N.m at 208480 V three phase  |
| Peak Stall Torque         | 6.8 N.m at 208 V three phase<br>6.8 N.m at 400 V three phase<br>6.8 N.m at 480 V three phase    |
| Nominal Output Power      | 400 W at 208 V three phase<br>800 W at 400 V three phase<br>900 W at 480 V three phase          |
| Nominal Torque            | 2.4 N.m at 208 V three phase 2.2 N.m at 400 V three phase 2 N.m at 480 V three phase            |
| Nominal Speed             | 1800 rpm at 208 V three phase<br>3600 rpm at 400 V three phase<br>4400 rpm at 480 V three phase |
| Maximum Current Irms      | 9.6 A at 208 V, three phase<br>9.6 A at 400 V, three phase<br>9.6 A at 480 V, three phase       |
| Product Compatibility     | Drive control unit LXM32i CANopen<br>Drive control unit LXM32i EtherCAT                         |
| Shaft End                 | Untapped  |
| Second Shaft              | Without second shaft end  |
| Shaft Diameter            | 11 mm   |

| Shaft Length                          | 23 mm  |
|---------------------------------------|--|
| Feedback Type                         | Absolute single turn SinCos Hiperface  |
| Speed Feedback Resolution             | 131072 points/turn   |
| Holding Brake                         | Without  |
| Mounting Support                      | International standard flange  |
| Motor Flange Size                     | 70 mm  |
| Electrical Connection                 | Printed circuit board connector  |
| Torque Constant                       | 1.15 N.m/A at 20 °C  |
| Back Emf Constant                     | 77.18 V/krpm at 20 °C  |
| Number Of Motor Poles                 | 10   |
| Rotor Inertia                         | 1.13 kg.cm²  |
| Stator Resistance                     | 8.89 Ohm at 20 °C  |
| Stator Inductance                     | 25.75 mH at 20 °C  |
| Stator Electrical Time Constant       | 2.9 ms at 20 °C  |
| Maximum Radial Force Fr               | 710 N at 1000 rpm<br>560 N at 2000 rpm<br>490 N at 3000 rpm<br>450 N at 4000 rpm<br>410 N at 5000 rpm<br>390 N at 6000 rpm |
| Maximum Axial Force Fa                | 0.2 x Fr   |
| Type Of Cooling                       | Natural convection   |
| Length                                | 268 mm   |
| Number Of Motor Stacks                | 2  |
| Centring Collar Diameter              | 60 mm  |
| Centring Collar Depth                 | 2.5 mm   |
| Number Of Mounting Holes              | 4  |
| Mounting Holes Diameter               | 5.5 mm   |
| Circle Diameter Of The Mounting Holes | 7582 mm  |
| Distance Shaft Shoulder-Flange        | 2.5 mm   |

### **Environment**

Ip Degree Of Protection Shaft: IP54
Housing: IP65

# **Packing Units**

| Unit Type Of Package 1       | PCE     |
|------------------------------|---------|
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 26.0 cm |
| Package 1 Width              | 20.0 cm |
| Package 1 Length             | 59.0 cm |
| Package 1 Weight             | 5.4 kg  |

# **Contractual warranty**

Warranty

18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

|          | Mercury Free               |     |
|----------|----------------------------|-----|
| <b>⊘</b> | Rohs Exemption Information | Yes |
| <b>⊘</b> | Pvc Free                   |     |


### **Certifications & Standards**

| Weee                     | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |  |
|--------------------------|---|--|
| Environmental Disclosure | Product Environmental Profile   |  |
| China Rohs Regulation    | China RoHS declaration  |  |
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)  |  |
| Reach Regulation         | REACh Declaration   |  |

## **Dimensions Drawings**

#### **External Dimensions**

### With Standard Braking Resistor



- (1) Module for supply voltage
- (2) I/O module
- (3) Standard braking resistor


#### Dimensions in mm

| W  | Н   | L   |
|----|-----|-----|
| 99 | 187 | 289 |

#### Dimensions in in

| Dimensions in in. |      |       |
|-------------------|------|-------|
| W                 | Н    | L     |
| 3,9               | 7,36 | 11,38 |

### Mounting type B



- (1) Module for supply voltage
- (2) I/O module

## BMI0702P01A

(3) Standard braking resistor


Dimensions in mm

| W  | Н     | L   |
|----|-------|-----|
| 99 | 138,5 | 338 |

#### Dimensions in in.

| W   | Н    | L     |
|-----|------|-------|
| 3,9 | 5,45 | 13,31 |

## With External Braking Resistor



- (1) Module for supply voltage
- (2) I/O module
- (4) External braking resistor

Dimensions in mm

| W  | Н   | L   |
|----|-----|-----|
| 99 | 187 | 301 |


Dimensions in in.

| W   | Н    | L     |
|-----|------|-------|
| 3,9 | 7,36 | 11,85 |

### Mounting type D

# **Product datasheet**

## BMI0702P01A




- (1) Module for supply voltage
- (2) I/O module
- External braking resistor (4)

#### Dimensions in mm

| W  | Н   | L   |
|----|-----|-----|
| 99 | 160 | 338 |

#### Dimensions in in.

| W   | Н   | L     |  |  |
|-----|-----|-------|--|--|
| 3,9 | 6,3 | 13,31 |  |  |



- Module for supply voltage (1)
- (2) I/O module
- (4) External braking resistor


#### Dimensions in mm

| W  | Н   | L   |
|----|-----|-----|
| 99 | 187 | 328 |

Dimensions in in.

| W   | Н    | L     |  |  |
|-----|------|-------|--|--|
| 3,9 | 7,36 | 12,91 |  |  |

### Mounting type F



- (1) Module for supply voltage
- (2) I/O module
- (4) External braking resistor

#### Dimensions in mm

| W  | Н   | L   |  |  |
|----|-----|-----|--|--|
| 99 | 180 | 338 |  |  |


#### Dimensions in in

| W   | Н    | L     |  |  |
|-----|------|-------|--|--|
| 3,9 | 7,09 | 13,31 |  |  |

#### Performance Curves

### **Performance Curves**

### Torque/Speed Curves with 208 V Three Phases Supply Voltage




- (X) Speed (rpm)
- (Y) Torque (N.m)
- (1) Motor peak
- (2) Drive peak
- (3) Drive cont
- (4) Motor cont
- (5) Operating point

|                         |   | Power  | At Speed | With Torque |
|-------------------------|---|--------|----------|-------------|
| max. Peak Power         |   | 1013 W | 1520 rpm | 6.36 N.m    |
| max Cont. Power (Drive) | • | 519 W  | 2240 rpm | 2.21 N.m    |

### **Performance Curves**

#### Torque/Speed Curves with 400 V Three Phases Supply Voltage




- (X) Speed (rpm)
- (Y) Torque (N.m)
- (1) Motor peak
- (2) Drive peak
- (3) Drive cont
- (4) Motor cont
- (5) Operating point

|                         |   | Power  | At Speed | With Torque |
|-------------------------|---|--------|----------|-------------|
| max. Peak Power         |   | 2161 W | 3280 rpm | 6.29 N.m    |
| max Cont. Power (Drive) | • | 892 W  | 4560 rpm | 1.87 N.m    |

### **Performance Curves**

#### Torque/Speed Curves with 480 V Three Phases Supply Voltage



- (X) Speed (rpm)
- (Y) Torque (N.m)
- (1) Motor peak
- (2) Drive peak
- (3) Drive cont
- (4) Motor cont
- (5) Operating point

|                         |   | Power  | At Speed | With Torque |
|-------------------------|---|--------|----------|-------------|
| max. Peak Power         |   | 2623 W | 4000 rpm | 6.26 N.m    |
| max Cont. Power (Drive) | • | 943 W  | 5600 rpm | 1.61 N.m    |