Product datasheet

Specification





servo motor BMI 1-phase untapped IP54 single turn -131072 p/t - brake

BMI0702T01F

EAN Code: 3606485375977



Main

Range Compatibility	Lexium 32i
Product Or Component Type	Servo motor with power stage
Device Short Name	BMI

Complementary

Maximum Mechanical Speed	8000 rpm
[Us] Rated Supply Voltage	115230 V - 1510 %
Supply Voltage Limits	100240 V
Network Number Of Phases	Single phase
Supply Frequency	50/60 Hz - 55 %
Network Frequency Limits	47.563 Hz
Emc Filter	Integrated
Continuous Output Current	2.6 A at 8 kHz
Output Current 3S Peak	10.5 A at 230 V for 1 s
Continuous Stall Current	2.6 A
Continuous Stall Torque	2.48 N.m at 115230 V single phase
Peak Stall Torque	6.6 N.m at 115 V single phase 6.6 N.m at 230 V single phase
Nominal Output Power	700 W at 230 V single phase 400 W at 115 V single phase
Nominal Torque	2.2 N.m at 115 V single phase 1.7 N.m at 230 V single phase
Nominal Speed	4000 rpm at 230 V single phase 1700 rpm at 115 V single phase
Maximum Current Irms	17.7 A at 230 V, single phase 17.7 A at 115 V, single phase
Product Compatibility	Drive control unit LXM32i CANopen Drive control unit LXM32i EtherCAT
Shaft End	Untapped
Second Shaft	Without second shaft end
Shaft Diameter	11 mm
Shaft Length	23 mm
Feedback Type	Absolute single turn SinCos Hiperface

Speed Feedback Resolution	131072 points/turn
Holding Brake	With
Holding Torque	3 N.m holding brake
Mounting Support	International standard flange
Motor Flange Size	70 mm
Electrical Connection	Printed circuit board connector
Torque Constant	0.63 N.m/A at 20 °C
Back Emf Constant	42.1 V/krpm at 20 °C
Number Of Motor Poles	10
Rotor Inertia	1.24 kg.cm²
Stator Resistance	2.7 Ohm at 20 °C
Stator Inductance	7.8 mH at 20 °C
Stator Electrical Time Constant	2.89 ms at 20 °C
Maximum Radial Force Fr	710 N at 1000 rpm 560 N at 2000 rpm 490 N at 3000 rpm 450 N at 4000 rpm 410 N at 5000 rpm 390 N at 6000 rpm
Maximum Axial Force Fa	0.2 x Fr
Brake Pull-In Power	5 W
Type Of Cooling	Natural convection
Length	306 mm
Number Of Motor Stacks	2
Centring Collar Diameter	60 mm
Centring Collar Depth	2.5 mm
Number Of Mounting Holes	4
Mounting Holes Diameter	5.5 mm
Circle Diameter Of The Mounting Holes	7582 mm
Distance Shaft Shoulder-Flange	2.5 mm

Environment

Ip Degree Of Protection Shaft: IP54
Housing: IP65

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	26.0 cm
Package 1 Width	20.0 cm
Package 1 Length	59.0 cm
Package 1 Weight	5.4 kg

Contractual warranty

Warranty

18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Mercury Free	
②	Rohs Exemption Information	Yes
	Pvc Free	


Certifications & Standards

Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
Environmental Disclosure	Product Environmental Profile	
China Rohs Regulation	China RoHS declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
Reach Regulation	REACh Declaration	

Dimensions Drawings

External Dimensions

With Standard Braking Resistor



- (1) Module for supply voltage
- (2) I/O module
- (3) Standard braking resistor


Dimensions in mm

W	Н	L
99	187	327

Dimensions in in.

W	Н	L
3,90	7,36	12,87

Mounting type B



- (1) Module for supply voltage
- (2) I/O module

(3) Standard braking resistor


Dimensions in mm

W	Н	L
99	138,5	376

Dimensions in in.

W	Н	L
3,90	5,45	14,8

With External Braking Resistor



- (1) Module for supply voltage
- (2) I/O module
- (4) External braking resistor

Dimensions in mm

W	Н	L
99	187	339


Dimensions in in.

W	Н	L
3,90	7,36	13,35

Mounting type D

Product datasheet

BMI0702T01F




- (1) Module for supply voltage
- (2) I/O module
- External braking resistor (4)

Dimensions in mm

W	Н	L
99	160	376

Dimensions in in.

D				
W	Н	L		
3,90	6,3	14,8		



- Module for supply voltage (1)
- (2) I/O module
- (4) External braking resistor


Dimensions in mm

W	Н	L
99	187	366

Dimensions in in.

W	Н	L
3,90	7,36	14,41

Mounting type F



- (1) Module for supply voltage
- (2) I/O module
- (4) External braking resistor

Dimensions in mm

W	Н	L	
99	180	376	


Dimensions in in.

W H I			
VV	П	_	
3,90	7,09	14,8	

Performance Curves

Performance Curves

Torque/Speed Curves with 115 V Single Phase Supply Voltage




- (X) Speed (rpm)
- (Y) Torque (N.m)
- (1) Motor peak
- (2) Drive peak
- (3) Drive cont
- (4) Motor cont
- (5) Operating point

		Power	At Speed	With Torque
max. Peak Power	•	860 W	1760 rpm	4.67 N.m
max Cont. Power (Drive)	•	499 W	2160 rpm	2.21 N.m

Performance Curves

Torque/Speed Curves with 230 V Single Phase Supply Voltage



- (X) Speed (rpm)
- (Y) Torque (N.m)
- (1) Motor peak
- (2) Drive peak
- (3) Drive cont
- (4) Motor cont
- (5) Operating point

		Power	At Speed	With Torque
max. Peak Power		2129 W	3360 rpm	6.05 N.m
max Cont. Power (Drive)	•	736 W	4640 rpm	1.51 N.m