



ARA auto recloser aux for iC60
3P-4P - 4 Prog

A9C70134

Main

Range Of Product	Acti9
Product Or Component Type	Automatic recloser auxiliary
Device Short Name	ARA iC60
Signal Contacts Composition	2 OF volt-free contacts
Signalling Circuit Voltage	24 V 10 mA AC/DC 230 V 1 A AC

Complementary

Control Type	Inhibition of automatism maintained 230 V AC 50/60 Hz Ultimate reclosing impulse 230 V AC 50/60 Hz
Input Current	5 mA
Impulse Duration	>= 200 ms control circuit
Response Time	< 500 ms
[Us] Rated Supply Voltage	230 V AC 50/60 Hz
Power Consumption In W	2 W
[Ui] Rated Insulation Voltage	400 V
[Uimp] Rated Impulse Withstand Voltage	6 kV
Value Of Setting	Program 1: 1 reclosing attemp, short cycle <10 s before reclosing /6 min check time Program 2: 3 reclosing attemps, short cycle <10 s before reclosing /2 min check time Program 2: 3 reclosing attemps, short cycle <1 min before reclosing /6 min check time Program 2: 3 reclosing attemps, short cycle <3 min before reclosing /6 min check time Program 3: 5 reclosing attemps, long fixed cycle <10 s before reclosing /2 min check time Program 3: 5 reclosing attemps, long fixed cycle <1 min before reclosing /6 min check time Program 3: 5 reclosing attemps, long fixed cycle <3 min before reclosing /6 min check time Program 4: 5 reclosing attemps, long progressive cycle <10 s before reclosing /2 min check time Program 4: 5 reclosing attemps, long progressive cycle <1 min before reclosing /6 min check time Program 4: 5 reclosing attemps, long progressive cycle <3 min before reclosing /8 min check time Program 4: 5 reclosing attemps, long progressive cycle <4 min before reclosing /10 min check time Program 4: 5 reclosing attemps, long progressive cycle <5 min before reclosing /12 min check time
Local Signalling	Flashing orange LED: not operational Flashing green LED: normal operation Flashing red LED: reclosing cycle in progress Fixed red LED: automatic recloser locked
Mounting Mode	Clip-on

Mounting Support	DIN rail
Comb Busbar And Distribution Block Compatibility	NO
9 Mm Pitches	7
Height	93 mm
Width	63 mm
Depth	75.5 mm
Net Weight	470 g
Colour	White
Electrical Durability	5000 cycles
Provision For Padlocking	Padlockable
Wire Stripping Length	Power supply: 10 mm for bottom connection Input: 10 mm for bottom connection Output: 8 mm for top connection
Tightening Torque	Power supply: 1 N.m Input: 1 N.m Output: 0.7 N.m
Range Compatibility	Acti 9 Acti9 iC60
Product Compatibility	4P iC60 3P iC60

Environment

Ip Degree Of Protection	IP20 conforming to IEC 60529
Pollution Degree	3 conforming to IEC 60947
Overvoltage Category	II
Tropicalisation	2
Relative Humidity	93 % at 40 °C
Ambient Air Temperature For Storage	-40...70 °C
Ambient Air Temperature For Operation	-25...60 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9 cm
Package 1 Width	11 cm
Package 1 Length	16 cm
Package 1 Weight	535 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	14
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	7.93 kg

Contractual warranty

Warranty	18 months
----------	-----------

ความยั่งยืน

ฉลาก **Green Premium™** เป็นความมุ่งมั่นของSchneider Electric ในการส่งมอบผลิตภัณฑ์ที่มีประสิทธิภาพด้านสิ่งแวดล้อมที่ดีที่สุด Green Premium ให้คำมั่นว่าจะปฏิบัติตามกฎระเบียบล่าสุด ความโปร่งใสต่อผลกระทบด้านสิ่งแวดล้อม รวมถึงผลิตภัณฑ์หมุนเวียนและ CO₂ ต่ำ

คู่มือการประเมินความยั่งยืนของผลิตภัณฑ์เป็นเอกสารวิจัยที่ช่วยชี้แจงมาตรฐานฉลากสิ่งแวดล้อมทั่วโลกและวิธีการตีความการประเมิน

[เรียนรู้เพิ่มเติมเกี่ยวกับ Green Premium >](#)

[แนวทางในการประเมินความยั่งยืนของผลิตภัณฑ์ >](#)



ความโปร่งใส RoHS/REACH

ประสิทธิภาพด้านสุขภาพ

 Mercury Free	
 Rohs Exemption Information	Yes
 Halogen Free Plastic Parts Product	

ใบรับรองและมาตรฐาน

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information