

Product datasheet

Specifications



fuse holder - GK1 - 1 pole - 125 A - for fuse NFC 22 x 58 mm

GK1FB

EAN Code: 3389110255911

! Discontinued

Main

Range	TeSys
Product Name	TeSys GK1
Device Short Name	GK1 F
Fuse Size	22 x 58 mm
Product Or Component Type	Fuse holder
Poles Description	1P
Network Type	AC DC

Complementary

Network Frequency	50/60 Hz
Control Type	Toggle
Mounting Support	Rail
[Ui] Rated Insulation Voltage	690 V 500 V AC for early break contact 440 V DC for early break contact
[Ith] Conventional Free Air Thermal Current	100 A 40 °C with gG cartridge fuses 125 A 40 °C with aM cartridge fuses 125 A 40 °C with tubular links 6 A for early break contact
[Ipk] Rated Peak Withstand Current	8 kA with tubular links conforming to IEC 60269-1
Connections - Terminals	Screw terminals 1 cable(s) 35 mm² flexible without cable end Screw terminals 1 cable(s) 50 mm² solid without cable end Screw terminals 2 cable(s) 16 mm² flexible without cable end Screw terminals 2 cable(s) 25 mm² solid without cable end
Tightening Torque	2 N.m - on screw terminals
Operating Position	+/- 23°
Height	128 mm
Width	35 mm
Depth	93.5 mm
Net Weight	0.23 kg
Quantity Per Set	Set of 12

Environment

Standards	IEC 60947-3
-----------	-------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Protective Treatment	TC
Ambient Air Temperature For Operation	-50...70 °C

Contractual warranty

Warranty	18 months
----------	-----------