

Product datasheet

Specifications



Ultimate Slimline - 2-way switch - 1 gang - 16 AX - white

Local distributor code:

391097777

GRWH1012

EAN Code: 5018486538660

Main

Range Of Product	Ultimate
Aesthetic Name	Slimline
Product Or Component Type	Plate switch
Control Type	Rocker
Switch Function	2-way
Rated Current	16 AX at 230 V AC

Complementary

Connections - Terminals	Screw terminals
Material	Plastic
Quantity Per Set	Set of 10
Number Of Gangs	1 gang
Device Mounting	Wall mounted
Height	86 mm
Width	86 mm
Depth	24 mm

Environment

Standards	BS EN 60947-3 BS EN 60669-1
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.7 cm
Package 1 Width	3 cm
Package 1 Length	8.7 cm
Package 1 Weight	66 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.7 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	18.7 cm
Package 2 Length	15.8 cm
Package 2 Weight	748 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	100
Package 3 Height	17.5 cm
Package 3 Width	38.8 cm
Package 3 Length	48 cm
Package 3 Weight	8.02 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration