



Current limiter module, TeSys GV2, on device mounting Local distributor code:

20550051

GV1L3

EAN Code: 3389110209952

Main

Range	TeSys
Range Of Product	TeSys GV2
	TeSys Deca
Accessory / Separate Part Category	Protection accessory
Product Or Component Type	Current limiting module
Range Compatibility	TeSys GV2
	TeSys Deca
Product Compatibility	GV2RT
	GV2ME
	GV2P
	GV2L
Function Of Module	Increasing the breaking capacity of a circuit breaker
Mounting Location	On top of the circuit breaker
[le] Rated Operational Current	32 A
[Ith] Conventional Free Air Thermal Current	63 A conforming to IEC 60947-1
Activation Threshold	1500 A
Breaking Capacity	<= 100 kA depending on protective device
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
[Ui] Rated Insulation Voltage	690 V AC 50/60 Hz conforming to IEC 60947-1

Complementary

Connections - Terminals	Screw clamp terminals 1 x 1.525 mm² rigid Screw clamp terminals 2 x 1.510 mm² rigid Screw clamp terminals 1 x 1.525 mm² flexible without cable end Screw clamp terminals 2 x 1.510 mm² flexible without cable end Screw clamp terminals 1 x 1.516 mm² flexible with cable end Screw clamp terminals 2 x 1.54 mm² flexible with cable end
Tightening Torque	2.2 N.m
Net Weight	0.13 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	5.0 cm
Package 1 Length	8.0 cm

Package 1 Weight	122.0 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	24
Package 2 Height	15.0 cm
Package 2 Width	15.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.104 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

Connections and Schema

Current Limiter

