

เอกสารข้อมูลผลิตภัณฑ์

ข้อมูลจำเพาะ



Control station, Harmony eXLhoist, standard, Remote ZART8L with base ZARB12W

XARS8L12W

Main

Range Of Product	Harmony eXLhoist
Product Or Component Type	Control station
Device Short Name	XARS
Control Station Type	Wireless
Product Specific Application	Material handling Hoisting applications
Number Of Channels	50
Control Station Application	Stop function: SIL 2 maximum (can reach PL d/category 3) conforming to IEC 62061 Stop function: SIL 2 maximum (can reach PL d/category 3) conforming to ISO 13849-1 Emergency stop function: SIL 3 maximum (can reach PL e/category 4) conforming to IEC 62061 Emergency stop function: SIL 3 maximum (can reach PL e/category 4) conforming to ISO 13849-1 Motion function: SIL 1 maximum (can reach PL c/category 1) conforming to IEC 62061 Motion function: SIL 1 maximum (can reach PL c/category 1) conforming to ISO 13849-1 Limiter protection function: SIL 1 maximum (can reach PL c/category 1) conforming to IEC 62061 Limiter protection function: SIL 1 maximum (can reach PL c/category 1) conforming to ISO 13849-1

Complementary

Kit Composition	Remote control Base station
Operating Distance	100 m in free air
Cable Entry	Cable gland
Communication Network Type	Wireless: bluetooth low energy
Transmission Frequency	2.4 GHz

Environment

Radio Agreement	ANATEL ARIB FCC ICASA SRRC RSS
Relative Humidity	0...95 % at -20...45 °C storage

การดูแลสิทธิ์: เอกสารนี้ไม่มีวัตถุประสงค์เพื่อใช้แทน หรือใช้เพื่อกำหนดความเหมาะสม หรือความน่าเชื่อถือของผลิตภัณฑ์เหล่านี้สำหรับการใช้งานเฉพาะทาง

Electromagnetic Compatibility	Resistance to electrostatic discharge - test level: 4 kV class B (on contact) conforming to IEC 61000-4-2 Resistance to electrostatic discharge - test level: 8 kV class B (in air) conforming to IEC 61000-4-2 Resistance to radiated electromagnetic fields - test level: 10 V/m class B conforming to IEC 61000-4-3
Standards	IEC 60204-1 safety ISO 13849-1 safety IEC 62061 safety IEC 61508 safety ISO 13850 safety IEC 60204-32 hoisting applications ETSI EN 301 489-1 radio ETSI EN 301 489-3 radio ETSI EN 301 489-17 radio ETSI EN 300 440-2 radio ETSI EN 300 328 radio FCC part 15 radio RSS GEN issue 3 radio RSS 210 issue 8 radio ARIB STD-T81 radio
Product Certifications	CE UL CSA C-Tick JIS KC EAC

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	20.000 cm
Package 1 Width	29.000 cm
Package 1 Length	31.000 cm
Package 1 Weight	2.352 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	2
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	5.497 kg

ความยั่งยืน

ฉลาก **Green Premium™** เป็นความมุ่งมั่นของSchneider Electric ในการส่งมอบผลิตภัณฑ์ที่มีประสิทธิภาพด้านสิ่งแวดล้อมที่ดีที่สุด Green Premium ให้คำมั่นว่าจะปฏิบัติตามกฎระเบียบล่าสุด ความโปร่งใสต่อผลกระทบด้านสิ่งแวดล้อม รวมถึงผลิตภัณฑ์หมุนเวียนและ CO₂ ต่ำ

คู่มือการประเมินความยั่งยืนของผลิตภัณฑ์เป็นเอกสารวิจัยที่ช่วยชี้แจงมาตรฐานฉลากสิ่งแวดล้อมทั่วโลกและวิธีการตีความการปร

[เรียนรู้เพิ่มเติมเกี่ยวกับ Green Premium >](#)

[แนวทางในการประเมินความยั่งยืนของผลิตภัณฑ์ >](#)



ความโปร่งใส

ประสิทธิภาพด้านสุขภาวะ

Mercury Free	
Rohs Exemption Information	Yes
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information