Specifications





# TeSys GV4 - thermal magnetic circuit breaker - 115A 3P - with Everlink

Local distributor code: 407810958

GV4PE115N

EAN Code: 3606481310309

#### Main

Range Of Product	TeSys GV4
Range	TeSys Deca TeSys Deca
Device Short Name	GV4PE
Product Name	TeSys GV4 TeSys Deca
Product Or Component Type	Motor circuit breaker
Device Application	Motor protection
Trip Unit Technology	Electronic Thermal-magnetic

## Complementary

Poles Description	3P
Utilisation Category	Category A conforming to IEC 60947-2
	AC-3 conforming to IEC 60947-4-1
Operating Position	Any position
Motor Power Kw	37 kW at 400415 V AC 50/60 Hz
	45 kW at 400415 V AC 50/60 Hz
	55 kW at 400415 V AC 50/60 Hz
	45 kW at 500 V AC 50/60 Hz
	55 kW at 500 V AC 50/60 Hz
	75 kW at 500 V AC 50/60 Hz
	75 kW at 660690 V AC 50/60 Hz
	90 kW at 660690 V AC 50/60 Hz
	110 kW at 660690 V AC 50/60 Hz
Breaking Capacity	100 kA lcu at 220240 V AC 50/60 Hz conforming to IEC 60947-2
	50 kA Icu at 380415 V AC 50/60 Hz conforming to IEC 60947-2
	50 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2
	15 kA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2
	65 kA at 208Y/120 V AC 50/60 Hz conforming to UL 60947
	65 kA at 240 V AC 50/60 Hz conforming to UL 60947
	35 kA at 480Y/277 V AC 50/60 Hz conforming to UL 60947
	8 kA Icu at 660690 V AC 50/60 Hz conforming to IEC 60947-2
	25 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2
	18 kA at 600Y/347 V AC 50/60 Hz conforming to UL 60947
Control Type	Toggle
[In] Rated Current	115 A
Magnetic Tripping Current	1955 A
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz conforming to IEC 60947-2
[Ui] Rated Insulation Voltage	800 V AC 50/60 Hz conforming to IEC 60947-2
[Ith] Conventional Free Air Thermal Current	115 A conforming to IEC 60947-4-1

Life Is On Schneider

[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-2				
Power Dissipation Per Pole	4.6 W				
Mechanical Durability	40000 cycles				
Electrical Durability	10000 cycles for AC-3 at 440 V In/2 5000 cycles for AC-3 at 440 V In				
Maximum Operating Rate	25 cyc/h				
Rated Duty	Continuous conforming to IEC 60947-4-1				
Connections - Terminals	EverLink BTR screw connectors (top) 1 cable(s) 1.570 mm <sup>2</sup> - solid EverLink BTR screw connectors (top) 1 cable(s) 1.550 mm <sup>2</sup> - flexible EverLink BTR screw connectors (bottom) 1 cable(s) 2.595 mm <sup>2</sup> - solid EverLink BTR screw connectors (bottom) 1 cable(s) 2.570 mm <sup>2</sup> - flexible				
Tightening Torque	9 N.m for cable 1695 mm <sup>2</sup> 5 N.m for cable 1.510 mm <sup>2</sup>				
Mechanical Robustness	Vibrations: +/- 1 mm 213.2 Hz conforming to IEC 60068-2-6 Vibrations: 0.7 gn 13.2100 Hz conforming to IEC 60068-2-6 Shocks: 15 gn 11 ms conforming to IEC 60068-2-27				
Phase Failure Sensitivity	Yes conforming to IEC 60947-4-1				
Height	155 mm				
Width	81 mm				
Depth	116 mm				
Net Weight	1.45 kg				
Colour	Grey (RAL 7016)				
Suitability For Isolation	Yes conforming to IEC 60947-1				

## Environment

Standards	CSA C22.2 No 60947-4-1 UL 60947-4-1 EN/IEC 60947-4-1 EN/IEC 60947-2
Product Certifications	IEC UL CSA CCC EAC ATEX EU-RO MR
Climatic Withstand	conforming to IACS E10
Ik Degree Of Protection	IK07 conforming to IEC 62262
Pollution Degree	3
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ambient Air Temperature For Storage	-5085 °C
Fire Resistance	960 °C conforming to IEC 60695-2-11
Operating Altitude	5000 m
Ambient Air Temperature For Operation	-2570 °C

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	16.8 cm

Package 1 Width	11.0 cm
Package 1 Length	22.0 cm
Package 1 Weight	1.67 kg
Unit Type Of Package 2	\$03
Number Of Units In Package 2	5
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	9.0 kg

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Plastic Parts Product


#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

#### Performance Curves


#### Thermal-Magnetic Tripping Curves for GV4P, GV4PE, GV4PEM

Average Operating Times at 20 °C Related to Multiples of the Setting Current Hot state



- 1 Class 10
- 2 Class 20
- 3 Isd = 5...13x Ir
- 4 li = 17 ln


Cold state



- 2 Class 20
- 3 Isd = 5...13x Ir
- 4 li = 17 ln

# Current Limitation on Short-Circuit for GV4P, GV4PE, GV4PEM (3-Phase 400/415 V) Dynamic Stress


I peak = f (prospective lsc) at 1.05 Ue = 435 V



- 1 Maximum peak current
- 2 GV4P115
- 3 GV4P80
- 4 GV4P50
- 5 GV4P25
- 6 GV4P12
- 7 GV4P07
- 8 GV4P03
- 9 GV4P02


#### Thermal Limit on Short-Circuit for GV4P, GV4PE, GV4PEM

Thermal Limit in kA<sup>2</sup>2s in the Magnetic Operating Zone Sum of  $I^{2}$ dt = f (prospective Isc) at 1.05 Ue = 435 V




- 1 GV4P115
- 2 GV4P80
- 3 GV4P50
- 4 GV4P25
- 5 GV4P12
- 6 GV4P07
- 7 GV4P03
- 8 GV4P02


#### GV4 with Toggle: GV4LE, GV4PE, GV4PEM With EverLink® Connector




With Crimp Lug Connector




GV4 with Rotary Handle: GV4L, GV4P, or GV4LE, GV4PE, GV4PEM with GV4ADN01, GV4ADN02 Direct Mounting Rotary Handle Dimensions




GV4L, GV4P, GV4LE, GV4PE, GV4PEM Panel Mounting with M4 Screws



Door Cut-Out for Rotary Handle



**Minimum Safety Clearance** 



Toggle-type, rotary handle-type: identical clearance values. Safety Clearance (mm)

Salety Clearance (mm)						
	Painted Sheet Metal			Bare Sheet Metal		
	A	В	С	A	В	С
No accessory	30	0	0	40	0	5
Interphase barriers	0	0	0	0	0	5
Long terminal shield	0	0	0	0	0	5

Connections and Schema