Product datasheet

Specification





TeSys GV4 - thermal magnetic circuit breaker - 25A 3P - with Everlink

Local distributor code:

407810783 GV4PE25S

EAN Code: 3606481310590

Main

Range Of Product	TeSys GV4
Range	TeSys Deca TeSys Deca
Device Short Name	GV4PE
Product Name	TeSys GV4 TeSys Deca
Product Or Component Type	Motor circuit breaker
Device Application	Motor protection
Trip Unit Technology	Electronic Thermal-magnetic

Complementary

Poles Description	3P
Utilisation Category	Category A conforming to IEC 60947-2
	AC-3 conforming to IEC 60947-4-1
Operating Position	Any position
Motor Power Kw	7.5 kW at 660690 V AC 50/60 Hz
	5.5 kW at 400415 V AC 50/60 Hz
	7.5 kW at 500 V AC 50/60 Hz
	9 kW at 660690 V AC 50/60 Hz
	11 kW at 660690 V AC 50/60 Hz
	7.5 kW at 400415 V AC 50/60 Hz
	9 kW at 400415 V AC 50/60 Hz
	11 kW at 400415 V AC 50/60 Hz
	9 kW at 500 V AC 50/60 Hz
	11 kW at 500 V AC 50/60 Hz
	15 kW at 500 V AC 50/60 Hz
	15 kW at 660690 V AC 50/60 Hz
	18.5 kW at 660690 V AC 50/60 Hz
Breaking Capacity	120 kA Icu at 220240 V AC 50/60 Hz conforming to IEC 60947-2
	100 kA Icu at 380415 V AC 50/60 Hz conforming to IEC 60947-2
	70 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2
	30 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2
	18 kA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2
	100 kA at 208Y/120 V AC 50/60 Hz conforming to UL 60947
	100 kA at 240 V AC 50/60 Hz conforming to UL 60947
	65 kA at 480Y/277 V AC 50/60 Hz conforming to UL 60947
	10 kA Icu at 660690 V AC 50/60 Hz conforming to IEC 60947-2
	25 kA at 600Y/347 V AC 50/60 Hz conforming to UL 60947
Control Type	Toggle
[In] Rated Current	25 A
Magnetic Tripping Current	425 A
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz conforming to IEC 60947-2
[Ui] Rated Insulation Voltage	800 V AC 50/60 Hz conforming to IEC 60947-2

[Ith] Conventional Free Air Thermal Current	115 A conforming to IEC 60947-4-1		
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-2		
Power Dissipation Per Pole	4.6 W		
Mechanical Durability	40000 cycles		
Electrical Durability	40000 cycles for AC-3 at 440 V In/2 20000 cycles for AC-3 at 440 V In		
Maximum Operating Rate	25 cyc/h		
Rated Duty	Continuous conforming to IEC 60947-4-1		
Connections - Terminals	EverLink BTR screw connectors (top) 1 cable(s) 1.570 mm² - solid EverLink BTR screw connectors (top) 1 cable(s) 1.550 mm² - flexible EverLink BTR screw connectors (bottom) 1 cable(s) 2.595 mm² - solid EverLink BTR screw connectors (bottom) 1 cable(s) 2.570 mm² - flexible		
Tightening Torque	9 N.m for cable 1695 mm ² 5 N.m for cable 1.510 mm ²		
Mechanical Robustness	Vibrations: +/- 1 mm 213.2 Hz conforming to IEC 60068-2-6 Vibrations: 0.7 gn 13.2100 Hz conforming to IEC 60068-2-6 Shocks: 15 gn 11 ms conforming to IEC 60068-2-27		
Phase Failure Sensitivity	Yes conforming to IEC 60947-4-1		
Height	155 mm		
Width	81 mm		
Depth	116 mm		
Net Weight	1.45 kg		
Colour	Grey (RAL 7016)		
Suitability For Isolation	Yes conforming to IEC 60947-1		
Environment			
Standards	CSA C22.2 No 60947-4-1 UL 60947-4-1 EN/IEC 60947-4-1 EN/IEC 60947-2		
Product Certifications	IEC UL CSA CCC EAC ATEX EU-RO MR		
Climatic Withstand	conforming to IACS E10		
Ik Degree Of Protection	IK07 conforming to IEC 62262		
Pollution Degree	3		
Ip Degree Of Protection	IP40 conforming to IEC 60529		
Ambient Air Temperature For Storage	-5085 °C		
Fire Resistance	960 °C conforming to IEC 60695-2-11		
Operating Altitude	5000 m		
Ambient Air Temperature For Operation	-2570 °C		
Packing Units			
Unit Time Of Beatiage 4	202		

PCE

Unit Type Of Package 1

Number Of Units In Package 1	1
Package 1 Height	12.5 cm
Package 1 Width	9.0 cm
Package 1 Length	22.0 cm
Package 1 Weight	1.45 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	9
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	14.0 kg

Contractual warranty

Warranty 18 months

Sustainability Green Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Mercury Free
Ø	Rohs Exemption Information Yes
Ø	Pvc Free
Ø	Halogen Free Plastic Parts Product


Certifications & Standards

Reach Regulation	REACh Declaration				
Eu Rohs Directive	Compliant with Exemptions				
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information				
Environmental Disclosure	Product Environmental Profile				
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins				
Circularity Profile	End of Life Information				

Performance Curves

Thermal-Magnetic Tripping Curves for GV4P, GV4PE, GV4PEM

Average Operating Times at 20 $^{\circ}\text{C}$ Related to Multiples of the Setting Current Hot state




X the setting current in

- 1 Class 10
- 2 Class 20
- 3 lsd = 5...13x lr
- 4 li = 17 ln

Cold state

Product datasheet

GV4PE25S




- 1 Class 10
- 2 Class 20
- 3 lsd = 5...13x lr
- 4 li = 17 ln

Current Limitation on Short-Circuit for GV4P, GV4PE, GV4PEM (3-Phase 400/415 V)

Dynamic Stress

I peak = f (prospective lsc) at 1.05 Ue = 435 V




- 1 Maximum peak current
- 2 GV4P115
- 3 GV4P80
- 4 GV4P50
- 5 GV4P25
- 6 GV4P12
- 7 GV4P07
- 8 GV4P03
- 9 GV4P02

Thermal Limit on Short-Circuit for GV4P, GV4PE, GV4PEM

Thermal Limit in kA²2s in the Magnetic Operating Zone

Sum of I^2 dt = f (prospective lsc) at 1.05 Ue = 435 V




- GV4P115 1
- GV4P80 2
- GV4P50 3
- 4 GV4P25
- GV4P12 5
- GV4P07 6
- GV4P03 7
- GV4P02 8


Dimensions Drawings

GV4 with Toggle: GV4LE, GV4PE, GV4PEM

With EverLink® Connector




With Crimp Lug Connector




GV4 with Rotary Handle: GV4L, GV4P, or GV4LE, GV4PE, GV4PEM with GV4ADN01, GV4ADN02 Direct Mounting Rotary Handle

Dimensions




GV4L, GV4P, GV4LE, GV4PE, GV4PEM


Panel Mounting with M4 Screws



Door Cut-Out for Rotary Handle



Minimum Safety Clearance



Toggle-type, rotary handle-type: identical clearance values.

Safety Clearance (mm)						
	Painted She	Bare Sheet Metal				
	Α	В	С	Α	В	С
No accessory	30	0	0	40	0	5
Interphase barriers	0	0	0	0	0	5
Long terminal shield	0	0	0	0	0	5

Connections and Schema

Magnetic Motor Circuit Breakers GV4P, GV4PE, GV4PEM

