# **Product datasheet**





## TeSys GV2 - safety undervoltage trip - 220...240 V AC 60 Hz

Local distributor code: 402742636

GVAX226

! Discontinued on: 9 Feb 2023

EAN Code: 3389110346114

! Discontinued

#### Main

Range	TeSys TeSys Deca
Product Or Component Type	Safety undervoltage trip
Device Short Name	GVAX

### Complementary

oompicine nai y		
Range Compatibility	TeSys GV2ME TeSys Deca	
[Uc] Control Circuit Voltage	220240 V AC 60 Hz	
Control Circuit Voltage Limits	0.851.1 Un	
[Ui] Rated Insulation Voltage	sulation Voltage 690 V AC conforming to IEC 60947-1 600 V AC conforming to UL 60947-4-1 600 V AC conforming to CSA C22.2 No 60947-4-1	
Threshold Tripping Voltage	0.70.35 Un	
Inrush Power In Va	12 VA AC	
Inrush Power In W	8 W	
Hold-In Power Consumption In Va	3.5 VA AC	
Hold-In Power Consumption In W	1.1 W	
Operating Time	1015 ms conforming to IEC 60947-1	
On-Load Factor	100 %	
Connections - Terminals	Screw clamp terminals 1 cable(s) 12.5 mm²solid Screw clamp terminals 2 cable(s) 12.5 mm²solid Screw clamp terminals 1 cable(s) 0.752.5 mm²flexible without cable end Screw clamp terminals 2 cable(s) 0.752.5 mm²flexible without cable end Screw clamp terminals 1 cable(s) 0.751.5 mm²flexible with cable end Screw clamp terminals 2 cable(s) 0.751.5 mm²flexible with cable end	
Tightening Torque	< 1.4 N.m on screw clamp terminals	
Mechanical Durability	30000 cycles	
Quantity Per Set	Set of 10	
Height	89 mm	
Width	18 mm	
Depth	66 mm	
Net Weight	0.105 kg	
Colour	Dark grey	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.3 cm
Package 1 Width	3.6 cm
Package 1 Length	9.1 cm
Package 1 Weight	129.0 g

### **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>Ø</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

### Connections and Schema

GVAX •••